

HIGH-END BASEBOARD

BA SERIES

THE DOLCE VITA WITH BELLA

The high-end BELLA™ baseboard is undoubtedly the most beautiful offered on the market. Its breathtaking design and sturdy facade made of an aluminum extrusion make it the ideal choice for residential and commercial locations. The BELLA™ is available in a choice of two densities: 150 W or 250 W per linear foot.

°STELPRO



**EXTRUDED ALUMINUM FRONT COVER
WITH STRIKING END CAPS**

EXTREMELY SOLID, IMPACT AND RUST RESISTANT

**IDEAL FOR ANY ROOM IN YOUR HOME
AND MANY COMMERCIAL APPLICATIONS**

IDEAL FOR:

KITCHEN, LIVING ROOM, BEDROOM, BASEMENT, BUSINESS, OFFICE

COLOURS

- standard: white
- optional: silica white, graphite, almond, black, clear anodized (paint), textured charcoal, nickel, champagne, light bronze, dark brown (10% surcharge)

FINISH

epoxy-polyester powdercoat

MANUFACTURING

- 22-gauge steel cabinet
- extruded aluminum front cover with a thickness equivalent to 11 gauge with molded and curved end-caps
- discrete air inlet: air enters through the front of the unit and exits from the top
- thermal protection with automatic reset
- full-length wireway

ELEMENT

single tubular, stainless steel sheathed element with boxed aluminum fins for improved heat dissipation; the element is securely fastened at its center, floating in nylon sleeves at each end, eliminating expansion and contraction noises

CONTROL

- wall thermostat (not included) – the use of an electronic thermostat is strongly recommended
- built-in mechanical single pole or double pole thermostat, installed in the left or right junction box (optional)
- low voltage relay kit installed in the left or right junction box (optional)
- disconnect switch (optional)

INSTALLATION

- floor mounted
- wiring compartment at both ends of unit

ACCESSORIES

PRODUCT	DESCRIPTION	PRICE
BA1T1W*	built-in single pole thermostat [120 V-600 V]	
BA2T1W*	built-in double pole thermostat [120 V-600 V]	
BARE153*	built-in electronic low voltage relay [15 A @ 120-347 V]	
BARE156*	built-in electronic low voltage relay [6 A @ 600 V]	
BARE153T*	built-in electronic low voltage relay c/w transformer 24 V [15 A @ 208-347 V]	
BADIS*	disconnect switch [120-480 V]	
BADIS6*	disconnect switch [600 V]	

Electronic relays can receive a PWM (pulsed width modulation) or digital (on/off) signal.

* Factory installed

* Factory installation is strongly recommended

TECHNICAL SPECIFICATIONS

STANDARD DENSITY 250 W PER LINEAR FOOT			LOW DENSITY 150 W PER LINEAR FOOT			VOLTAGE	TOTAL LENGTH *		WEIGHT	
---	--	--	--------------------------------------	--	--	---------	----------------	--	--------	--

CODE	WATTS		CODE	WATTS		VOLTS	MM	IN.	KG	LB
BA0301W	300		---	---		120	529	20 13/16	2.3	5.1
BA0308W	300		---	---		208	529	20 13/16	2.3	5.1
BA0302W	300/225		---	---		240/208	529	20 13/16	2.3	5.1
---	300		---	---		277	529	20 13/16	2.3	5.1
---	300		---	---		347	529	20 13/16	2.3	5.1
---	300		---	---		480	529	20 13/16	2.3	5.1
---	300		---	---		600	529	20 13/16	2.3	5.1
BA0501W	500		BAL0301W	300		120	732	28 13/16	3.0	6.5
BA0508W	500		BAL0308W	300		208	732	28 13/16	3.0	6.5
BA0502W	500/375		BAL0302W	300/225		240/208	732	28 13/16	3.0	6.5
BA0507W	500		---	300		277	732	28 13/16	3.0	6.5
BA0503W	500		---	300		347	732	28 13/16	3.0	6.5
---	500		---	300		480	732	28 13/16	3.0	6.5
---	500		---	300		600	732	28 13/16	3.0	6.5
BA0751W	750		BAL0451W	450		120	978	38 1/2	3.6	8.0
BA0758W	750		BAL0458W	450		208	978	38 1/2	3.6	8.0
BA0752W	750/560		BAL0452W	450/340		240/208	978	38 1/2	3.6	8.0
BA0757W	750		BAL0457W	450		277	978	38 1/2	3.6	8.0
BA0753W	750		BAL0453W	450		347	978	38 1/2	3.6	8.0
BA0755W	750		---	450		480	978	38 1/2	3.6	8.0
BA0756W	750		---	450		600	978	38 1/2	3.6	8.0
BA1001W	1000		BAL0601W	600		120	1229	48 3/8	4.4	9.7
BA1008W	1000		BAL0608W	600		208	1229	48 3/8	4.4	9.7
BA1002W	1000/750		BAL0602W	600/450		240/208	1229	48 3/8	4.4	9.7
BA1007W	1000		BAL0607W	600		277	1229	48 3/8	4.4	9.7
BA1003W	1000		BAL0603W	600		347	1229	48 3/8	4.4	9.7
BA1005W	1000		---	600		480	1229	48 3/8	4.4	9.7
BA1006W	1000		---	600		600	1229	48 3/8	4.4	9.7
BA1251W	1250		BAL0751W	750		120	1478	58 3/16	5.2	11.4
BA1258W	1250		BAL0758W	750		208	1478	58 3/16	5.2	11.4
BA1252W	1250/940		BAL0752W	750/560		240/208	1478	58 3/16	5.2	11.4
BA1257W	1250		BAL0757W	750		277	1478	58 3/16	5.2	11.4
BA1253W	1250		BAL0753W	750		347	1478	58 3/16	5.2	11.4
BA1255W	1250		BAL0755W	750		480	1478	58 3/16	5.2	11.4
BA1256W	1250		BAL0756W	750		600	1478	58 3/16	5.2	11.4
BA1501W	1500		BAL0901W	900		120	1707	67 3/16	6.0	13.2
BA1508W	1500		BAL0908W	900		208	1707	67 3/16	6.0	13.2
BA1502W	1500/1125		BAL0902W	900/675		240/208	1707	67 3/16	6.0	13.2
BA1507W	1500		BAL0907W	900		277	1707	67 3/16	6.0	13.2
BA1503W	1500		BAL0903W	900		347	1707	67 3/16	6.0	13.2
BA1505W	1500		BAL0905W	900		480	1707	67 3/16	6.0	13.2
BA1506W	1500		BAL0906W	900		600	1707	67 3/16	6.0	13.2
---	1750		BAL1051W	1050		120	1953	76 7/8	6.8	15.0
BA1758W	1750		BAL1058W	1050		208	1953	76 7/8	6.8	15.0
BA1752W	1750/1310		BAL1052W	1050/790		240/208	1953	76 7/8	6.8	15.0
BA1757W	1750		BAL1057W	1050		277	1953	76 7/8	6.8	15.0
BA1753W	1750		BAL1053W	1050		347	1953	76 7/8	6.8	15.0
BA1755W	1750		BAL1055W	1050		480	1953	76 7/8	6.8	15.0
BA1756W	1750		BAL1056W	1050		600	1953	76 7/8	6.8	15.0
---	2000		BAL1201W	1200		120	2154	84 13/16	7.7	16.9
BA2008W	2000		BAL1208W	1200		208	2154	84 13/16	7.7	16.9
BA2002W	2000/1500		BAL1202W	1200/900		240/208	2154	84 13/16	7.7	16.9
BA2007W	2000		BAL1207W	1200		277	2154	84 13/16	7.7	16.9
BA2003W	2000		BAL1203W	1200		347	2154	84 13/16	7.7	16.9
BA2005W	2000		BAL1205W	1200		480	2154	84 13/16	7.7	16.9
BA2006W	2000		BAL1206W	1200		600	2154	84 13/16	7.7	16.9
---	2250		---	1350		120	2405	94 11/16	8.6	18.8
BA2258W	2250		BAL1358W	1350		208	2405	94 11/16	8.6	18.8
BA2252W	2250/1690		BAL1352W	1350/1010		240/208	2405	94 11/16	8.6	18.8
BA2257W	2250		BAL1357W	1350		277	2405	94 11/16	8.6	18.8
BA2253W	2250		BAL1353W	1350		347	2405	94 11/16	8.6	18.8
BA2255W	2250		BAL1355W	1350		480	2405	94 11/16	8.6	18.8
BA2256W	2250		BAL1356W	1350		600	2405	94 11/16	8.6	18.8
---	2500		---	1500		120	2629	103 1/2	9.4	20.7
BA2508W	2500		BAL1508W	1500		208	2629	103 1/2	9.4	20.7
BA2502W	2500/1875		BAL1502W	1500/1125		240/208	2629	103 1/2	9.4	20.7
BA2507W	2500		BAL1507W	1500		277	2629	103 1/2	9.4	20.7
BA2503W	2500		BAL1503W	1500		347	2629	103 1/2	9.4	20.7
BA2505W	2500		BAL1505W	1500		480	2629	103 1/2	9.4	20.7
BA2506W	2500		BAL1506W	1500		600	2629	103 1/2	9.4	20.7

* For the wall length, subtract 1/2 in. (13 mm) from the total length.

TECHNICAL DRAWINGS



