



Product Code	Nominal Size	R	FAB CUT LENGTH
029307	50mm (2")	610mm (24")	1295mm (51")

SIZES SHOWN ARE FOR REFERENCE
3D MODEL IS TO BE USED FOR
MANUFACTURING / VERIFICATION

PLASTIC/RUBBER SIZES

<small>PART WEIGHT: g at g/cm³ DENSITY. PART WEIGHT MAY VARY DEPENDING ON MATERIAL, GRADE AND MOLDING CONDITIONS PROJECTED AREA, ONE PART WITH SHRINKAGE APPLIED: Sq. In. SHRINKAGE:</small>		<small>ALL CHANGES MUST BE APPROVED AND RECORDED BY ENGINEERING</small>	
<small>UNIT: INCHES UNLESS DUAL DIMENSION: INCH [METRIC]</small>	<small>PROJECTION</small> 		
<small>THIS DRAWING AND ALL TECHNICAL INFORMATION APPEARING HEREON ARE PROPERTY OF IPEX TECHNOLOGIES INC. AND MUST BE KEPT IN CONFIDENCE BY THE RECIPIENT. THE SAME MAY NOT BE USED OR REPRODUCED EITHER IN WHOLE OR IN PART WITHOUT THE EXPRESS CONSENT OF IPEX TECHNOLOGIES INC.</small>		<small>TITLE</small> 029307	
<small>PAPER SIZE</small> ANSI B	<small>NAME</small>	<small>DATE</small>	<small>SCALE:</small> 1:1
<small>PART APPEARANCE:</small>	<small>COLOR:</small>	<small>DRAWN</small>	<small>MAT'L:</small>
<small>SURFACE FINISHES: (UNLESS OTHERWISE NOTED)</small>		<small>APP'D</small>	<small>PRODUCT CODE:</small>
<small>INSIDE:</small>	<small>OUTSIDE:</small>	<small>OTHER:</small>	029307
<small>DIMENSIONS ARE IN INCHES TOLERANCES (UNLESS OTHERWISE SPECIFIED) FRACTIONAL ± 1/32 X.X ± 0.015 X.XX ± 0.010 X.XXX ± 0.005 ANGULAR ± 1.0</small>		<small>CRITICAL DIMENSIONS ARE SHOWN AS **DIM** REFERENCE DIMENSIONS ARE SHOWN WITH REF. NOTE</small>	
<small>FILENAME:</small>	<small>FOLDER:</small>	<small>PROJECT No.</small>	