

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

LED REFLECTORS CHOICE SERIES

PAR20

ORDERING INFORMATION

Order code: 69209
Model number: P20/S2/6.5W/30K/40/CHOICE/STD
UPC: 069549025400
Case quantity: 12

PHYSICAL DATA

Shape: PAR20
Base: E26
Heat sink color: White

PERFORMANCE DATA

Watts (W): 6.5
Volts (VAC): 120
Colour temperature (K): 3 000
Lumen output (lm): 554
Efficacy (lm/W): 111
CRI: 90
Life L70 (h): 25 000
Dimming: Phase cut
Beam angle (°): 40
CBCP: 1 031
Power factor: 0.90
Frequency (Hz): 60
Operating temp. range: - 20 °C to 40 °C / - 4 °F to 104 °F

¹ Typical colour temperature range: +/- 5 %.

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.


³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.

COMPATIBLE DIMMERS¹

Brand	Model
LUTRON	PD-5NE, PD-6WCL, DVCL-153P, CTCL-153P, DVCL-253P, AYCL-253P, DVRP-253-WH, SELV-300P, MACL-153P
COOPER	AAL06, RRD-6NA-WH
LEVITON	IPL06, 6674, DSL06-1LZ, DSM10-1LZ, DDMX1
LUTRON	RH703PTUTC

¹ This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Standard recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.

DIMENSIONS



This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications.

Data is based upon tests performed in a controlled environment.

Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



3 yrs
warranty



dimmable

66

wet location



enclosed
fixture



ICES
005

RoHS

cUL us

FC

