

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

LED HIGH INTENSITY LAMP

CCT and Power Selectable

ORDERING INFORMATION

Order code: 69125
Model number: CRN/PS60W/2CCT/BYP/120-277/EX39/STD
UPC: 069549024748
Case quantity: 12
DLC Unique ID: S-UDVJYR

PHYSICAL DATA

Base: EX39
Type: 360° High Intensity

PERFORMANCE DATA

Watts (W): 42/60
Traditional equivalent (W) 250
Volts (V AC): 120-277
Color temperature (K)¹: 4 000/5 000
Lumen output (lm)²: 5 376/7 659.3
Efficacy (lm/W): 128/128.63
CRI: 80
Life L70 (h)³: 50 000
Beam angle (°): 360
Power factor: >0.9
Frequency (Hz): 50/60
Operating temp. range: - 40 °C / - 40 °F to 45 °C / 113 °F
Installation: Ballast Bypass

¹ Typical color temperature range: +/- 5 %.


² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.

³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.

LUMEN SPECIFICATION TABLE

Order code	Description	Watts (W)	4 000/5 000 K	
			Lumen output (lm)	Efficacy (lm/W)
69125	CRN/PS60W/2CCT/BYP/120-277/EX39/STD	42	5 376 lm	128 lm/W
		60	7 659.3 lm	128.63 lm/W

DIMENSIONS



60W

This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications.

Data is based upon tests performed in a controlled environment.

Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



ICES
005



enclosed
fixture

