

# Eaton XBUT6

Catalog number: XBUT6

Eaton XB IEC terminal block, Screw connection single level through-feed terminal block, 8.2 mm, Gray, 8 AWG/6 mm<sup>2</sup> maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XB IEC terminal block	XBUT6
<b>UPC</b>	<b>Product Length/Depth</b>
782116904945	1.75 in
<b>Product Height</b>	<b>Product Width</b>
2.17 in	.1 in
<b>Product Weight</b>	<b>Warranty</b>
.01 lb	1 year
<b>Certifications</b>	
UL Listed CSA Certified	

Type

IEC-XB Series

Voltage rating

IEC 800V, EN 700V, UL 600V

Amperage Rating

527 (IEC), 40A (EN), 50A (EN), 50A (UL)

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[XBUT6 AutoCAD 2D Footprint](#)

[XBUT6 2D PDF](#)

[XBUT6 3D Inventor](#)

[XBUT6 3D Model Xchange](#)

[XBUT6 2D Drawing Xchange](#)

[XBUT6 AutoCAD 2D Footprint \(mm\)](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT6](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2022 Eaton  
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)