




Parallel Jaw Grip - Lock, HDPE Wire to 1.362-Inch



This parallel jaw grip was specifically designed to securely pull slippery HDPE-coated cable or tree wire. The innovative high-traction surface grips the cable without damaging the outer jacket. The tough carbide grit technology withstands even the harshest jobsite conditions. The grip is spring-loaded for one-handed operation and easy placement on the conductor.

Specifications

Type:	Parallel Jaw Grip	Application:	Wire Pulling
Special Features:	High Traction Grip Surface, Lock	Overall Length:	13.05" (17.7 cm)
Overall Height:	8.5" (21.6 cm)	Overall Width:	6.975" (7 cm)
Material:	Forged Steel	Cable Type:	HDPE-Coated
Cable Diameter:	0.625" to 1.362" (15.9 to 34.6 mm)	Hot Latch:	Y
Swing Latch:	N	Spring:	Y
Locking Handle:	Y	Jaw Type:	Round
Jaw Length:	4.5" (11.4 cm)	Maximum Safe Load:	4000 lb (1814 kg)
Standard:	OSHA	Weight:	5.10 lb (2.3 kg)