

NetKey® Category 6A Punchdown Patch Panels

specifications

Category 6A/Class E_A punchdown patch panels shall terminate unshielded twisted 4-pair, 22 – 26 AWG, 100 ohm cable and mount to standard EIA 19 inches or 23 inches racks. Punchdown tool shall properly terminate each conductor for optimum performance. Universal T568A and T568B color-coded wiring schemes included.



technical information

Category 6A/Class E_A performance: Exceeds ANSI/TIA-568.2-D Category 6A and ISO 11801 Class E_A channel requirements at swept frequencies up to 500 MHz
Exceeds ANSI/TIA-568.2-D Category 6A and ISO 11801 Class E_A component requirements at swept frequencies up to 500 MHz

FCC and ANSI compliance: Meets ANSI/TIA-1096-A; contacts plated with 50 microinches of gold for superior performance

IEC compliance: Meets IEC 60603-7 and IEC 60512-99-002

PoE and PoH compliance: Meets IEEE 802.3af/802.3at and 802.3bt type 3 and type 4
Supports Power over HDBaseT up to 100 watts

c(UL)us Listed: UL 1863 (Use as communications circuit accessory); CSA standard C22.2

RoHS compliance: Compliant

Mounting options: Mounts to standard EIA 19" or 23" racks (23" requires use of extender brackets: PEB1 or PEB2)

key features and benefits

100% performance tested: Confidence that each port delivers specified performance

110 style punchdown termination: Utilizes industry standard termination style and includes wire retention cap

Identification: Write-on areas allow for port and panel identification

Industry standard RJ45 interface: Familiar to end-users; backwards compatible with Category 6

applications

NetKey Category 6A Punchdown Patch Panels provide a cost effective medium for ensuring that network bandwidth needs are easily met today and tomorrow. The NetKey Solution helps organizations efficiently and reliably meet data transmission needs. With certified performance to ISO 11801 Class E_A and ANSI/TIA-568.2-D Category 6A component standards, this system will support high bandwidth applications such as those required by education, healthcare, finance, and banking.

NetKey Category 6A Flat Punchdown Patch Panels

24-port, 1 RU: [NK6XPPG24Y](#)

48-port, 2 RU: [NK6XPPG48Y](#)

Termination Tools

Punchdown tool: [PDT110‡](#)


Snipping tool: [CWST](#)

Stripping tool: [CJAST](#)

Replacement retention cap: [DRWCIW-24](#)

‡Terminates the NetKey Keystone Punchdown Jack Module and NetKey Punchdown Patch Panels.

NetKey® Category 6A Punchdown Patch Panels



NK6XPPG24Y

NK6XPPG48Y

Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

© 2023 Panduit Corp.
ALL RIGHTS RESERVED.
CODS2-WW-ENG
4/2023