Wallbox Controls

Diva LED+ Dimmer

Dimmer for dimmable LED, CFL, halogen, and incandescent bulbs.

Features

- Large paddle switch with a captive linear-slide dimmer for a standard designer wallplate opening.
- LED+ includes the most advanced technology for superior dimmng of LED, CFL, incandescent, and halogen bulbs.
- UL_® Listed to control:
 - Dimmable LEDs
 - Dimmable compact fluorescent lamps (CFL) with integrated ballast
 - Lutron LTEA Hi-lume 1% forward-phase LED driver
 - Halogen
 - Incandescent
- Low-end adjustment to accommodate a wide range of bulbs.
- 100% factory tested.
- Formerly C•L.
- Coordinating Claro and Stainless Steel wallplates available separately.

Application Requirements

- When dimming LEDs or CFLs, only bulbs marked or rated as DIMMABLE may be used.
- For a complete list of compatible DIMMABLE LEDs please visit www.lutron.com/LEDfinder
- Some DIMMABLE LEDs and CFLs require a minimum number of bulbs for proper operation. For details and a list of bulbs, please visit www.lutron.com/LEDfinder

Model Numbers


DVCL-153P-XX^{1,2} Gloss Finish, Single pole/3-way³ DVCL-153PH-XXC⁴ Gloss Finish, Single pole/3-way³ DVSCCL-153P-XX¹ Satin Finish, Single pole/3-way³

¹ "XX" in the model number represents color/finish code; see "Colors and Finishes" on pages 3 & 4.

- ² For clamshell packaging, add "H" after "153P".
- ³ For 3-way and 4-way switching, use Claro switches or other mechanical switches.
- 4 Clamshell packaged product for Canada.
- ⁵ Clamshell packaged product. Available in AL, IV, LA, and WH.
- ⁶ Clamshell packaged product for Canada. Available in LA and WH.

LUTRON SPECIFICATION SUBMITTAL

| LUTRON SPECIFICATION SUBMITTAL | | Page |
|---------------------------------------|----------------|------|
| Job Name: | Model Numbers: | |
| | | |
| Job Number | | |
| Job Number: | | |



Packages

DVWCL-153PH-XX^{1,5}

DVWCL-153PH-XXC⁶

Includes

1 DVCL-153P-XX and 1 CW-1-XX (single-gang faceplate)

1 DVCL-153P-XX-C and 1 CW-1-XX (single-gang faceplate)

369682g 2 10.26.2021

Specifications

Regulatory Approvals

- UL_® Listed to US and Canadian safety requirements UL1472/CSA C22.2 184.1
- NOM

Power and Ratings

- 120 V∼ 60 Hz
- 150 W dimmable LED/CFL or
- 600 W incandescent/halogen or
- Mixed bulb type per Multigang and Mixed Bulb Type Ratings table (see page 3) or
- 250 W Lutron LTEA Hi-lume 1% forward-phase LED driver (maximum 6 drivers)

Environment


- For indoor use only.
- Operating temperatures 32 °F to 104 °F (0 °C to 40 °C).

Performance

- Power-failure memory
- Captive linear slider
- Electrostatic discharge tested
- Precise color matching
- Mechanical air-gap switch to disconnect load power

Warranty

• 1 Year Limited Warranty For additional Warranty information, please visit www.lutron.com/TechnicalDocumentLibrary/369-119_ Wallbox Warranty.pdf



Note: Requires a U.S. wallbox 21/2 in (64 mm) deep minimum.

| LUTRON SPECIFICATION SUBMITTAL | | Page |
|--------------------------------|----------------|------|
| Job Name: | Model Numbers: | |
| | | |
| Job Number: | | |
| | | |

369682g 3 10.26.2021 **Colors and Finishes** Add color/finish code to model # Example: DVCL-153P-WH **Gloss Finishes Satin Finishes** White Brilliant White Glacier White Architectural Snow lvory White BW SW WH IV GL RW Light Almond Lunar Gray Pebble Cobblestone Almond Mist LG PB CS AL MI Sand SD Brown Slate Midnight Biscuit Gray GR BR SL ΜN BI Black Taupe TP Pumice Clay CY Sage SA BL PM Deep Sea DE Truffle TF Signal Red SR Espresso EP

Due to printing limitations, colors and finishes shown cannot be guaranteed to perfectly match actual product colors.

• Color chip keychains are available for more precise color matching: Gloss Finishes: DG-CK-1 Satin Finishes: SF-CK-1

For coordinating wallplates and accessories, visit lutron.com/claro

| LUTRON SPECIFICATION SUBMITTAL | | Page |
|--------------------------------|----------------|------|
| Job Name: | Model Numbers: | |
| | | |
| Job Number: | | |
| | | |

369682g 4 10.26.2021

Colors and Finishes (cont.)

Satin Colors (while supplies last)

| Hot | Merlot | Plum | Turquoise |
|------------|-----------|-------------|------------|
| HT | MR | PL | TQ |
| Palladium | Eggshell | Sienna | Terracotta |
| PD | ES | Sl | TC |
| Greenbriar | Bluestone | Mocha Stone | Goldstone |
| GB | BG | MS | GS |
| | | | |

Desert Stone DS

Limestone LS

Stone ST

Due to printing limitations, colors and finishes shown cannot be guaranteed to perfectly match actual product colors.

• Color chip keychains are available for more precise color matching: Satin Colors: SC-CK-1 (while supplies last)

| LUTRON SPECIFICATION SUBMITTAL | | Page |
|---------------------------------------|----------------|------|
| Job Name: | Model Numbers: | |
| | | |
| Job Number: | | |
| | | |


Page

Multigang and Mixed-Bulb-Type Ratings

When installing more than one dimmer in the same wallbox, it may be necessary to remove some side sections prior to wiring **(see diagram)**. Removal of dimmer side sections may reduce maximum wattage, as shown in the chart below.

Mixing bulb types (using a combination of LED/CFL, and incandescent/halogen bulbs) will also affect the maximum ratings, as shown in the chart below.

*EXAMPLE: If one set of side sections is removed and you have three 10 W LED bulbs installed (Total LED Wattage = 30 W), you may add up to 300 W of incandescent or halogen lighting.




| Total LED/CFL 🛛 🚳 🚝 Wattage Installed LED CFL | | Maximum Allowable Incandescent/Halogen Wattage | | |
|--|---|--|----------------|-----------------|
| (Wattage per bulb x # of bulbs) | | No sides removed | 1 side removed | 2 sides removed |
| 0 W | + | 600 W | 500 W | 400 W |
| 1 W – 25 W | + | 500 W | 400 W | 300 W |
| 26 W – 50 W | + | 400 W | 300 W | 200 W |
| 51 W – 75 W | + | 300 W | 200 W | 100 W |
| 76 W – 100 W | + | 200 W | 100 W | 50 W |
| 101 W – 125 W | + | 100 W | 50 W | 0 W |
| 126 W – 150 W | + | 0 W | 0 W | 0 W |


| Job Name: | Model Numbers: | |
|-------------|----------------|--|
| | | |
| Job Number: | | |
| | | |

369682g 6 10.26.2021


Operation (View with wallplate removed)



1 Switch Turns lights ON and OFF.




Lever-type Adjustment Dial



OR

Wheel-type Adjustment Dial




Page

| Job Name: | Model Numbers: |
|-------------|----------------|
| | |
| Job Number: | |
| | |


LED+ Dimmer

Wiring Diagrams


Single-Pole Wiring



3-Way Wiring



4-Way Wiring



CATION CUDNITTAL

| SPECIFICATION SUBMITTAL | | Page |
|-------------------------|----------------|------|
| Job Name: | Model Numbers: | |
| | | |
| | | |
| Job Number: | | |

- * or Copper/Black screw terminal
- *; or Brass/Gold screw terminal
 - ** or Green screw terminal
 - t Please refer to the switch's instruction sheet for proper wiring.

Note for 4-Way Wiring: Dimmer must be installed Line Side or Load Side. It cannot be installed in the

4-way location.

The Lutron logo, Lutron, Claro, C•L, Hi-lume, LED+, Satin Colors and Diva are trademarks or registered trademarks of Lutron Electronics Co., Inc. in the US and/or other countries.

All other product names, logos, and brands are

property of their respective owners.