RadioRAZ product specifications


369971c


GRAFIK T RF C•L Hybrid Keypads

RadioRA 2 architectural GRAFIK T RF C•L Hybrid keypads function as a dimmer and keypad combined into a single device. Hybrid keypads are great for retro-fit applications since they eliminate the need to install two separate devices. Normal keypad operation is available if no load is connected or load burns out.¹

Features


- Hybrid keypad allows for local control of load as well as typical keypad functionality.
- Hybrid keypad will function as a normal keypad when no load is installed or load burns out.¹
- Custom, backlit, engraved, scene/zone descriptions on faceplate.
- Dynamic Backlighting Management (DBM) automatically adjusts the intensity of the backlit engraving to ensure text is readable in any light.
- All buttons are fully programmable, including the raise/lower functionality.
- C•L technology with microprocessor based dimming for control of dimmable LED lamps.
- If using LED bulbs, they must be Lutron compatible! For compatibility and performance information, visit our website at www.lutron.com/led, which is constantly being updated.
- Optional neutral connection available for superior LED dimming performance.¹
- Simple touch control.
- Distinctive architectural aesthetic.
- Low-end and high-end trim are available for improved LED dimming performance.
- Installs in single-pole or multi-location applications. Companion devices are available for multi-location control with a hybrid keypad (maximum 4 companion devices per keypad, 1 main control per circuit).²
- Use Lutron GRAFIK T wallplates (sold separately). See **Colors and Finishes** on page 13 for details.
- Lutron GRAFIK T wallplates snap on with no visible means of attachment.





2 Button Keypad

4 Button Keypad





6 Button Keypad

5 Button Keypad



Companion Device

¹ If no load is connected, a neutral connection is required.

² Companion devices provide control of local load only.

RadioRAZ product specifications

369971c

10.26.16

GRAFIK T RF C•L Hybrid Keypads

Model Numbers

Hybrid Keypads ¹	
	Clear Connect RF Technology
RRT-GH2B	250 W Dimmable LED ² 600 W Incandescent/Halogen
RRT-GH4B	400 VA (300 W) Magnetic Low-Voltage with Halogen based lamps
RRT-GH5B	3.3 A (400 VA) Dimmable Fluorescent ³
RRT-GH6B	3.3 A (400 W) Hi-lume 1% 2-wire LED driver (10 driver maximum) Neutral connection available Multi-location dimmer
Companion Device	
RT-GRDW	Companion device (works with hybrid keypad, dimmer or switch)

1 Not for use with receptacles or appliances (e.g., garbage disposals). See Application Note #109 for compatibility with dimmable receptacles.

2 If using LED bulbs, they must be Lutron compatible! For compatibility and performance information, visit our website at www.lutron.com/led, which is constantly being updated.

³ Includes Mark X_®, Tu-Wire, and POWERSENSE_® ballasts.

Design Features

- When neutral is connected, the Hybrid Keypad can be used as a Normal Keypad even if there is no load.
- If load is connected the top button will toggle the load (before commissioning).
- Internal dimmer can be assigned to any button on the Hybrid Keypad and can be programmed • to be controlled by any Keypad.
- Can be installed in either single location or multilocation (with a Companion Device) installations. Companion devices connected to Hybrid Keypad will control local lighting zone only.
- Can be installed in two-wire or neutral wire applications.

- Dynamic Backlighting Management (DBM) ٠ automatically adjusts the intensity of the backlit engraving to ensure text is readable in any light.
- At the press of a keypad button, lights fade ON or OFF to desired levels and shades/draperies open or close to desired shade positions.
- Keypad buttons are programmable to select scene or room preset levels or positions. Buttons can also be programmed with raise or lower functions.
- Faceplates are ordered separately and can be custom engraved with scene or zone description.



GRAFIK T RF C•L Hybrid Keypads

Specifications

Model Numbers	Hybrid Keypads: RRT-GH2B, RRT-GH4B, RRT-GH5B, RRT-GH6B
	Companion Device: RT-GRDW
	Wallplate ¹ : LWT-G-XXX-E, LWT-GG-XXX-E, LWT-GGG-XXX-E,
	LWT-GGGG-XXX-E, LWT-GT-XXX-E, LWT-GGT-XXX-E,
	LWT-GGGT-XXX-E, LWT-TG-XXX-E, LWT-GTT-XXX-E,
	LWT-GGTT-XXX-E, LWT-TGG-XXX-E, LWT-GTTT-XXX-E,
	LWT-TTG-XXX-E, LWT-TGGG-XXX-E, LWT-TTTG-XXX-E,
	LWT-TTGG-XXX-E
Power	120 V∼ 50/60 Hz
Typical Power	Hybrid Keypad: 0.20 W
Consumption	Companion Device: 0.10 W
	Test conditions: load is off, if connected.
Regulatory	Compliant with UL 1472, Compliant with CSA C22.2 NO. 184.1-15, Compliant
Approvals	with NOM 003, Compliant with Part 15 of the FCC rules and Industry Canada
	license-exempt IC standards, IFTEL
Environment	Ambient operating temperature: 32 °F to 104 °F (0 °C to 40 °C), 0% to 90%
	humidity, non-condensing. Indoor use only.
Communications	Hybrid Keypads communicate with the RadioRA 2 system through Radio
	Frequency (RF) and must be located within 30 ft (9 m) of a repeater. Companion
	devices are not required to be within a specific range of a repeater.
ESD Protection	Tested to withstand electrostatic discharge without damage or memory loss.
Surge Protection	Tested to withstand surge voltages without damage or loss of operation, in
J	accordance with IEEE C62.41-1991 Recommended Practice on Surge Voltages
	in Low-Voltage AC Power Circuits.
Power Failure	Power failure memory: should power be interrupted, the control will return to its
(load connected	previous state when power is restored.
only)	
Mounting	Requires a U.S. wallbox. 31/2 in (89 mm) deep recommended, 21/4 in (57 mm)
-	deep minimum.
Wiring	Uses conventional 3-way and 4-way wiring. Total multi-location wire length (blue
(load connected	wire) between all units must not exceed 150 ft (45 m).
only)	
Warranty	www.lutron.com/TechnicalDocumentLibrary/warranty.pdf

¹ "XXX" in the model number represents color/finish code. See Colors and Finishes on page 13 for details.

З

GRAFIK T RF C•L Hybrid Keypads

Ganging and Derating

When combining controls in the same wallbox, derating is required. See **Load Type and Capacity**. No derating is required for companion devices.

Load Type and Capacity

Control 1,2,3	Load Type	Not Ganged	End of Gang	Middle of Gang	Neutral Connection
RRT-GH2B RRT-GH4B RRT-GH5B RRT-GH6B	LED	250 W	250 W	250 W	
	MLV Halogen ^{4,5,6}	400 VA (300 W)	400 VA (300 W)	400 VA (300 W)	
	Incandescent/ Halogen	600 W	500 W	400 W	Optional
	Lutron Hi-lume 1% 2-wire LED Driver	3.3 A (400 W), 10 drivers max	3.3 A (400 W), 10 drivers max	3.3 A (400 W), 10 drivers max	
	Dimmable Fluorescent ⁷	3.3 A (400 VA)	3.3 A (400 VA)	3.3 A (400 VA)	Required

1 Designed for use with permanently installed LED, incandescent, tungsten halogen, or magnetic low voltage transformers with halogen based lamps.

² Power Boosters/Load Interfaces: can be used to control power boosters/load interfaces. For a list of compatible power boosters/load interfaces see **Compatible Power Boosters and Load Interfaces**. When using with power boosters/load interfaces, the neutral must be connected.

³ Not for use with receptacles or appliances (e.g., garbage disposals). See Application Note #109 for compatibility with dimmed receptacles.

4 Low-Voltage Applications: Use only with magnetic (core and coil) low-voltage transformers with halogen based lamps. Not recommended for use with electronic (solid-state) low-voltage transformers but UL® listed for dimmable ELV transformers.

⁵ Operation of a low-voltage circuit with lamps inoperative or removed may result in transformer overheating and premature failure. Lutron strongly recommends the following:
 Do not operate low-voltage circuits without operative lamps in place.

Do not operate low-voltage circuits without operative lamps
Replace burned-out lamps as soon as possible.

Replace burned-out lamps as soon as possible.

• Use transformers that incorporate thermal protection or fused transformer primary windings to prevent transformer failure due to overcurrent.

⁶ When using the hybrid keypad to control MLV halogen fixtures, the maximum lamp wattage is determined by the efficiency of the transformer, with 70%–85% as typical. For actual transformer efficiency, contact either the fixture or transformer manufacturer. The total VA rating of the transformer(s) shall not exceed the VA rating of the hybrid keypad.

4

7 Includes Mark X_®, Tu-Wire, and POWERSENSE_® ballasts.

RadioRA2 product specifications

369971c

GRAFIK T RF C•L Hybrid Keypads

Minimum Load

Keypad		LED ¹		Incandescent/ Halogen		MLV Halogen ²	
Application	Number of Companion Devices	With Neutral Connected	With Neutral Disconnected	With Neutral Connected	With Neutral Disconnected	With Neutral Connected ²	With Neutral Disconnected
Single Pole	0	1 LED lamp ³	3 LED lamps ³	5 W	80 W	40 W	80 W
Multi-location	1	1 LED lamp ³	4 LED lamps ³	5 W	120 W	40 W	120 W
Multi-location	2	1 LED lamp ³	5 LED lamps ³	5 W	160 W	40 W	160 W
Multi-location	3	1 LED lamp ³	6 LED lamps ³	5 W	200 W	40 W	200 W
Multi-location	4	1 LED lamp ³	7 LED lamps ³	5 W	240 W	40 W	240 W

¹ Includes Lutron compatible LED replacement lamps and Hi-lume 1% 2-wire LED driver.

² Must meet transformer minimum load requirements.

³ If using LED bulbs, they must be Lutron compatible! For compatibility and performance information, visit our website at www.lutron.com/led, which is constantly being updated.

Compatible Power Boosters and Load Interfaces

Some local controls can be used to control power boosters or load interfaces. Up to three power boosters or load interfaces can be used with one control. See table below for a list of controls and compatible power boosters and load interfaces. When controlling power boosters/load interfaces, the neutral must be connected.

Control	Phase Adaptive Power Modules (PHPM-PA-120-WH & PHPM-PA-DV-WH)1	3-wire Fluorescent Power Modules (PHPM-3F-120-WH & PHPM-3F-DV-WH) ²	Switched Power Module (PHPM-SW-DV-WH) ³	0-10 V Interface and Switching Module (GRX-TVI) ⁴
RRT-GH2B RRT-GH4B RRT-GH5B RRT-GH6B	\checkmark	\checkmark		✓

5

¹ See Lutron P/N 369356 for wiring diagrams.

² See Lutron P/N 369355 for wiring diagrams.

³ See Lutron P/N 369357 for wiring diagrams.


⁴ See Lutron P/N 369247 for wiring diagrams.

RadioRAZ product specifications

369971c

GRAFIK T RF C•L Hybrid Keypads

Operation¹



RadioRA2 product specifications

369971c


10.26.16


GRAFIK T RF C•L Hybrid Keypads

Dimensions


All dimensions are shown as in (mm)

Front View





Mounting and Parts Identification



7




10.26.16

GRAFIK T RF C•L Hybrid Keypads

Wiring Diagrams


Wiring Diagram 1

Single Location Installation with Optional Neutral^{1,2} RRT-GH2B, RRT-GH4B, RRT-GH5B, or RRT-GH6B



Wiring Diagram 2

Normal Keypad Wiring (No load connected) RRT-GH2B, RRT-GH4B, RRT-GH5B, or RRT-GH6B



¹ When using controls in single location installations, cap the blue wire. **Do not** connect the blue wire to any other wiring or to ground.

² When neutral wire connection is unavailable, cap the white wire. **Do not** connect the white wire to any other wiring or to ground.

Continued on next page ...




10.26.16

GRAFIK T RF C•L Hybrid Keypads

Wiring Diagrams (continued)


Wiring Diagram 3

Multi-Location Installation without Neutral^{1,2,3} - **Keypad Line Side** RRT-GH2B, RRT-GH4B, RRT-GH5B, or RRT-GH6B with RT-GRDW



Wiring Diagram 4

Multi-Location Installation without Neutral^{1,2,3} - Keypad Load Side RRT-GH2B, RRT-GH4B, RRT-GH5B, or RRT-GH6B with RT-GRDW



1 When neutral wire connection is unavailable, cap the white wire. **Do not** connect the white wire to any other wiring or to ground.

2 Up to 4 companion devices may be connected to the dimmer. Total blue traveler wire length may be up to 150 ft (45 m).

3 Dimmers may be connected on the Line side or Load side of a multi-location installation if neutral is not connected. The hybrid keypad cannot be installed in the middle location of a 4-way installation.

9

Continued on next page...




GRAFIK T RF C•L Hybrid Keypads

Wiring Diagrams (continued)

Wiring Diagram 5

Multi-Location Installation with Neutral^{1,2} - Keypad Line Side RRT-GH2B, RRT-GH4B, RRT-GH5B, or RRT-GH6B with RT-GRDW




¹ Up to 4 companion devices may be connected to each hybrid keypad. Total blue traveler wire length may be up to 150 ft (45 m). ² Control must be installed on line side of circuit if using neutral wire.

Wiring Diagram 6

Multi-Location Installation with PHPM - Neutral Required

RRT-GH2B, RRT-GH4B, RRT-GH5B, or RRT-GH6B with RT-GRDW



Continued on next page...




10.26.16

GRAFIK T RF C•L Hybrid Keypads

Wiring Diagrams (continued)


Wiring Diagram 7

Multi-Location Installation with GRX-TVI - Neutral Required RRT-GH2B, RRT-GH4B, RRT-GH5B, or RRT-GH6B with RT-GRDW



Wiring Diagram 8

Multi-Location Installation with Hi-lume 1% 2-wire LED Driver with Neutral RRT-GH2B, RRT-GH4B, RRT-GH5B, or RRT-GH6B with RT-GRDW



Continued on next page ...




GRAFIK T RF C•L Hybrid Keypads

Wiring Diagrams (continued)

Wiring Diagram 9


Multi-Location Installation with Hi-lume 1% 2-wire LED Driver without Neutral - Keypad Line Side

RRT-GH2B, RRT-GH4B, RRT-GH5B, or RRT-GH6B with RT-GRDW



Wiring Diagram 10

Multi-Location Installation with Hi-Lume LED Driver without Neutral - Keypad Load Side RRT-GH2B, RRT-GH4B, RRT-GH5B, or RRT-GH6B with RT-GRDW



RadioRA2 product specifications


369971c

10.26.16

GRAFIK T RF C•L Hybrid Keypads

How to Build a Faceplate Kit Model Number

Ganging with GRAFIK T controls.




Colors and Finishes




- Due to printing limitations, colors and finishes shown cannot be guaranteed to perfectly match actual product colors.
- Color chip keychains are available for more precise color matching:
- Architectural Matte Finishes: AM-CK-1


Correct (LWT-GTT-XXX-E⁵)



Correct (LWT-TTG-XXX-E⁵)

TTGG TTTG





1 GRAFIK T controls will only fit into "G" openings.

² New Architectural accessories will fit into "T" openings when ganging with GRAFIK T controls.


- ³ GRAFIK T controls cannot be ganged with Vierti controls or wallplates.
- 4 GRAFIK T controls cannot be ganged with Palladiom controls ("P" openings)

⁵ "XXX" in the model number represents color/finish code. See Colors and Finishes on page 13 for details.



GRAFIK T RF C•L Hybrid Keypads

GRAFIK T Wallplates



2

"XXX" in the model number represents color/finish code. See **Colors and Finishes** on page 13 for details. "E" in the model number represents custom engraving on the faceplate and is defined and ordered using the RadioRA 2 GUI software.

Lutron, CoL, Clear Connect, Hi-lume, Palladiom, RadioRA, Tu-Wire and Vierti are trademarks of Lutron Electronics Co., Inc., registered in the U.S. and other countries.

FASS and GRAFIK T are trademarks of Lutron Electronics Co., Inc.

Mark X is a registered trademark of Philips Electronics North America Corporation

POWERSENSE is a trademark of Community Light & Sound, Inc.

UL is a trademark of ULLEC

Customer Assistance: 1.844.LUTRON1 (U.S.A./Canada)