

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

T8 - BALLAST BYPASS

5 CCT SELECTABLE

ORDERING INFORMATION

Order code: 69194
Model number: T8/14W/80/5CCT/48/BYP/120-277/STD
UPC: 069549025332
Case quantity: 25
DLC Unique ID: S-UMVD09

PHYSICAL DATA


Shape: T8
Base: G13
Material: Glass
Length in. (mm): 48 (1 219)

PERFORMANCE DATA

Installation method: Ballast bypass
Watts (W): 14
Volts (VAC): 120-277
Colour temperature (K)1: 3 000/3 500/4 000/5 000/6 500
Lumen output (lm)2: 1 800
CRI: 80+
Life L70 (h)3: 50 000
Beam angle (°): 210°
Power factor: 0.90
Frequency (Hz): 50/60
Operating temp. range: -25°C/-13°F to 45°C/ 113°F

¹ Typical color temperature range: +/- 5 %.
² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.
³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.

DIMENSIONS



ADDITIONAL INFORMATION

Only for ballast bypass installation in 120-277 V applications.
 Not for use in 347 V direct line voltage applications.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications.
 Data is based upon tests performed in a controlled environment.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

