



SAFETY DATA SHEET

1. Identification

Product identifier OCAL PVC Patching Compound White

Other means of identification

SDS number SDS-00022

Product code PATCHT-W

Recommended use PVC Patching Compound.

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Company name ABB Installation Products Inc.

Address 860 Ridge Lake Blvd.

Memphis, TN 38120

USA

Telephone 901-252-5000 ext. 8324

Emergency telephone CHEMTREC - 24 hours:
+1-800-424-9300 (Toll-free)
+1 703-741-5970

2. Hazard(s) identification

Physical hazards Not classified.

Health hazards Skin corrosion/irritation Category 2
Serious eye damage/eye irritation Category 1

OSHA defined hazards Not classified.

Label elements



Signal word Danger

Hazard statement Causes skin irritation. Causes serious eye damage.

Precautionary statement

Prevention Wash thoroughly after handling. Wear protective gloves/eye protection/face protection.

Response If on skin: Wash with plenty of water. If skin irritation occurs: Get medical advice/attention. Take off contaminated clothing and wash it before reuse. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a poison center/doctor.

Storage Store away from incompatible materials.

Disposal Dispose of waste and residues in accordance with local authority requirements.

Hazard(s) not otherwise classified (HNOC) None known.

Supplemental information None.

3. Composition/information on ingredients

Mixtures

Chemical name	CAS number	%
Polyvinyl chloride	9002-86-2	50 - 60
Diisononyl phthalate	28553-12-0	20 - 30
Calcium carbonate	1317-65-3	5 - 10

Chemical name	CAS number	%
2,2,4-Trimethylpentane-1,3-diol monoisobutyrate	25265-77-4	1 - 5
Alkanes, C10-13-iso-	68551-17-7	1 - 5
Calcium oxide	1305-78-8	1 - 5
Titanium dioxide	13463-67-7	1 - 5

Composition comments The specific chemical identity and/or exact percentage of component(s) have been withheld as a trade secret.
All concentrations are in percent by weight unless otherwise indicated.

4. First-aid measures

Inhalation At ambient/normal handling temperatures, minimal or no irritation due to inhalation of vapor/mist is expected. If overcome by vapor from hot product, immediately remove from further exposure and call a physician.

Skin contact Remove contaminated clothing. Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.

Eye contact Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention immediately.

Ingestion Rinse mouth. Get medical attention if symptoms occur.

Most important symptoms/effects, acute and delayed Causes serious eye damage. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Permanent eye damage including blindness could result. Skin irritation. May cause redness and pain.

Indication of immediate medical attention and special treatment needed Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.

General information Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media Water fog. Foam. Dry chemical powder. Carbon dioxide (CO₂).

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

Specific hazards arising from the chemical Containers may explode when heated. During fire, hazardous combustion products are released that may include: Carbon oxides. Chlorine compounds. Toxic fumes.

Special protective equipment and precautions for firefighters Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

Fire fighting equipment/instructions In case of fire and/or explosion do not breathe fumes. Move containers from fire area if you can do so without risk. Cool containers exposed to flames with water until well after the fire is out. Prevent runoff from fire control or dilution from entering streams, sewers, or drinking water supply.

Specific methods Use standard firefighting procedures and consider the hazards of other involved materials.

General fire hazards Will burn if involved in a fire.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. In case of spills, beware of slippery floors and surfaces. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.

Methods and materials for containment and cleaning up Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.

Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Environmental precautions Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling

Avoid breathing mist or vapor. Do not ingest. Use with adequate ventilation. Eating, drinking, and smoking should be prohibited in areas where this material is handled, stored, and processed. Wash hands thoroughly after handling. In case of spills, beware of slippery floors and surfaces. Wear appropriate personal protective equipment (See Section 8). Observe good industrial hygiene practices. Do not get in eyes and avoid contact with skin and clothing.

Conditions for safe storage, including any incompatibilities

Keep container tightly closed in a dry and well-ventilated place. Store in original container. Protect from direct sunlight. Keep container tightly closed and sealed until ready for use. Containers which are opened must be carefully resealed and kept upright to prevent leakage. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Components	Type	Value
Polyvinyl chloride (CAS 9002-86-2)	STEL	5 ppm
	TWA	1 ppm

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value	Form
Calcium carbonate (CAS 1317-65-3)	PEL	5 mg/m ³	Respirable fraction.
		15 mg/m ³	Total dust.
Calcium oxide (CAS 1305-78-8)	PEL	5 mg/m ³	
Titanium dioxide (CAS 13463-67-7)	PEL	15 mg/m ³	Total dust.

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Calcium oxide (CAS 1305-78-8)	TWA	2 mg/m ³	
Polyvinyl chloride (CAS 9002-86-2)	TWA	1 mg/m ³	Respirable fraction.
Titanium dioxide (CAS 13463-67-7)	TWA	10 mg/m ³	

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value	Form
Calcium carbonate (CAS 1317-65-3)	TWA	5 mg/m ³	Respirable.
		10 mg/m ³	Total
Calcium oxide (CAS 1305-78-8)	TWA	2 mg/m ³	

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower must be available when handling this product.

Individual protection measures, such as personal protective equipment

Eye/face protection

Wear approved chemical safety goggles. Wear face shield if there is risk of splashes.

Skin protection

Hand protection

Wear appropriate chemical resistant gloves. Nitrile, butyl rubber or neoprene gloves are recommended. Other suitable gloves can be recommended by the glove supplier.

Skin protection

Other

Wear suitable protective clothing. Selection of specific items such as boots, apron, or full body suit will depend on task.

Respiratory protection	In case of insufficient ventilation, wear suitable respiratory equipment. Follow OSHA respirator regulations (29CFR 1910.134) and use NIOSH/MSHA approved respirators. Check with respiratory protective equipment suppliers.
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
General hygiene considerations	Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state	Liquid.
Form	Heavy glossy fluid.
Color	White.
Odor	Mild.
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not available.
Flash point	> 212 °F (> 100 °C)
Evaporation rate	Not available.
Flammability (solid, gas)	Not applicable.
Upper/lower flammability or explosive limits	
Explosive limit - lower (%)	1 %
Explosive limit - upper (%)	5 %
Vapor pressure	Not available.
Vapor density	Not available.
Relative density	1.29 (Water=1)
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not applicable.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Explosive properties	Not explosive.
Oxidizing properties	Not oxidizing.

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Avoid heat, sparks, open flames and other ignition sources. Protect against direct sunlight. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents. Strong reducing agents.
Hazardous decomposition products	Decomposition is not expected under normal conditions of use and storage. Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapors. Chlorine compounds. Toxic fumes.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Prolonged inhalation may be harmful.
-------------------	--------------------------------------

Skin contact Causes skin irritation.
Eye contact Causes serious eye damage.
Ingestion May cause discomfort if swallowed.

Symptoms related to the physical, chemical and toxicological characteristics Causes serious eye damage. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Permanent eye damage including blindness could result. Skin irritation. May cause redness and pain.

Information on toxicological effects

Acute toxicity Not expected to be acutely toxic.

Components	Species	Test Results
2,2,4-Trimethylpentane-1,3-diol monoisobutyrate (CAS 25265-77-4)		

Acute

Oral

LD50 Rat 3200 - 6400 mg/kg

Titanium dioxide (CAS 13463-67-7)

Acute

Oral

LD50 Rat > 5000 mg/kg

Skin corrosion/irritation Causes skin irritation.

Serious eye damage/eye irritation Causes serious eye damage.

Respiratory or skin sensitization

Respiratory sensitization Not a respiratory sensitizer.

Skin sensitization This product is not expected to cause skin sensitization.

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity Due to the form of the product, exposure to the potentially carcinogenic components is not expected.

IARC Monographs. Overall Evaluation of Carcinogenicity

Polyvinyl chloride (CAS 9002-86-2) 3 Not classifiable as to carcinogenicity to humans.
Titanium dioxide (CAS 13463-67-7) 2B Possibly carcinogenic to humans.

NTP Report on Carcinogens

Not listed.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Polyvinyl chloride (CAS 9002-86-2) Cancer

Reproductive toxicity This product is not expected to cause reproductive or developmental effects.

Specific target organ toxicity - single exposure Not classified.

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard Not an aspiration hazard.

Chronic effects Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Components	Species	Test Results
Titanium dioxide (CAS 13463-67-7)		
Aquatic		
<i>Acute</i>		
Crustacea	EC50 Daphnia magna	> 100 mg/l, 48 Hours
Fish	LL50 Oryzias latipes	> 100 mg/l, 96 Hours

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential	No data available on bioaccumulation.
Mobility in soil	No data available for this product.
Other adverse effects	No data available.

13. Disposal considerations

Disposal instructions	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Incinerate the material under controlled conditions in an approved incinerator. Dispose of contents/container in accordance with local/regional/national/international regulations.
Local disposal regulations	Dispose in accordance with all applicable regulations.
Hazardous waste code	The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not established.

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Polyvinyl chloride (CAS 9002-86-2)	Cancer
	Central nervous system
	Liver
	Blood
	Flammability

Toxic Substances Control Act (TSCA) All components of the mixture on the TSCA 8(b) inventory are designated "active".

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes

Classified hazard categories Skin corrosion or irritation
Serious eye damage or eye irritation

SARA 313 (TRI reporting)
Not regulated.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.**US state regulations****US. Massachusetts RTK - Substance List**

Calcium carbonate (CAS 1317-65-3)

Calcium oxide (CAS 1305-78-8)

Titanium dioxide (CAS 13463-67-7)

US. New Jersey Worker and Community Right-to-Know Act

Calcium carbonate (CAS 1317-65-3)

Calcium oxide (CAS 1305-78-8)

Polyvinyl chloride (CAS 9002-86-2)

Titanium dioxide (CAS 13463-67-7)

US. Pennsylvania Worker and Community Right-to-Know Law

Calcium carbonate (CAS 1317-65-3)

Calcium oxide (CAS 1305-78-8)

Titanium dioxide (CAS 13463-67-7)

US. Rhode Island RTK

Calcium carbonate (CAS 1317-65-3)

Calcium oxide (CAS 1305-78-8)

Titanium dioxide (CAS 13463-67-7)

California Proposition 65**WARNING:** This product can expose you to chemicals including Diisononyl phthalate, which are known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.**California Proposition 65 - CRT: Listed date/Carcinogenic substance**

Diisononyl phthalate (CAS 28553-12-0)

Listed: December 20, 2013

Titanium dioxide (CAS 13463-67-7)

Listed: September 2, 2011

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

Titanium dioxide (CAS 13463-67-7)

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Industrial Chemicals (AICIS)	Yes
Canada	Domestic Substances List (DSL)	No
Canada	Non-Domestic Substances List (NDSL)	Yes
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	Yes
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision**Issue date** 30-November-2015**Revision date** 23-September-2021**Version #** E**Further information** D - Face Shield, Gloves, Apron

HMIS® ratings

Health: 3
Flammability: 1
Physical hazard: 0
Personal protection: D

NFPA ratings**Disclaimer**

ABB Installation Products Inc. cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available.