

Technical Information Bulletin Fluorescent

E-Lume™

ORDERING INFORMATION

Order code: 59190
 Description: F21T5/35K/8/PS/G5/ELUME
 UPC: 69549591905
 Case quantity: 25




Nominal length : 34 in. (864 mm) Dia. : 5/8 in. (16 mm)

PERFORMANCE DATA


Shape: T5
 Base: G5 (Min Bipin)
 Starting method: Program Start (PS)
 Wattage (W): 21
 Colour temperature (K): 3 500
 CRI: 85
 Rated life on PS/PRS¹ ballast:
 Based on a 3 hour start 24 000
 Based on a 12 hour start 30 000
 Initial lumens (lm): 2 100
 Mean lumens (lm): 2 000
 Nominal efficiency (lm/W): 100
 TCLP compliant: Yes
 Phosphor composition: Triphosphor
 Nominal lamp operating frequency (Hz): 60
² Minimum starting temperature (°C): -10

DIMENSIONS



A Max	B Min / B Max	C Max
Base face to base face	Base face to end of opposite face pin	End of base pin to the end of opposite end
33.42 in.	33.61 in./33.70 in.	33.98 in.
849.0 mm	853.7 mm/856.1 mm	863.2 mm

SPECTRAL DISTRIBUTION



¹ The life rating indicated is based on 3 hour burning cycles under specified conditions and with ballast meeting ANSI specifications.

² The minimum starting temperature is a function of the ballast. The minimum starting temperature is based on a STANDARD brand T5 E-Lume ballast.

