


ORDERING INFORMATION


Order code: 59591
 Description: E1528-120-SL GLB
 UPC: 69549595910

SPECIFICATIONS

| | |
|------------------------|---------------|
| Ballast type: | Electronic |
| Starting method: | Instant Start |
| Lamp connection: | Series |
| Input voltage (V): | 120 V |
| Input frequency (Hz): | 50/60 HZ |
| Max. case temperature: | 70 °C |
| Type: | 1 Outdoor |
| Sound rating: | A |
| ICES-005 Compliant: | Class A |



WIRING DIAGRAM




WIRING NOTE:

- 1) DO NOT JOIN THE 2 YELLOW WIRES OR THE 2 RED WIRES TOGETHER. EACH WIRE MUST GO TO THE APPROPRIATE SOCKET PIN INDIVIDUALLY
- 2) GREEN WIRE IS FOR EMI FILTER GROUND. DO NOT CONNECT FOR HI POT TESTING

BALLAST DIMENSIONS

| | |
|---|-----------------|
| A | 2.00" (5.08 cm) |
| B | 1.50" (3.91 cm) |
| C | 1.00" (2.54 cm) |
| D | 0.93" (2.36 cm) |
| E | 2.88" (42 cm) |
| F | 2.50" (6.35 cm) |



WARRANTY:

Ballast warranty of 5 years for electronic ballast 70-75 °C. Ballast warranty of 3 years for electronic ballast 90 °C. For more information visit our website.

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.
 December 18, 2017

ORDERING INFORMATION

Order code: 59591
 Description: E1528-120-SL GLB
 UPC: 69549595910

| Lamp Type: | Number of lamps | Rated lamp watts | Min. start temp. (°F / °C) | Input current (A) | Input power (ANSI watts) | Ballast factor | Max THD (%) | Power factor | Max. lamp current crest factor | B.E.F. |
|------------------|-----------------|------------------|----------------------------|-------------------|--------------------------|----------------|-------------|--------------|--------------------------------|--------|
| 120 VOLTS | | | | | | | | | | |
| PL26/TTT (26W) | 1 | 26 | 14/-10 | 0.17 | 18 | 0.83 | 6 | 0.91 | 2.0 | 4.50 |
| PL18/TTT (18W) | 1 | 18 | 14/-10 | 0.15 | 16 | 0.86 | 6 | 0.90 | 2.0 | 5.27 |
| PL13/TTT (13W) | 1 | 13 | 14/-10 | 0.10 | 14 | 1.09 | 6 | 0.87 | 2.0 | 7.59 |
| PL10/TTT (10W) | 1 | 10 | 14/-10 | 0.12 | 12 | 1.00 | 6 | 0.88 | 2.0 | 8.24 |
| PL24/TTL (24W) | 1 | 24 | 14/-10 | 0.14 | 15 | 0.60 | 6 | 0.90 | 2.0 | 4.03 |
| PL18/TTL (18W) | 1 | 18 | 14/-10 | 0.10 | 11 | 0.56 | 6 | 0.89 | 2.0 | 5.19 |
| PL13/TT (13W) | 1 | 13 | 14/-10 | 0.10 | 10 | 0.71 | 6 | 0.87 | 2.0 | 6.94 |
| PL11/TT (11W) | 1 | 11 | 14/-10 | 0.13 | 14 | 1.20 | 6 | 0.90 | 2.0 | 8.44 |
| PL9/TT (9W) | 1 | 9 | 14/-10 | 0.09 | 9 | 1.06 | 6 | 0.88 | 2.0 | 11.41 |
| PL7/TT (7W) | 1 | 7 | 14/-10 | 0.08 | 8 | 1.03 | 6 | 0.88 | 2.0 | 12.97 |
| PL5/TT (5W) | 1 | 5 | 14/-10 | 0.06 | 7 | 0.95 | 6 | 0.87 | 2.0 | 14.44 |
| F28T5 (28W) | 1 | 28 | 14/-10 | 0.21 | 24 | 1.06 | 6 | 0.92 | 2.0 | 4.49 |
| F21T5 (21W) | 1 | 21 | 14/-10 | 0.18 | 19 | 1.06 | 6 | 0.91 | 2.0 | 5.45 |
| F14T5 (14W) | 1 | 14 | 14/-10 | 0.14 | 15 | 1.06 | 6 | 0.90 | 2.0 | 7.16 |
| F13T5 (13W) | 1 | 13 | 14/-10 | 14.80 | 15 | 1.09 | 6 | 0.90 | 2.0 | 7.36 |
| F8T5 (8W) | 1 | 8 | 14/-10 | 0.07 | 7 | 0.79 | 6 | 0.88 | 2.0 | 11.52 |
| F6T5 (6W) | 1 | 6 | 14/-10 | 0.07 | 8 | 1.13 | 6 | 0.88 | 2.0 | 14.66 |
| F4T5 (4W) | 1 | 4 | 14/-10 | 0.06 | 6 | 1.06 | 6 | 0.88 | 2.0 | 18.24 |
| F25T8 (25W) | 1 | 25 | 14/-10 | 0.17 | 19 | 0.97 | 6 | 0.91 | 2.0 | 5.13 |
| F18T8 (18W) | 1 | 18 | 14/-10 | 0.11 | 11 | 0.67 | 6 | 0.90 | 2.0 | 5.88 |
| F17T8 (17W) | 1 | 17 | 14/-10 | 0.12 | 13 | 0.97 | 6 | 0.90 | 2.0 | 7.35 |
| F16T8 (16W) | 1 | 16 | 14/-10 | 0.11 | 11 | 0.84 | 6 | 0.89 | 2.0 | 7.43 |
| F15T8 (15W) | 1 | 15 | 14/-10 | 0.10 | 11 | 0.84 | 6 | 0.89 | 2.0 | 7.92 |
| F14T8 (14W) | 1 | 14 | 14/-10 | 0.09 | 10 | 0.84 | 6 | 0.89 | 2.0 | 8.40 |
| F13T8 (13W) | 1 | 13 | 14/-10 | 0.08 | 8 | 0.84 | 6 | 0.88 | 2.0 | 10.37 |
| F15T12 (15W) | 1 | 15 | 14/-10 | 0.10 | 11 | 0.79 | 6 | 0.90 | 2.0 | 7.10 |
| F14T12 (14W) | 1 | 14 | 14/-10 | 0.10 | 11 | 0.79 | 6 | 0.90 | 2.0 | 7.10 |
| 2D (28W) | 1 | 28 | 14/-10 | 0.18 | 19 | 0.56 | 6 | 0.91 | 2.0 | 2.90 |
| 2D (21W) | 1 | 21 | 14/-10 | 0.15 | 17 | 0.69 | 6 | 0.91 | 2.0 | 4.16 |
| 2D (16W) | 1 | 16 | 14/-10 | 0.15 | 16 | 0.92 | 6 | 0.90 | 2.0 | 5.83 |
| 2D (10W) | 1 | 10 | 14/-10 | 0.12 | 12 | 1.00 | 6 | 0.88 | 2.0 | 8.24 |

WARRANTY:

Ballast warranty of 5 years for electronic ballast 70-75 °C. Ballast warranty of 3 years for electronic ballast 90 °C.
 For more information visit our website.

Data is based upon tests performed in a controlled environment and representative of relative performance.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

December 18, 2017