


## HEAT SHRINKABLE BOOTS

### MATERIAL:

Thermally stabilized, modified polyolefin provided with factory internally applied adhesive sealant.

### COLOR:

Black



Cat. No.	No. of Legs	A		B		L Nom.	Wire Range AWG / MCM
		Expanded ID min.	Recovered ID max.	Expanded ID min.	Recovered ID max.		
HSB200-75-2	2	1.97	0.90	0.83	0.30	4.69	#3 – 300
HSB120-50-3	3	1.50	0.50	0.65	0.16	4.47	#8 – 3/0
HSB170-82-3	3	2.20	0.89	1.20	0.35	7.09	#1 – 600
HSB240-112-3	3	2.83	1.38	1.46	0.69	7.01	300 – 1000
HSB125-50-4	4	1.38	0.47	0.59	0.12	3.74	#12 – 2/0
HSB175-82-4	4	2.36	0.90	1.18	0.25	7.95	#4 – 600
HSB265-120-4	4	3.10	1.40	1.50	0.49	9.45	3/0 – 1000
HSB430-157-3	3	4.33	1.38	1.57	0.69	7.01	300 – 1000
HSB350-138-3	3	3.54	1.34	1.38	0.55	7.87	4/0 – 1000
HSB490-200-3	3	4.92	2.32	2.00	1.00	11.14	750 – 1000
HSB520-135-4	4	5.25	3.00	1.35	0.55	10.02	4/0 – 1000
HSB120-50-2	2	1.18	0.37	0.59	0.16	3.70	#10-2/0

### INSTALLATION INSTRUCTIONS:

1. Insert leads, conductors or smallest parts of system through legs of boot.
2. Slide boot over cable section to be sealed. Press multi-legged boots firmly into the crotch of leads, conductors, etc.
3. Shrink boot by applying heat using hot air blower WT1400 (heat gun), SIT1 (torch) or other heat source. Boots start to shrink at approximately 250-275°F.
4. Start from the center of the boot to avoid trapping air under boot, then shrink the legs starting from the center of boot working toward the end of the legs. Shrink main end first. As heat is applied, move the heat source back and forth as well as around the boot.
5. When the boot assumes the configuration of the cable and excess sealant appears at the ends, discontinue heating as the shrink process is complete.

**WARRANTY:** Thomas & Betts sells this product with the understanding that the user will perform all necessary tests to determine the suitability of this product for the user's intended application. Thomas & Betts warrants that this product will be free from defects in materials and workmanship for a period of two (2) years following the date of purchase. Upon prompt notification of any warranted defect, Thomas & Betts will, at its option, repair or replace the defective product or refund the purchase price. Proof of purchase is required. Misuse or unauthorized modification of the product voids all warranties.

**Limitations and Exclusions:** THE ABOVE WARRANTY IS THE SOLE WARRANTY CONCERNING THIS PRODUCT, AND IS IN LIEU OF ALL OTHER WARRANTIES EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, WHICH ARE SPECIFICALLY DISCLAIMED. LIABILITY FOR BREACH OF THE ABOVE WARRANTY IS LIMITED TO COST OF REPAIR OR REPLACEMENT OF THE PRODUCT, AND UNDER NO CIRCUMSTANCES WILL THOMAS & BETTS BE LIABLE FOR ANY INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES.

Thomas & Betts Corporation  
 Memphis, Tennessee  
 www.tnb.com