




# Ty-Rap®



LOOP TIE THRU HOLE IN FRAME,  
AROUND ITEMS TO BE CLAMPED AND THRU HEAD. TIGHTEN

INSTALLED



## NOTES:

1. MATERIAL: NYLON 6,6, BLACK
2. FLAMMABILITY: UL94V-2
3. OPERATING TEMPERATURE RANGE: -40°F [-40°C] TO 185°F [85°C]
4. TENSILE RATING: 65 LBS [289 N]
5. INSTALLATION TOOL/SETTING: ERG50/6-8

CATALOG NUMBER	L LENGTH	MAXIMUM BUNDLE DIAMETER	MOUNTING HOLE SIZE
TY541M	9.600 [243,84]	2.370 [60,2]	.320-.680 [8.13] - [17.27]
650-41600	10.250 [260,35]	2.500 [63,5]	
696-41848	12.500 [317,5]	3.000 [76,2]	
GENERAL NOTES		<div>Thomas &amp; Betts</div> <div>www.tnb.com</div>	
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY. 2. DIMENSIONS IN BRACKETS [ ] ARE IN METRIC UNITS.			
REVISIONS		DESCRIPTION:	
- SEE ERN ( **** ) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: ****		UNIVERSAL CLAMP	
ORIGINAL PROJECT NO / ( ERN NO )		SHEET NO:	REV. NO:
FM401183 / ( 2011456 )		1 OF 1	-
		DRAWING NO:	
		WSD-000559	

**Thomas & Betts**  
www.tnb.com