

Technical Information Bulletin

LED Linear Tubes



Date: _____ Name of distributor: _____
In hands date of project: _____ Client #: _____
Project name/Number: _____ Name of end user: _____

ORDERING INFORMATION

Order code: 65505
Description: LED/T8/S4/9W/835/24/STD/SMX
UPC: 69549655058
Case quantity: 25
DLC Unique ID: PJF8RR91



Nominal length : 24 in. (610 mm) Dia. : 1 1/2 in. (26 mm)

PHYSICAL DATA

Shape: T8
Base: G13
Material: PET Polyethylene Terephthalate

PERFORMANCE DATA

Install method: Instant, Rapid & Program Start
Volts (VAC): 120 V-277 V / 347 V
Colour temperature (K)¹: 3 500
Life L70 (hrs): 50 000
CRI: >80
Beam angle (°) : >240
Total Harmonic Distortion (%): <20
Operating temperature range: -20°C to 45°F (-4°C to 113°F)

¹ Typical colour temperature range: +/- 5 %

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %

Order code	Average System Watts (W)			Initial Lumens (lm) ²		
	LBF	NBF	HBF	LBF	NBF	HBF
65505	10	12	16	1 000	1 200	1 550



DAMP



NO MERCURY



RoHS COMPLIANT



5 YEARS WARRANTY



UL US



ETL

Intertek
CONFORMS TO NSF/ANSI 2

Please refer to the ballast compatibility list to confirm lamp compatibility with the existing luminaire.

ADDITIONAL INFORMATION

THIS LAMP OPERATES ON INSTANT START, RAPID START AND MANY PROGRAM START ELECTRONIC BALLASTS.

Direct replacement for 32 watts lamps only. Risk of fire. Do not install this lamp in a pre-heat luminaire. Risk of electric shock – for use in damp locations.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____

Company: _____

Signature: _____

Date: _____

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.
Data is based upon tests performed in a controlled environment and representative of relative performance.
Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.