

Technical Information Bulletin

LED Linear



Date: _____ Name of distributor: _____
 In hands date of project: _____ Client #: _____
 Project name/Number: _____ Name of end user: _____

ORDERING INFORMATION

Order code: 66995
Description: T5/13W/835/46/BYP/120-277/ND/STD
UPC: 69549669956
Case quantity: 25
DLC Unique ID: PLR9H2UZK3LE



Nominal length : 46 in. (1 168 mm) Dia. : 19/16 in. (21 mm)

PHYSICAL DATA

Shape: T5
Base: G5
Material: Glass

PERFORMANCE DATA

Install method: Ballast bypass
Watts (W): 13
Volts (VAC): 120-277
Colour temperature (K)¹: 3 500
Initial Lumens (lm)²: 1 600
Initial lumens per watt (lm/W): 123
Life L70 (hrs): 50 000
CRI: 82
Operating temperature range: -25°C to 45°F (-13°C to 113°F)

¹ Typical colour temperature range: +/- 5 %
² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %



*This product complies with UL1598C Standard for LED luminaire Retrofit kits. Not suitable for hazardous location.

ADDITIONAL INFORMATION

ONLY FOR BALLAST BYPASS INSTALLATION IN 120-277V APPLICATIONS. NOT FOR USE IN 347V DIRECT LINE VOLTAGE APPLICATIONS.
 Direct replacement for 28 watts lamps only.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____ Date: _____

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

