

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

LED HIGH INTENSITY LAMP

CCT and Power Selectable

ORDERING INFORMATION

Order code: 69127
Model number: CRN/PS100W/2CCT/BYP/120-277/EX39/STD
UPC: 069549024762
Case quantity: 6
DLC Unique ID: S-FCHG5Z

PHYSICAL DATA

Base: EX39
Type: 360° High Intensity

PERFORMANCE DATA


Watts (W): 70/100
Traditional equivalent (W) 400
Volts (V AC): 120-277
Color temperature (K)¹: 4 000/5 000
Lumen output (lm)²: 8 400/11 746
Efficacy (lm/W): 120/118
CRI: 80
Life L70 (h)³: 50 000
Beam angle (°): 360
Power factor: >0.9
Frequency (Hz): 50/60
Operating temp. range: - 40 °C / - 40 °F to 45 °C / 113 °F
Installation: Ballast Bypass

¹ Typical color temperature range: +/- 5 %.
² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.
³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.

LUMEN SPECIFICATION TABLE

Order code	Description	Watts (W)	4 000/5 000 K	
			Lumen output (lm)	Efficacy (lm/W)
69127	CRN/PS100W/2CCT/BYP/120-277/EX39/STD	70	8 400 lm	120 lm/W
		100	11 746 lm	118 lm/W

DIMENSIONS



ICES 005



enclosed fixture



This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.