

# Technical Information Bulletin

## DESIGN LED Lamps




Date: \_\_\_\_\_ Name of distributor: \_\_\_\_\_  
 In hands date of project: \_\_\_\_\_ Client #: \_\_\_\_\_  
 Project name/Number: \_\_\_\_\_ Name of end user: \_\_\_\_\_

### ORDERING INFORMATION

Order code: 67607  
 Description: P20/7W/30K/45/DESIGN/STD  
 UPC: 69549676077  
 Case quantity: 10/60

### PHYSICAL DATA

Type: PAR20  
 Base: E26  
 Material: Glass  
 Lens type: Clear



MOL: 3 11/32" (85 mm) Dia.: 2 15/32" (63 mm)

### PERFORMANCE DATA

Watts (W): 7  
 Lamp volts (VAC): 120  
 Colour temperature (K)<sup>1</sup>: 3 000  
 Life L70 (hrs): 25 000  
 Lumens (lm)<sup>2</sup>: 500  
 Lumens per watt (lm/W): 71  
 Traditional equivalent (W): 50  
 CRI: 80  
 Beam angle (°): 45  
 CBCP (cd): 520  
 THD (%): 55  
 Frequency (Hz): 60  
 Power factor: 0.88  
 Operating temperature range: -20°C to 45°C (-4°F to 113°F)

<sup>1</sup> Typical colour temperature range: +/- 5 %  
<sup>2</sup> Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %

### COMPATIBLE DIMMERS

|         |  |
|---------|--|
| Legrand | RH703PTUTC   |
| Cooper  | AAL06, SLC03P  |
| Leviton | 6615, IPL06, 6674, DSL06-1LZ, IPE04-1LZ, DDMX1                             |
| Lutron  | RRD-6NA, DVCL-153P, DVCL-253P, AYCL-253P, DVRP-253P, SELV-300P, MACL-153P, |

### CAUTIONS

- Not for use in totally enclosed luminaires.



| Qty | Description | Price |
|-----|-------------|-------|
|     |             |       |

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_  
 Company: \_\_\_\_\_  
 Signature: \_\_\_\_\_ Date: \_\_\_\_\_

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications. Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.