

roject:		Type:	
Drawn by:	Catalogue #:	Date:	

Individual Spec Sheet

L2STN

LED STRIP WITH LENS

ORDERING INFORMATION

Order code: 68125

Model number: L2STN-48LS4-Q/40K UPC: 069549014527

Case quantity:

DLC unique ID: PL6K7JWTAC1M

PHYSICAL DATA

Length: 47 3/8" (1 202 mm) Lens material: Frosted PMMA

Housing material: 24 gauge white powder painted steel

Mounting: Surface, suspended or row mounted (V-Hooks included in the box)

PERFORMANCE DATA

Watts (W): 40 Volts (VAC): 120-347 Color temperature (K)1: 4 000 Lumen output (Im)2: 5 280 Efficiency (Im/W): 132 CRI: +08 Life L70 (h)3: 162 000 Tested LM-80 (h)3: 9 000 Dimming: 0-10V Power factor: 0.90 THD (%): 10 Frequency (Hz): 50/60 Surge protection (kV): 2.5 Input current (A): 0.115-0.333

-20°C to 50°C (-4°F to 122°F) Operating temp. range:

¹ Typical colour temperature range: +/- 5 %.

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.
³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.

COMPATIBLE ACCESSORIES

Order code	Туре
68676	Suspension kit - 2 chains (1 m)
68677	Continuous row mounting connector
68679 Replacement lens 48"	
68622	Wireguard kit 48"

COMPATIBLE DIMMERS

branu	Model
LEVITON	ILLUMATECH IP710-LFZ
LUTRON	DIVADVSTV
LUTRON	Maestro MS-Z101
LUTRON	Nova T NTSTV
PHILIPS	Sunrise SR1200ZTUNV

This lighting equipment meets requirements of ICES-005 issue 5 for class A products.

Data is based upon tests performed in a controlled environment.

Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

Dimming range: 10%-100%

NOTE: This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instalaces, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Starpor recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation. Some dimmers may require more than one product for stable operation. The maximum number of products is determined by the dimmer wattage rating with LEDs. Be careful, these dimmers have different ratings depending on the product type. Again, refer to the dimmer installation instructions.

























Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at www.designlights.org/search.





DIMENSIONS








PHOTOMETRIC DATA¹

68125 • L2STN-48LS4-Q/40K • 5 278.9 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 095.3	20.7
0-40	1 800.3	34.1
0-60	3 258.2	61.7
60-90	1 439.9	27.3
70-100	1 071.1	20.3
90-120	495.4	9.4
0-90	4 698.1	89
90-180	580.8	11
0-180	5 278.9	100

Illuminance at a distance

	Center beam fc		Beam	Beam width	
1.7'	488		4.5'	9.2'	
3.3'	129		8.7'	17.9'	
5.0'	56.4		13.2'	27.11	
6.7'	31.4		17.7'	36.3'	
8.3'	20.5		21.9'	45.0'	
10.0'	14.1		26.4'	54.2'	
	Vert. spread: Horiz. spread:	105.7° 139.5°			

Qty Description Price I accept the specifications of the luminaire configuration mentioned above. Name: Company: Signature: Date:

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.

¹ Complete IES files available on our website.