

Project: _

Drawn by:

_____ Catalogue #: ____

Type:

Date: _

Individual Spec Sheet

WCI-L **MINI WALL PACK**

Selectable color temperature (4 000/4 500/5 000 K) Integrated Photocell

ORDERING INFORMATION

Order code:
Model number:
UPC:
Case quantity:

68312 WCI-LS2-W/3C-BR 069549015906 10

PHYSICAL DATA

Dimensions:	5.79" x 8.58" x 3.07"
Housing Material:	Aluminum die-cast
Lens type:	Polycarbonate frosted lens
Mounting:	Surface mount to a junction box or use with surface conduit.
Photocell:	Integrated 120-277 V photocell which can easily be disabled.

PERFORMANCE DATA

Watts (W):	20	
Volts (VAC):	120-277	
Color temperature (K) ¹ :	3 CCT (4 000/4 500/5 000)	
Lumen output (lm) ² :	2 522/2 926/2 637	
Efficiency (Im/W):	127	
CRI:	80	
Finish:	Bronze	
Dimming (Yes/No):	No	
LED current (mA):	310	
Power factor:	0.94	
Frequency (Hz):	50/60	
THD (%):	13	
Operating temp. range:	-40°C to 40°C	

Typical color temperature range: +/- 5 %
Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %
Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations

SELECTABLE COLOR TEMPERATURE SWITCH



This lighting equipment complies with Canadian standard ICES-005 for use in residential applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

\$ 514.342.1199, 1.800.361.6965 • 514.807.3011 • www.standardpro.com 2233 rue de l'Aviation, Dorval, QC H9P 2X6















LED

((•))

ICES 005


fixture








DIMENSIONS



PHOTOMETRIC DATA¹

68312 • WCI-LS2-W-3C-BR at 4 000 K • 2 520.9 Im

Polar candela distribution




¹ Complete IES files available on our website.

Zonal lumen summary

8.58

Zone	Lumens	% Luminaire			
0-30	640.2	25.4%			
0-40	988.5	39.2%			
0-60	1 660.3	65.9%			
60-90	619.3	24.6%			
70-100	414.9	16.5%			
90-120	182.0	7.2%			
0-90	2 279.6	90.4%			
90-180	241.3	9.6%			
0-180	2 520.9	100%			

Illuminance at a distance



Qty	Description		Price		
I accept the specifications	of the luminaire configuration mentioned	d above.			
Name:					
Company:					
Signature:			Date:		
Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.					

