



B2D12 Copper Braid, 12" Long, 2 Braids, 2 Holes 2 Ferrules, 7/16" Stud, 1-1/4" Stud Hole Spacing, 380 amps Indoor, 455 amps Outdoor

By Burndy
Catalog # B2D12



Copper Braid, 12" Long, 2 Braids, 2 Holes 2 Ferrules, 7/16" Stud, 1-1/4" Stud Hole Spacing, 380 amps Indoor, 455 amps Outdoor.

Application

Flexible copper braid jumpers designed to take up linear expansion and contraction, compensate for misalignment and absorb vibratory movement of electrical equipment and devices

General

Connector Type	Braid
EU RoHS Indicator	Yes
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
Sub Brand	BRAID
Type	B, Flexible
UPC	781810807002
UPC 12 Digit	7818108070022

Dimensions

Dimension - D inch	2.5
Dimension - Hole Size inch	0.44
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Dimension - N inch	0.62
Dimension - Pad Width inch	0.94
Length	12 in

Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - B2D12_MODEL-STEP](#)
[3D Models - B2D12_MODEL-IGES](#)
[3D Models - B2D12_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SE210201-02_DI](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-B2D12-SPEC-EN | REV 8/2023