



radiant Collection  
radiant® LED/CFL Dimmer, Two Wire, White  
Part No. RHL373PW



Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant® Collection is optimized for use with LED 2-wire bulbs and fixtures compliant with the SSL 7A standard for energy efficiency. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Designed to save energy, this dimmer is for use with LED bulbs and fixtures also designed to the SSL 7A standard for efficiency. For use in both single-pole and 3-way applications.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Constant memory features returns lights to their previous level after a power failure or outage.

No derating\* required for 2-gang applications. \*Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

|                    |                |                    |                           |
|--------------------|----------------|--------------------|---------------------------|
| Product Line       | Pass & Seymour | Color              | White                     |
| Finish             | Matte          | UPC Number         | 785007161939              |
| Country Of Origin  | China          | Features           | Locator Light             |
| Switch Type        | Paddle, Slider | Number of Switches | 1                         |
| Application Sector | Residential    | Warranty Type      | Limited Lifetime Warranty |
| Type               | Dimmer         |                    |                           |

---

## Dimensions

---

|                   |         |                  |        |
|-------------------|---------|------------------|--------|
| Product Width US  | 1.29 in | Product Depth US | 1.0 in |
| Product Height US | 3.18 in |                  |        |

---

## Listing Agencies / 3rd Party Agencies

---

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

## Technical Information

---

|                    |                                 |                 |                    |
|--------------------|---------------------------------|-----------------|--------------------|
| Number of Gangs    | 1                               | Amperage        | 2.1 A              |
| Bulb Compatibility | LED, CFL, Incandescent, Halogen | Number of Poles | Single Pole, 3-Way |
| Wattage            | 300 W                           | Mounting Type   | Box                |
| Voltage            | 0 V, 120 V                      |                 |                    |

---