

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

FLB

LED FLOOD LIGHT GEN 4

Quick and Easy Mounting accessories (Sold separately)

ORDERING INFORMATION

Order code: 68550
Model number: FLBS-L2AM-I-4K-BR
UPC: 069549017252
Case quantity: 1
DLC unique ID: P5B41N8Y

PHYSICAL DATA

Dimensions: 12 1/4" x 12 5/8" x 2 5/8" (312 mm x 320 mm x 65 mm)
Lens material: Polycarbonate
Housing material: Aluminum die-cast
Finish: Bronze

PERFORMANCE DATA

Watts (W): 151
Volts (V): 347-480
Color temperature (K): 4 000
Lumen output (lm): 20 649
Efficiency (lm/W): 137
CRI: 70
NEMA Type (HxV): 7x6
Life L70 (h): >60 000
Dimming (Yes/No): Yes
Power factor: 0.93
THD (%): 10.49
Surge protection (kV): 10
LED current (mA): 0.8
Operating temp. range: -40 °C to 40 °C

¹ Typical colour temperature range: +/- 5 %

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %

³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations

COMPATIBLE ACCESSORIES

Order code	Description
68569	Bronze Yoke for FLBS-FLBM
68571	Bronze Slipfitter
68572	Bronze square/round Pole arm
68573	Bronze Trunnion
68574	Bronze Wall/Pole mount adapter ¹
68717	Bronze Slipfitter and Wall mount adapter

¹ Wall mount adapter used conjunctively with Slipfitter.

This lighting equipment complies with Canadian standard ICES-005 for use in commercial applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



quick
ship



LED
fixture



dimmable
fixture



wet
location



IK08




ICES
005



Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at www.designlights.org/search.


DIMENSIONS



PHOTOMETRIC DATA¹

68550 • FLBS-L2AM-I-40K-BR • 20 617 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	6 828.2	33.1%
0-40	11 150.5	54.1%
0-60	18 378.7	89.1%
60-90	2 238.2	10.9%
70-100	551.5	2.7%
90-120	0	0%
0-90	20 617	100%
90-180	0	0%
0-180	20 617	100%

Illuminance at a distance

Center beam fc	Beam width
17'	29.9 fc
34'	7.47 fc
51'	3.32 fc
68'	1.87 fc
85'	1.19 fc
102'	0.83 fc

Beam width	Beam height
33.5'	51'
67.0'	102'
100.4'	153'
133.9'	204'
167.4'	254'
200.9'	305.9'

■ Vert. spread: 89.1°
■ Horiz. spread: 112.6°

¹ Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.