

Project:		Type:
Drawn by:	Catalogue #:	Date:

# Individual Spec Sheet

# **FLB**

# **LED FLOOD LIGHT GEN 4**

Quick and Easy Mounting accessories (Sold separately) Selectable color temperature Power selectable

## **ORDERING INFORMATION**

Order code: 68568

**Model number:** FLBX-PS300M-W-3C-BR **UPC:** 069549017436

Case quantity:

**DLC unique ID:** PLW6WKGVMN0Q

#### PHYSICAL DATA

**Dimensions:** 22 3/8" x 12 5/8" x 2 3/4" (569 mm x 320 mm x 70 mm)

**Lens material:** Polycarbonate **Housing material:** Aluminum die-cast

Finish: Bronze

#### PERFORMANCE DATA

**Watts (W):** 150/200/240/300 **Volts (V):** 120-277

 Color temperature (K)¹:
 3 000/4 000/5 000

 Lumen output (Im)²:
 22 400 - 38 000

 Efficiency (Im/W):
 123 - 159

CRI: 70 **NEMA Type (HxV)** 7x7 Life L70 (h)3: >60 000 Dimming (Yes/No): Yes Power factor: 0.99 THD (%): 4.26 Surge protection (kV): 10 LED current (mA): 2.64-1.18 Operating temp. range: -40 °C to 40 °C

# **COMPATIBLE ACCESSORIES**

	Order code	Description
	68570	Bronze Yoke for FLBL-FLBX
	68571	Bronze Slipfitter
68572 Bro		Bronze square/round Pole arm
	68573	Bronze Trunnion
	68574	Bronze Wall/Pole mount adapter <sup>1</sup>
	68717	Bronze Slipftter and Wall mount adapter

Wall mount adapter used conjunctively with Slipfitter.

This lightling equipment complies with Canadian standard ICES-005 for use in commercial applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.







selectable





quick









ship















Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at www.designlights.org/search.


 $<sup>^{\</sup>rm 1}$  Typical colour temperature range: +/- 5 %

<sup>&</sup>lt;sup>2</sup> Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %

<sup>&</sup>lt;sup>3</sup> Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations




## **DIMENSIONS**



# PHOTOMETRIC DATA<sup>1</sup>

# 68568 • FLBX-PS300M-W-3C-BR • 37 441.4 lm

#### Polar candela distribution



<sup>&</sup>lt;sup>1</sup> Complete IES files available on our website.

### **Zonal lumen summary**

Zone	Lumens	% Fixture	
0-30	12 139.0	32.4%	
0-40	19 139.7	51.1%	
0-60	30 849.2	82.4%	
60-90	5 995.1	16%	
70-100	2 438.5	6.5%	
90-120	156.7	0.4%	
0-90	36 844.3	98.4%	
90-180	597.0	1.6%	
0-180	37 441.4	100%	

#### Illuminance at a distance

Center beam fc			Beam width	
17'	53.8 fc		29.7'	46.4'
34'	13.4 fc		59.3'	92.8'
51'	5.98 fc		89.0'	139.1'
68'	3.36 fc		118.7'	185.5'
85'	2.15 fc		148.4'	231.9'
102'	1.49 fc		178.0'	278.3'
	Vert. spread: Horiz. spread:	82.2° 107.5°		

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.

Oty Description Price

I accept the specifications of the luminaire configuration mentioned above.

Name:
Company:
Signature:
Date: