


Graesslin Electronic Timer Control - 24-Hour or 7-Day 120-277V Electronic Surface/DIN Rail Mount Module, 15A, 14 Setpoint Programs, SPDT

Item FM1D14A-AV



PRODUCT DESCRIPTION

The FM1D14 Series is a great value electronic time-based control solution for ventilating, heating, cooling, lighting or other electrical loads in commercial and industrial applications. These one-channel time switches are programmable for 24-hour or 7-day schedules. The FM1D14 Series is intended for either panel, surface, flush or DIN rail mounting. Flush and surface/DIN rail (A & E models) are completely enclosed in a plastic housing and include a terminal cover, dust cover and subbase for installation and hard wiring.

FEATURES

- ▶ 24-Hour or 7-day applications
- ▶ 14 Setpoint programs
- ▶ Easy to program
- ▶ Manual override with status indication
- ▶ Self-recharging battery with backup protection up to 2500-hours
- ▶ LCD display
- ▶ 5 Preset adjustable block programs
- ▶ A & E models come with clear dust cover

APPLICATIONS

- ▶ Refrigeration Merchandiser
- ▶ Air Movement & Ventilation
- ▶ Aeration
- ▶ Septic Treatment
- ▶ Generator Exercising

TECHNICAL DATA

General	
Model Number	FM1D14A-AV
Description	24-Hour or 7-Day 120-277V Electronic Surface/DIN Rail Mount Module, 15A, 14 Setpoint Programs, SPDT
UPC Code	078275143166
Brand	Domestic Intermatic
Country of Origin (Intermatic)	CHINA
Warranty Period	1-Year limited
Expected Lifetime (Operations)	6000
Application Compatibilities	LED
Control Specifications	
Minimum ON/OFF Times	1 min
Setpoint Program Count	14
ON/OFF Operations	98
Operation Mode	24 hour; 7 day
Daylight Savings Adjustment	Manual
Backup Type	Battery
Backup Protection Time	2500 Hours
Battery Service Type	Self-recharging
Mechanism Type	Digital/Electrical

Has Manual Override Status Indication	Yes
---------------------------------------	-----

Mechanical Specifications

Mounting Options	Surface; DIN Rail
------------------	-------------------

Dimensions

Product Dimensions (H x W x D) in	4 x 2.83 x 2.06 in
Cut-Out Width (In)	2 5/8
Cut-Out Width (mm)	66
Cut-Out Height (in)	2 5/8
Cut-Out Height (mm)	66
Wire Size Min	#24 AWG
Wire Size Max	#10 AWG

Electrical Specifications

Maximum Power Consumption (VA)	4
Voltage Selection Type	Voltage Specific
Wiring Option	Screw terminals for #24 to #10 AWG wire (A models)
Number of Circuits	1
Switch Type	SPDT
Maximum Power Consumption (W)	1.4 W

Packaging

Shipping Weight (lbs)	0.529
Unit Carton Dimensions (H x W x L) in	3.25 x 3.25 x 4.75 in

Environmental Specifications

Operating Humidity	0-95% RH, Non-condensing
Display Operating Temperature Min (°F)	-13
Display Operating Temperature Min (°C)	-25
Temperature (operation)	-40 °F to 131 °F / (-40 °C to 55 °C)

Standards and Certifications

Other Certifications and Compatibilities	cRUUs; Title 20
RU File Number	#E10694
California Proposition 65	None
RoHS Certification	Yes

DRAWINGS AND DIAGRAMS

