

# **WIREMOLD**° Plugmold° Multioutlet Systems



Plugmold systems are available in a variety of colors and configurations.

# Plugmold® Raceway & Multioutlet Assemblies

Plugmold Multioutlet Systems are available in a wide variety of lengths and fittings and in a variety of finishes to provide versatile solutions for many applications. Plugmold options include single or alternating circuits, standard or isolated ground receptacles, GFCI protection, tamper-resistant protection, USB charging, Snapicoil harnesses of prewired receptacles, and cord-ended units.

Plugmold\* Multioutlet Systems are available in black or ivory ScuffCoat\* finish, painted white or gray enamel steel, stylish stainless steel, anodized aluminum and durable textured ivory nonmetallic. The painted steel product works with many types of decor and is paintable to integrate with most color schemes. Durable stainless steel and anodized aluminum Plugmold products are corrosion-resistant, making them ideal for labs.

PRODUCTS: PLUGMOLD 2000 SERIES, 2400 SERIES, AL2000 SERIES, NM2000 SERIES, NM2400 SERIES

#### **Features & Benefits**

- Compact, low profile appearance. Enhanced aesthetics and ideal for installations within minimal spaces.
- Multiple finishes. Choose from black or ivory ScuffCoat, white or gray painted enamel or durable stainless steel finishes.
- USB Charging. Available with dual-port USB-A modules, sharing 2.4 amps of charging capacity and single-port USB-C module with 30W Power Delivery.
- Tamper-resistance protection. Prevents the accidental insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements.
- Single, alternating circuit, and isolated ground wiring options available. Wiring options to meet virtually any job or environment requirement.
- Variety of lengths. Installed power and USB charging in multiple lengths to meet space and location requirements.

- Full range of fittings. Provide flexibility for multiple installation options or integrations with 2000 or 2400 Series Raceway systems.
- Snapicoil harnesses with different lengths and receptacle spacing. Custom solution available for large or specific use electrical installations.
- Customization available. Plugmold products can be modified to accommodate virtually any application or aesthetic need.
- Receptacle spacing options. Select the right configuration for your application.
- cULus Listed. Safety and reliability in the applications.

#### **Vertical Markets**

Commercial

Retail

Education

Hospitality

Entertainment

Healthcare



Download this product's PEP ecopasport, environmental product declaration at www.legrand.us/resources-and-downloads. This declaration conforms with ISO 14025 and 14040 and is in alignment with EN 15804.

## Compliance

cULus Listed Base & Blank Cover: File E4376 Guide RJBT

Multioutlet Assemblies: File E15191 Guide PVGT

Fittings: File E41751 Guide RJPR

Base & Blank Cover: Meets Article 386 of NEC Plugmold Strips: Meets Article 380 of NEC




# Plugmold<sup>®</sup> Multioutlet Systems

# **Plugmold Multioutlet Systems Quick Selection Guide**

FABRICATION	PROFILE	FINISH OPTIONS	LENGTHS	WIRING CONFIGS.	OUTLET O.C. SPACING	OPTIONS QUANTITY	OPTIONS
Steel	2000 Series	Black Scuffcoat Ivory Scuffcoat Gray Enamel White Enamel Stainless Steel	2' (610mm) * 3' (910mm) 5' (1.5m) 6' (1.8m) * Stainless steel only	GB, GB/USB, GBA	6" (152mm) 9" (229mm) 12" (305mm) 18" (457mm) 24" (608mm)	4 Single 5 Single 6 Single 8 Single 10 Single 12 Single 3 Duplex 4 Duplex 5 Duplex 6 Duplex	Hard-Wired models     Cord-Ended models     USB Charging models     Plug-In model     GFCI Protection     Tamper-Resistant
Steel	2400 Series	Ivory Scuffcoat	3' (910mm) 5' (1.5m) 6' (1.8m)	GB, GBA, IG	6" (152mm) 12" (305mm) 18" (457mm) 24" (608mm)	4 Single 5 Single 6 Single 10 Single 12 Single 3 Duplex 4 Duplex 5 Duplex 6 Duplex	Hard-Wired models     Cord-Ended models
Aluminum	AL2000 Series	Anodized	4' (1.2m) 5' (1.5m) 6' (1.8m)	GB, GBA, GB/USB	6" (152mm) 12" (305mm) 18" (457mm)	4 Single 5 Single 6 Single 10 Single 12 Single	Hard-Wired models     Cord-Ended models     USB Charging models     GFCI Protection     Tamper-Resistant
Nonmetallic	NM2000 Series	Ivory PVC	4' (1.2m) 5' (1.5m) 6' (1.8m)	GB, GBA, IG	9" (229mm) 12" (305mm) 15" (381mm) 18" (457mm) 30" (760mm)	2 Duplex 4 Duplex 5 Duplex 6 Duplex 8 Duplex	Hard-Wired models     Cord-Ended models
Nonmetallic	NM2400 Series	Ivory PVC	3' (910mm) 4' (1.2m) 5' (1.5m) 6' (1.8m)	GB, GBA	12" (305mm) 18" (457mm) 30" (760mm)	2 Duplex 3 Duplex 4 Duplex 5 Duplex 6 Duplex	Hard-Wired models     Cord-Ended models

# Plugmold 2000 Series Steel Multioutlet Systems Ordering Information



NOTE: Color codes: "V" for Ivory ScuffCoat<sup>--</sup> finish, "BK" for Black ScuffCoat<sup>--</sup> finish, "G" for Gray enamel finish, "WH" for white enamel finish, and "S" for stainless steel. Receptacle colors match extrusion colors except for stainless steel which has black receptacles.

 <sup>\*</sup> All 2000 Series Plugmold products include two (2) 2010B Blank End Fittings and one (1) 2001 Base Coupling unless otherwise
indicated in the product desciption.



# Plugmold<sup>®</sup> Multioutlet Systems

# Steel Plugmold<sup>®</sup> Multioutlet Systems

Steel Plugmold Multioutlet Systems are available in a wide range of lengths and finishes to provide a versatile solution for many applications. Options include versions with single or alternating circuits, standard receptacles, Snapicoil harnesses of prewired receptacles, USB charging options, GFCI protection, tamper-resistance, plug-in and cord-ended units.

Steel Plugmold Multioutlet Systems are available in black or ivory ScuffCoat finish, painted white or gray enamel finish, or stylish stainless steel. The enamel finishes work with many types of decor or can be painted to blend with most color schemes. Stainless steel Plugmold raceway is both durable and aesthetically pleasing.



Steel Plugmold systems are available in a variety of colors and configurations.


# **Plugmold 2000 Series Steel Multioutlet Systems**

Plugmold 2000 Series Wire Fill Capacities for Power							
CABLE	WIRE SIZE	o.	T	NO. OF CONDUCTORS (40% FILL)			
TYPE	THHN/THWN	Inches	(mm)	2000			
POWER WIRING	12 AWG	0.130	(3.3)	7*			
WITHOUT DEVICES	14 AWG	0.111	(2.8)	7*			
POWER WIRING	12 AWG	0.122	(3.1)	5**			
WITH DEVICES (Plugmold Series)	14 AWG	0.105	(2.7)	5**			



<sup>\*</sup>Wire capacity limited to maximum of seven conductors due to .025" (.6mm) material thickness of cover.

<sup>\*\*</sup>Including one hot, neutral, and ground wire from the receptacle.









Steel Plugmold Multioutlet Systems are ideal for use in homes, dormitories and office applications, anywhere convenient access to power or USB charging is needed.



Plugmold Multioutlet Systems

# Plugmold 2000 Series Steel Multioutlet Systems Ordering Information

# **Plugmold 2000 Series Wiring Configurations**

#### **GB Series:**

3-wire, #12 THHN (1 hot,1 neutral and 1 ground), 1 circuit; has insulated grounding conductor.




#### **GBA Series:**

4-wire, #12 THHN (2 hot, 1 neutral and 1 ground), 2 circuit; outlets wired alternately; has insulated grounding conductor.

# 

#### **GB Series:**

3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated grounding conductor.



#### **GBA Series:**

4-wire, #12 THHN (2 hot, 1 neutral and 1 ground), 2 circuit; outlets wired alternately; has insulated grounding conductor.

NOTE: SNAPICOIL REELS on custom order. Snapicoil harness is available on reels if lengths greater than 50' are needed, or if multiple lengths are required for production-type jobs. The maximum length per reel is 240' for Snapicoil with outlets 12" and 18" on centers; 500' with outlets 30" on center. Packaging includes the necessary number of lengths of base, holecut cover, wire clips, and couplings for complete installation. Price and delivery information should be obtained prior to specifying or ordering. To specify or order, add "R" to the Snapicoil number. Ex: V20GB12R. Other outlet spacings available on custom order.

Receptacles are made from high impact thermoplastic. Snapicoil packaging includes the necessary lengths of 2000B Base, 2000C Hole Cut Cover, 2000WC Wire Clips, and 2001 Couplings for complete installation.

#### Plugmold 2000 Series Steel Multioutlet Systems Ordering Information

	Plugmold 2000 Series Steel with Snapicoil Harness Ordering Information									
CATALOG NO.	LEI	NGTH	WIRING CONFIG			HOLE CUT COVER QUANTITY LENGTH			HOUSING	
	Feet	(meters)		Inches	(mm)			Feet	(m)	
20GB12*	48'	(14.63)	GB	12"	(305mm)	48 Single	8	6'	(1.8m)	Steel – Ivory, Gray
20GB18*	48'	(14.63)	GB	18"	(457mm)	32 Single	8	6'	(1.8m)	Steel - Ivory, Gray
V20GB30	50'	(15.25)	GB	30"	(760mm)	20 Single	10	5'	(1.5m)	Steel - Ivory
20GBA12*	48'	(14.63)	GBA	12"	(305mm)	48 Single	8	6'	(1.8m)	Steel – Ivory, Gray

#### **CUSTOM PLUGMOLD**

Plugmold is one of our most frequently requested custom products. From airports, to trains, to classrooms, dormitories or residences, anywhere multiple access to power or USB charging is needed. Custom receptacle spacing options, custom colors, wiring modifications, or any number of custom configurations are available for special applications. Contact the factory to discuss our capabilities and why Plugmold is often the best option for locations requiring multiple access to power or USB charging.





Plugmold<sup>®</sup> Multioutlet Systems


# Plugmold 2000 Series Steel Multioutlet Systems Ordering Information


#### **Product**

#### **Description/Specifications**

#### **GFCI Plugmold**

19/32 (32mm)






3/4" (19.1mm)


GFCI Module provi	aes aowns	stream prote	ction for all	outlets and connec	tions. Available in 3
(914mm), 5' (1.5m)	and 6' (1.8r	n) lengths w	ith 6" (152m	nm) receptacle spac	ing. 15A tamper-resistant
receptacles. 3-wire	, #12 THHN	N (1 hot, 1 ne	utral, and in	sulated ground cor	nductor).
.040" (1.0mm) steel	housing. F	Packed 2 per	carton. Eac	ch unit supplied wit	h one (1) Coupling
and two (2) Blank	End Fitting	s. GFCI Clas	s A 20A 125	5V 60Hz.	
	_				
CATALOG NO.	FINISH	LENGTH	WIRING	CENTER DISTANCE	OUTLETS

CATALOG NO.	FINISH		NGTH	WIRING		DISTANCE	OUTLETS	
		Feet	(mm)	CONFIG	Inches	(mm)	QUANTITY & TYPI	=
WH20GB306TRGFI6	White	3'	(915mm)	GB	6"	(152mm)	1 GFCI, 5 Single	15A
BK20GB306TRGFI6	Black	3'	(915mm)	GB	6"	(152mm)	1 GFCI, 5 Single	15A
V20GB306TRGFI6	lvory	3'	(915mm)	GB	6"	(152mm)	1 GFCI, 5 Single	15A
G20GB306TRGFI6	Gray	3'	(915mm)	GB	6"	(152mm)	1 GFCI, 5 Single	15A
S20GB306TRGFI6	Stainless	3'	(915mm)	GB	6"	(152mm)	1 GFCI, 5 Single	15A
WH20GB506TRGFI6	White	5'	(1.5m)	GB	6"	(152mm)	1 GFCI, 9 Single	15A
BK20GB506TRGFI6	Black	5'	(1.5m)	GB	6"	(152mm)	1 GFCI, 9 Single	15A
V20GB506TRGFI6	lvory	5'	(1.5m)	GB	6"	(152mm)	1 GFCI, 9 Single	15A
G20GB506TRGFI6	Gray	5'	(1.5m)	GB	6"	(152mm)	1 GFCI, 9 Single	15A
S20GB506TRGFI6	Stainless	5'	(1.5m)	GB	6"	(152mm)	1 GFCI, 9 Single	15A
WH20GB606TRGFI6	White	6'	(1.8m)	GB	6"	(152mm)	1 GFCI, 11 Single	15A
BK20GB606TRGFI6	Black	6'	(1.8m)	GB	6"	(152mm)	1 GFCI, 11 Single	15A
V20GB606TRGFI6	lvory	6'	(1.8m)	GB	6"	(152mm)	1 GFCI, 11 Single	15A
G20GB606TRGFI6	Gray	6'	(1.8m)	GB	6"	(152mm)	1 GFCI, 11 Single	15A
S20GB606TRGFI6	Stainless	6'	(1.8m)	GB	6"	(152mm)	1 GFCI, 11 Single	15A

NOTE: GFCI module does not contain an outlet.

# **Tamper-Resistant Plugmold**





Receptacles prevent the accidental insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements. Available in 3' (914mm), 5' (1.5m) and 6' (1.8m) lengths with 6" (152mm) receptacle spacing. 15A tamper-resistant receptacles. | 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor). .040" (1.0mm) steel housing. Packed 2 per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings.

CATALOG NO.	FINISH	LE Feet	NGTH (mm)	WIRING CONFIG	CENTER Inches	DISTANCE (mm)	OUTLE QUANTITY &	-
WH20GB306TR	White	3'	(915mm)	GB	6"	(152mm)	6 Single TR	15A
BK20GB306TR	Black	3'	(915mm)	GB	6"	(152mm)	6 Single TR	15A
V20GB306TR	lvory	3'	(915mm)	GB	6"	(152mm)	6 Single TR	15A
G20GB306TR	Gray	3'	(915mm)	GB	6"	(152mm)	6 Single TR	15A
S20GB306TR	Stainless	3'	(915mm)	GB	6"	(152mm)	6 Single TR	15A
WH20GB506TR	White	5'	(1.5m)	GB	6"	(152mm)	9 Single TR	15A
BK20GB506TR	Black	5'	(1.5m)	GB	6"	(152mm)	9 Single TR	15A
V20GB506TR	lvory	5'	(1.5m)	GB	6"	(152mm)	9 Single TR	15A
G20GB506TR	Gray	5'	(1.5m)	GB	6"	(152mm)	9 Single TR	15A
S20GB506TR	Stainless	5'	(1.5m)	GB	6"	(152mm)	9 Single TR	15A
WH20GB606TR	White	6'	(1.8m)	GB	6"	(152mm)	11 Single TR	15A
BK20GB606TR	Black	6'	(1.8m)	GB	6"	(152mm)	11 Single TR	15A
V20GB606TR	lvory	6'	(1.8m)	GB	6"	(152mm)	11 Single TR	15A
G20GB606TR	Gray	6'	(1.8m)	GB	6"	(152mm)	11 Single TR	15A
S20GB606TR	Stainless	6'	(1.8m)	GB	6"	(152mm)	11 Single TR	15A


Color codes: "V" for Ivory ScuffCoat" finish, "BK" for Black ScuffCoat" finish, "G" for Gray enamel finish, "WH" for white enamel finish, and "S" for stainless steel. Receptacle colors match extrusion colors except for stainless steel which has black receptacles and isolated ground versions which have orange receptacles.


All 2000 Series Plugmold products include two (2) 2010B Blank End Fittings and one (1) 2001 Base Coupling unless otherwise indicated in the product desciption.



# Plugmold® Multioutlet Systems

# Plugmold 2000 Series Steel Multioutlet Systems Ordering Information





Available in 3' [914mm], 5' [1.5m] and 6' [1.8m] lengths with 6" [152mm] receptacle spacing. 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor rated for use on 20A circuits). .040" [1.0mm] steel housing. Packed 2 per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. USB is 2.4 Amp (shared between 2 ports) 5VDC.

USB PLUGMOLD		LE	ENGTH	WIRING	CENTER	DISTANCE	OUTLETS	
CATALOG NO.	FINISH	Feet	[mm]	CONFIG	Inches	[mm]	QUANTITY &	
BK20GB306TRUSB	Black	3'	[915mm]	GB	6"	[152mm]	1 USB A, 5 Single	15A
BK20GB506TRUSB	Black	5'	[1.5m]	GB	6"	[152mm]	1 USB A, 9 Single	15A
BK20GB606TRUSB	Black	6'	[1.8m]	GB	6"	[152mm]	1 USB A, 11 Single	15A
G20GB306TRUSB	Gray	3'	[915mm]	GB	6"	[152mm]	1 USB A, 5 Single	15A
G20GB506TRUSB	Gray	5'	[1.5m]	GB	6"	[152mm]	1 USB A, 9 Single	15A
G20GB606TRUSB	Gray	6'	[1.8m]	GB	6"	[152mm]	1 USB A, 11 Single	15A
V20GB306TRUSB	lvory	3'	[915mm]	GB	6"	[152mm]	1 USB A, 5 Single	15A
V20GB506TRUSB	lvory	5'	[1.5m]	GB	6"	[152mm]	1 USB A, 9 Single	15A
V20GB606TRUSB	lvory	6'	[1.8m]	GB	6"	[152mm]	1 USB A, 11 Single	15A
S20GB306TRUSB	Stainless	3'	[915mm]	GB	6"	[152mm]	1 USB A, 5 Single	15A
S20GB506TRUSB	Stainless	5'	[1.5m]	GB	6"	[152mm]	1 USB A, 9 Single	15A
S20GB606TRUSB	Stainless	6'	[1.8m]	GB	6"	[152mm]	1 USB A, 11 Single	15A
WH20GB306TRUSB	White	3'	[915mm]	GB	6"	[152mm]	1 USB A, 5 Single	15A
WH20GB506TRUSB	White	5'	[1.5m]	GB	6"	[152mm]	1 USB A, 9 Single	15A
WH20GB606TRUSB	White	6'	[1.8m]	GB	6"	[152mm]	1 USB A, 11 Single	15A

Available in 3' [914mm], and 5' [1.5m] lengths with 12" spacing. USB is 2.4 Amps (shared between two ports) 5VDC. .040" [1.0mm] steel housing. Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. Each USB module provides 2 ports with 2.4 Amps of shared charging. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.



Available in 5' [1.5m] length with 9" spacing. 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor rated for use on 20A circuits). .040" [1.0 mm] steel housing. Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. USB is 2.4 Amps (shared between two ports) 5VDC. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

							•	
ALTERNATING		LE	NGTH		CENTER DISTANCE			
USB PLUGMOLD CATALOG NO.	FINISH	Feet	[mm]	WIRING CONFIG	Inches	[mm]	OUTLETS QUANTITY & TYPE	
BK20GB509TRUSBA	Black	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/3 USB A Modules	
G20GB509TRUSBA	Gray	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/3 USB A Modules	
V20GB509TRUSBA	lvory	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/3 USB A Modules	
S20GB509TRUSBA	Stainless	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/3 USB A Modules	
WH20GB509TRUSBA	White	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/3 USB A Modules	
BK20GB509TRUAC	Black	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/2 USB A & 1 USB C Modules	
G20GB509TRUAC	Gray	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/2 USB A & 1 USB C Modules	
V20GB509TRUAC	lvory	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/2 USB A & 1 USB C Modules	
S20GB509TRUAC	Stainless	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/2 USB A & 1 USB C Modules	
WH20GB509TRUAC	White	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/2 USB A & 1 USB C Modules	
·							· · · · · · · · · · · · · · · · · · ·	





NOTE: Color codes: "V" for Ivory ScuffCoat™ finish, "BK" for Black ScuffCoat™ finish, "G" for Gray enamel finish, "WH" for white enamel finish, and "S" for stainless steel. Receptacle colors match extrusion colors except for stainless steel which has black receptacles and isolated ground versions which have orange receptacles.

All 2000 Series Plugmold products include two (2) 2010B Blank End Fittings and one (1) 2001 Base Coupling unless otherwise indicated in the product desciption.



# Plugmold Multioutlet Systems

# Plugmold 2000 Series Steel Multioutlet Systems Ordering Information


	Cord-Ended Plugmold 2000 Series Steel Ordering Information								
CAT NO.		NIT GTH	OUTLETS QUANTITY	CORD SI	ET LENGTH	TYPE	SWITCH	CIRCUIT BREAKER	FINISH
20-C2*	3' 4"	(1m)	6 Single	6'	(1.8m)	12/3 SJT	No	Yes	Steel - Gray, Ivory

<sup>\*</sup> Use "V" prefix for Ivory ScuffCoat" finish and "G" prefix for Gray enamel finish.

V2000BC (Ivory) WH2000BC (White) **G2000BC** (Gray) BK2000BC (Black) S2000BC (Stainless Steel)

Base and Cover - 2000B Base: .040" (1.0mm) steel; 2000C Cover: .025" (.6mm) steel. Packed ten 5' (1.5m) lengths of each per carton.

# W30/W30G



NOTE: Not for use with aluminum conductors.

#### **Pressure-Type Wire**

Connectors - This part comes with both 16-W30 and 8-W30G. W30 - For common connection of two, three, or four No. 12 or No.14 solid copper conductors. W30G - For connection of equipment grounding of two, three, or four No.12 or No. 14 AWG solid conductors. 300V maximum; 20A 105° C maximum.

V2000B-5 (Ivory) WH2000B-5 (White) G2000B-5 (Gray)

(33mm)

Raceway Base - 040" (1.0mm) steel. Packed twenty 5' (1.5m) lengths per carton.

#### 2000WC



Wire Clip (Plated) - Use when conductors bypass receptacles. Not UL Listed.




#### V2000B-10 (Ivory) WH2000B-10 (White)



Raceway Base - .040" (1.0mm) steel. Packed ten 10' (3.05m) lengths per carton.

#### 2001



#### **Coupling (Galvanized Steel)**


- Joins lengths of 2000 Series Raceway Base.

#### V2000C (Ivory) WH2000C (White) **G2000C** (Gray)



Raceway Cover - .025" (.6mm) steel. Packed twenty 5' (1.5m) lengths per carton. Has no receptacle hole cuts.


#### **V2003** (Ivory) 2003 (Plated Finish)



2003 Supporting Clip -Temporary support, while positioning lengths of raceway base. Use with 2000 Series Raceway.

- 1. 2003 mounted on surface with No. 6 flathead screw.
- 2. Plugmold 2000 snaps into 2003 Supporting Clip.

# **Raceway Base and Cover**




**V2006** (Ivory) WH2006 (White) G2006 (Gray) BK2006 (Black) S2006 (Stainless Steel) 2006 Cover Clip - Covers seam where lengths of cover or base meet.

#### **620BCK**


620

Replacement Blade Kit -Replacement blades and die set for 620 Cutter.




# 2000 Series Steel Raceway Fittings Ordering Information


#### 2009




V2010A3 (Ivory) WH2010A3 (White) G2010A3 (Gray) BK2010A3 (Black)




V2010A2 (Ivory) WH2010A2 (White) G2010A2 (Gray) BK2010A2 (Black) S2010A2 (Stainless Steel)



**V2010B** (Ivory) WH2010B (White) **G2010B** (Gray) BK2010B (Black) S2010B (Stainless Steel)



**V2011** (Ivory) **WH2011** (White) **G2011** (Gray) **BK2011** (Black) S2011 (Stainless Steel)



Ground Clamp (Galvanized) -Connects equipment grounding

conductor to provide an additional ground to raceway.



2010A3 Entrance End Fitting -

Offers larger capacity than V2010A2, 1/2" trade size KOs on end, each side and bottom. 3/4" trade size KOs on bottom and rear. Includes ground screw.


2010A2 Entrance End Fitting

- Smallest entrance end fitting for connecting Plugmold 2000TR Series with 1/2" trade size conduit and armored cable connectors. 1/2" trade size KOs on end, each side and bottom. Includes ground screw.

Blank End - Closes off open end of 2000 Series Raceway.


90° Flat Elbow - Right angle turns on same surface. Cover stop permits neat butting of 2000C Cover. Two couplings furnished.

V2015 (Ivorv) WH2015 (White) **G2015** (Gray) **BK2015** (Black)



Tee - Branches raceway at right angles. Couplings furnished.

#### 2017TC



**V2018C** (Ivory) WH2018C (White) **G2018C** (Gray) BK2018C (Black) S2018C (Stainless Steel) Internal Corner Coupling -Furnished with one fiber bushing.




1. 2017TC used as a corner coupling.



2. 2017TC used as a corner coupling and a straight-through fitting.

#### **External Elbow Cover -**


Continues raceway runs around outside corner. Fills the gap when external corner is made by notching and bending the 2000 Base.



Corner Gap Filler snapped into place in 2018C.



V2048 (Ivorv) WH2048 (White) G2048 (Gray) BK2048 (Black) S2048 (Stainless Steel)




## Single-Gang Device Box -

Cover has twistouts for 2000, 500 and 700 Series Raceways. Base has 1/2" trade size KO and rectangular KO for extension to wall box. Base has No. 10 threaded hole for ground connection.


# 2000 Series Steel Raceway Fittings Ordering Information

V2048-2 (Ivory) WH2048-2 (White) G2048-2 (Gray) BK2048-2 (Black)



Two-Gang Device Box - Cover has twistouts for 2000, 500 and 700 Series Raceways. Base has 1/2' trade size KO and rectangular KO for extension to wall box. Base has No.10 threaded hole for ground connection.

#### V2089




**Side Reducing Connector** onnects 2000 Series Plugmold with 500 Series Raceway through the side of 2000 Series Plugmold.


V2051H (Ivory) WH2051H (White) **G2051H** (Gray) BK2051H (Black) S2051H (Stainless Steel)

Flush Plate Adapter - Feeds 2000 Series Plugmold from an existing wall outlet. Equipped with 1/2" (12.7mm) threaded stud, toothed lock washer for grounding, threaded hole for and conduit


#### V2089E



**End Reducing Connector -**Connects 2000 Series Plugmold with 500 Series Raceway through the end of 2000 Series Plugmold.



bushing.





Plug-In Outlet Center Unit -Six outlets, steel housing with ivory (V20-C2) or gray finish (G20-C2). 6' (1.8m) cord. Length 40" (1m). Receptacle center-tocenter 6" (152mm).







2051H fastened to horizontally mounted wall box.



2051H fastened to vertically mounted wall

# 2000 Series Interconnectivity Fittings

CONNECTION		
FROM	ТО	USE CATALOG NUMBER
500 Series Raceway	Side of Plugmold 2000 Series	V2089, V2048, V2048-2
500 Series Raceway	End of Plugmold 2000 Series	V2089E, V2048, V2048-2
Existing Outlet	Plugmold 2000 Series	V2051H
1/2" trade size Conduit or Armored Cable	End of Plugmold 2000 Series	V2010A2, V2010A3





Plugmold Multioutlet Systems

# **Plugmold 2400 Series Steel Multioutlet Systems**

2400 Series Plugmold Wire Fill Capacities for Power								
CABLE TYPE	WIRE SIZE THHN/THWN	O. Inches	D. (mm)	NO. OF CONDUCTORS (40% FILL) 2400				
POWER WIRING WITHOUT DEVICES	10 AWG 12 AWG 14 AWG	0.166 0.130 0.111	(4.2) (3.3) (2.8)	26 41 57				
POWER WIRING WITH DEVICES (Plugmold Series)	8 AWG 10 AWG 12 AWG 14 AWG	0.218 0.153 0.122 0.105	(5.5) (3.9) (3.1) (2.7)	2 6 10 -				







#### **Plugmold 2400 Series Steel Part Numbering System**

2400 Series Steel Plugmold Series w/Simplex Receptacle - Example: 24GBA512



	<u>V</u>					
COLOR						







12 CENTER DISTANCE:

lvory

= V 2400 =

GB = **GB** GBA = **GBA**  36" (915mm) 60" (1.5m)

72" (1.8m)

=

WIRING CONFIGURATION: COLOR:

= 5

= 6

6" (152mm) = **6** 12" (305mm) = **12** 18" (457mm) = **18** 

2400 Series Steel Plugmold Series w/Duplex Receptacle - Example: 24SGBX3618I

-	2 _	<u>4</u>	<u>S</u> _	
R/	(CE	WA	Y:	

= **24S** 

3 6

1 8

<u>G B X</u>

9 <u>9 I V</u>

2400 =

36" (915mm) 60" (1.5m)

72" (1.8m)

**CENTER DISTANCE:**12" (305mm) = 12

= 18

18" (457mm)

24" (610mm)

GBX = GBX GBA = GBA

= IGX

IGX

Ivory = **99IV** 

NOTE: Not all combinations of color, wiring configurations, length, and center distance are available as standard products. For additional information, contact Wiremold Technical Support at 1-844-957-3783.

NOTE: Color codes: "V" for Ivory ScuffCoat<sup>--</sup> finish. Receptacle colors match extrusion colors except for isolated ground versions which have orange receptacles.

\* All 2400 Series Plugmold products include two (2) 2410B Blank End Fittings and one (1) 2401 Base Coupling unless otherwise indicated in the product desciption.

= 36

= 60




Plugmold<sup>®</sup> Multioutlet Systems

# Plugmold 2400 Series Steel Multioutlet Systems Ordering Information


**Product** 

#### **Description/Specifications**

Plugmold 2400 Series







Available in 3' (914mm), 5' (1.5m) and 6' (1.8m) lengths with 6" (152mm), 12" (305mm), 18" (457mm) and 24" (608mm) receptacle spacing. 15A and 20A receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor). .040" (1.0mm) steel housing. Packed 2 per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings.

CATALOG NO.	FINISH	LEI	NGTH	WIRING	CENTE	R DISTANCE	OUTLET	'S
		Feet	(mm)	CONFIG	Inches	(mm)	QUANTITY &	TYPE
V24GB306	lvory	3'	(915mm)	GB	6"	(152mm)	6 Single	20A
24S3612GBX99IV	lvory	3'	(915mm)	GB	12"	(305mm)	3 Duplex	20A
24S3612GBA99IV	lvory	3'	(915mm)	GBA	12"	(305mm)	3 Duplex	20A
V24GB506	lvory	5'	(1.5m)	GB	6"	(152mm)	10 Single	20A
V24GB512	lvory	5'	(1.5m)	GB	12"	(305mm)	5 Single	20A
V24GBA512	lvory	5'	(1.5m)	GBA	12"	(305mm)	5 Single	20A
24S6012GBX99IV	lvory	5'	(1.5m)	GB	12"	(305mm)	5 Duplex	20A
24S6012GBA99IV	lvory	5'	(1.5m)	GBA	12"	(305mm)	5 Duplex	20A
24S6012IGX99IV	lvory	5'	(1.5m)	IG	12"	(305mm)	5 Duplex	20A
V24GB606	lvory	6'	(1.8m)	GB	6"	(152mm)	12 Single	20A
V24GB612	lvory	6'	(1.8m)	GB	12"	(305mm)	6 Single	20A
V24GBA612	lvory	6'	(1.8m)	GBA	12"	(305mm)	6 Single	20A
V24GB618	lvory	6'	(1.8m)	GB	18"	(457mm)	4 Single	20A
V24GBA618	lvory	6'	(1.8m)	GBA	18"	(457mm)	4 Single	20A
24S7212GBX99IV	lvory	6'	(1.8m)	GB	12"	(305mm)	6 Duplex	20A
24S7224GBA99IV	lvory	6'	(1.8m)	GBA	24"	(608mm)	3 Duplex	20A
24S7218GBX99IV	lvory	6'	(1.8m)	GB	18"	(457mm)	4 Duplex	20A
24S7224GBX99IV	lvory	6'	(1.8m)	GB	24"	(608mm)	3 Duplex	20A
24S7218IGX99IV	lvory	6'	(1.8m)	IG	18"	(457mm)	4 Duplex	20A
24S7212IGX99IV	lvory	6'	(1.8m)	IG	12"	(305mm)	6 Duplex	20A
24S7224IGX99IV	lvory	6'	(1.8m)	IG	24"	(608mm)	3 Duplex	20A
24S7212GBA99IV	lvory	6'	(1.8m)	GBA	12"	(305mm)	6 Duplex	20A
24S7218GBA99IV	lvory	6'	(1.8m)	GBA	18"	(457mm)	4 Duplex	20A

NOTE: Color codes: "V" for Ivory ScuffCoat" finish. Receptacle colors match extrusion colors except for isolated ground versions which have orange receptacles.

All 2400 Series Plugmold products include two (2) 2410B Blank End Fittings and one (1) 2401 Base Coupling unless otherwise indicated in the product desciption.

#### 2400 Series Plugmold Wiring Configurations With Snapicoil **GBA Series: GB Series:**

#### **GB Series:**

3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated grounding conductor.

4-wire, #12 THHN (2 hot, 1 neutral and 1 ground), 2 circuit; outlets wired alternately; has insulated grounding conductor.

#### **IG Series:**

3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated-isolated grounding conductor. Orange receptacles.

3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated grounding conductor.

#### **GBA Series:**

4-wire, #12 THHN (2 hot, 1 neutral and 1 ground), 2 circuit; outlets wired alternately; has insulated grounding conductor.


NOTE: SNAPICOIL REELS on custom order. Snapicoil harness is available on reels if lengths greater than 50' are needed, or if multiple lengths are required for production-type jobs. The maximum length per reel is 240' for Snapicoil with outlets 12" and 18" on centers; 500' with outlets 30" on center. Packaging includes the necessary number of lengths of base, holecut cover, wire clips, and couplings for complete installation. Price and delivery information should be obtained prior to specifying or ordering. To specify or order, add "R" to the Snapicoil number. Ex: V24GB12R. Other outlet spacings available on custom order.

Receptacles are made from high impact thermoplastic. Snapicoil packaging includes the necessary lengths of 2400B Base, 2400C Hole Cut Cover, 2400WC Wire Clips, and 2401 Couplings for complete installation.



# Plugmold® Multioutlet Systems

# 2400 Series Steel Raceway Fittings Ordering Information



#### Base and Cover -


Base – V2400B .040" (1.0mm) steel. Cover – V2400C .040" (1.0mm) steel. Also available in custom colors.

**Country of Origin: USA** 

Cross-Sectional Area: 1.39in² (897mm²)


ITEM	CAT. NO.	LE	NGTH	MATERIAL
Base	V2400B	5'	(1.5m)	.040 Steel
Cover	V2400C	5'	(1.5m)	.025 Steel
Base & Cover	V2400BC	5'	(1.5m)	.025 Steel





Entrance End Fitting – Has 1/2" and 3/4" trade size KOs on end and bottom. Additional 1/2" trade size KO on sides.


<sup>2 1/8"</sup> Country of Origin: USA



**90° Flat Elbow** – For right angle turns on the same surface (nonmetallic cover).


**Country of Origin: USA** 






**Coupling** – For joining lengths of raceway. Use with V2400 Series.

**Country of Origin: USA** 



**Internal Elbow** – For making internal 90° corners. All steel construction.


**Country of Origin: USA** 



**Wire Clip** – Holds conductors in place in raceway.

**Country of Origin: USA** 






**External Elbow** – For covering outside corners (nonmetallic cover).

**Country of Origin: USA** 


#### V2406



**Cover Clip** – For covering joint where lengths of cover or base adjoin. Use with V2400 Series (nonmetallic).

Country of Origin: USA






Back Feed Fitting – For feeding 2400 Series Raceway from an existing outlet box. Equipped with 1/2" trade size male bushing and locknut washer for grounding.

**Country of Origin: USA** 

#### 2409


1/0/440/



**Ground Clamp** – No. 10 ground screw provided. Use with V2400 Series Raceway.

**Country of Origin: USA** 

#### V2448 V2448-2



**Device Box** – Base has 1/2" trade size KO and rectangular KO for extension to wall box. Has #10 threaded hole for ground connection. Cover has twistouts for 500/700 Series Raceway on each end and twistouts for 2400 Series Raceway on each side.

**Country of Origin: USA** 

V241UA	
15/8" (41mm)	2"
	(51mm)
1 3/16"	
(46mm)	

**Entrance End** – For connecting V2400 with 1/2" trade size conduit and armored cable. Use with V2400 Series Raceway.

**Country of Origin: USA** 

CAT. NO.	L	W	D	GANG #
V2448	4 5/8" (117mm)	2 7/8" (73mm)	13/4" (44mm)	1
V2448-2	4 3/4" (121mm)	4 3/4" (121mm)	13/4" (44mm)	2

#### V2410B



**Blank End** – For closing open end of V2400 Series Raceway.


**Country of Origin: USA** 



# Plugmold<sup>®</sup> Multioutlet Systems

# 2400 Series Steel Raceway Fittings Ordering Information

V2444 V2444-2



Extra Deep Device Box – Base has rectangular knockout to enable extension from existing singlegang flush wall box and 1/2" and 1" concentric KOs. Cover has twistouts for 500/700 Series Raceway on each end and twistouts for 2400 Series Raceway on each side.

**Country of Origin: USA** 

CAT. NO.	L	W	D	GANG #
V2444	4 5/8" (117mm)	2 7/8" (73mm)	2 3/4" (44mm)	1
V2444-2	4 3/4" (121mm)	4 3/4" (121mm)	2 3/4" (44mm)	2

V2489



Side Reducing Connector – For connecting V2400 Series Raceway with V500 Series Raceway.

**Country of Origin: USA** 

624



2400 and 2400BD Raceway & Cover Cutter – Portable

cutter for 2400B and 2400BD
Raceway and Cover. Tooled steel
construction for clean and easy
square cuts. Total manual operation.

**Country of Origin: USA** 


**624BCK** 

Replacement Blade Kit -

Replacement blades and die set for 624 Cutter.

**Country of Origin: USA** 


V2427GA



**Duplex Receptacle** – 3-wire, 15A, 125V, NEMA 5-15R. Provided with 10 1/2" (267mm) pigtails and inline splice connectors.

**Country of Origin: USA** 

V2427GT



2686FO



**Duplex Receptacle** – 3-wire, 20A, 125V, NEMA 5-20R. Provided with 10 1/2" (267mm) pigtails and inline splice connectors.


**Country of Origin: USA** 

**FiberReady Transition Feed** 

Fitting – Eliminates offsetting V2400 in connecting with surface panel boxes. Has 3/4" and 1" concentric trade size KOs with 1" trade size KO elongated so adjustment from surface to center of bushing is 1" (25mm) minimum to 1 5/8" (41mm) maximum. Has twistouts for transition to Pancake 1500 and 2600 Series Raceway.

**Country of Origin: USA** 


**IG2427GA** 



Isolated Ground Duplex Receptacle – 3-wire, 15A, 125V NEMA 5-15R. Provided with 10 1/2" (267mm) pigtails and inline splice connectors.

**Country of Origin: USA** 

**IG2427GT** 



Isolated Ground Duplex Receptacle – 3-wire, 20A, 125V NEMA 5-20R. Provided with 10 1/2" (267mm) pigtails and inline splice connectors.

**Country of Origin: USA** 


**Lamp Holder** – Medium base lamp holder 660W, 250V. Black, general purpose phenolic.

Country of Origin: USA

Plugmold® Multioutlet Systems

# Aluminum Plugmold<sup>®</sup> Multioutlet Systems

Aluminum Plugmold Multioutlet Systems offer an attractive choice for hospital and commercial labs, as well as for residential applications. The durable finish offers both aesthetics and corrosion resistance. Aluminum Plugmold Series is available in single and alternating circuits, with standard or isolated ground tamper-resistant receptacles. It can also be customized to meet virtually any job requirement.





The durable corrosion-resistant finish of Aluminum Plugmold Series makes it an ideal solution for use in laboratories.

Plugmold AL2000 Series Wire Fill Capacities for Power											
CABLE TYPE	WIRE SIZE THHN/THWN	O Inches	).D.   (mm)	NO. OF CONDUCTORS (40% FILL) AL2000							
POWER WIRING WITHOUT DEVICES	8 AWG 10 AWG 12 AWG 14 AWG	0.216 0.166 0.130 0.111	(5.5) (4.2) (3.3) (2.8)	12 24 38 51							
POWER WIRING WITH DEVICES (Plugmold Series)	8 AWG 10 AWG 12 AWG 14 AWG	0.218 0.153 0.122 0.105	(5.5) (3.9) (3.1) (2.7)	- 3 6 8							

Plo	Plugmold AL2400 Series Wire Fill Capacities for Power									
CABLE TYPE	WIRE SIZE THHN/THWN	O Inches	.D.   (mm)	NO. OF CONDUCTORS (40% FILL) AL2000						
POWER WIRING WITHOUT DEVICES	6 AWG 8 AWG 10 AWG 12 AWG 14 AWG	0.254 0.216 0.164 0.130 0.111	(6.5) (5.5) (4.2) (3.3) (2.8)	13 18 37 58 78						
POWER WIRING WITH DEVICES (Plugmold Series)	6 AWG 8 AWG 10 AWG 12 AWG 14 AWG	0.254 0.216 0.164 0.130 0.111	(6.5) (5.5) (4.2) (3.3) (2.8)	3 4 8 12 16						

Plugmold Multioutlet Systems

# Plugmold AL2000 Series Steel Multioutlet Systems Ordering Information

# Plugmold AL2000 Series Aluminum Part Numbering System AL2000 Series Aluminum Plugmold Series - Example: AL20GB306TR





Aluminum = AL 2000





GB = GB

GBA = GBA

= IG\*



6



WIRING CONFIGURATION: LENGTH:

**CENTER DISTANCE:** Tamper-Resistant = TR

24'' (608mm) = 26" (152mm) 36" (915mm) = 39" (229mm) 60" (1.5m) 72" (1.8m) = 6

12" (305mm) = 12 18" (457mm) = **18** 

NOTE: Not all combinations of color, wiring configurations, length, and center distance are available as standard products. For additional information on custom options, contact Wiremold Technical Support at 1-844-957-3783.

NOTE: AL2000 Series Aluminum Plugmold products are available in an anodized finish with gray receptacles.

\* All AL2000 Series Plugmold products include two (2) AL2010B Blank End Fittings and one (1) AL2001 Base Coupling unless otherwise indicated in the product desciption.


# Plugmold AL2000 Series Aluminum Multioutlet Systems Ordering Information


#### **Product**

#### **Description/Specifications**

#### **Plugmold AL2000 Series**

Available in 3' (914mm), 5' (1.5m) and 6' (1.8m) lengths with 6" (152mm), 12" (305mm) and 18" (457mm) receptacle spacing. 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor). Packed 2 per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings.






CATALOG NO.	FINISH	LE Feet	NGTH (mm)	WIRING CONFIG	CENTE Inches	R DISTANCE (mm)	OUTLETS QUANTITY & T	
AL20GB306TR	Aluminum	3'	(915mm)	GB	6"	(152mm)	6 Single	15A
AL20GB506TR	Aluminum	5'	(1.5m)	GB	6"	(152mm)	10 Single	15A
AL20GB512TR	Aluminum	5'	(1.5m)	GB	12"	(305mm)	5 Single	15A
AL20GB606TR	Aluminum	6'	(1.8m)	GB	6"	(152mm)	12 Single	15A
AL20GB612TR	Aluminum	6'	(1.8m)	GB	12"	(305mm)	6 Single	15A
AL20GB618TR	Aluminum	6'	(1.8m)	GB	18"	(457mm)	4 Single	15A
AL20GBA606TR	Aluminum	6'	(1.8m)	GBA	6"	(152mm)	12 Single	15A
AL20GBA612TR	Aluminum	6'	(1.8m)	GBA	12"	(305mm)	6 Single	15A
AL20GBA618TR	Aluminum	6'	(1.8m)	GBA	18"	(457mm)	4 Single	15A

#### **Aluminum GFCI Plugmold**

GFCI Module provides downstream protection for all outlets and connections. Available in 3' (914mm), 5' (1.5m) and 6' (1.8m) lengths with 6" (152mm) receptacle spacing. 15A tamper-resistant receptacles. 3-wire,#12 THHN (1 hot, 1 neutral, and insulated ground conductor). Packed 2 per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. GFCI Class A 20A 125V 60Hz.



CATALOG NO.	FINISH	LEI Feet	NGTH (mm)	WIRING CONFIG	CENTER Inches	DISTANCE (mm)	OUTLETS QUANTITY & TYPE	
AL20GB306TRGFI6	Aluminum	3'	(915mm)	GB	6"	(152mm)	1 GFCI, 5 Single	15A
AL20GB506TRGFI6	Aluminum	5'	(1.5mm)	GB	6"	(152mm)	1 GFCI, 9 Single	15A

NOTE: GFCI module does not contain an outlet.




Plugmold Multioutlet Systems


# Plugmold AL2000 Series Steel Multioutlet Systems Ordering Information

#### **Product**


#### **Description/Specifications**

Aluminum All USB Plugmold





CATALOG NO.	FINISH	LE	NGTH	WIRING	CENTER	DISTANCE	OUTLETS
		Feet	(mm)	CONFIG	Inches	(mm)	QUANTITY & TYPE
AL20USB312	Aluminum	3'	(915mm)	USB	12"	(305mm)	3 USB Modules
AL20USB512	Aluminum	5'	(1.5m)	USB	12"	(305mm)	5 USB Modules



Available in 5' (1.5m) length with 9" spacing. 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral and insulated ground conductor). Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. USB Type-A Module is 2.4 Amps (shared between two ports) 5VDC. USB Type-C module is a single 30W Power Delivery port. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

CATALOG NO.	FINISH	LEN Feet	IGTH (mm)	WIRING CONFIG	CENTER DISTANCE Inches (mm)	OUTLETS QUANTITY & TYPE
AL20GB509TRUSBA	Aluminum	5'	(1.5m)	GB/USB	9"(229mm)	3 Outlets/3USB Modules
AL20GB509TRUAC	Aluminum	5'	(1.5m)	GB/USB	9" (229mm)	3 Outlets/2 USB-AModules/

NOTE: AL2000 Series Aluminum Plugmold products are available in an anodized finish with gray receptacles. """""


All AL2000 Series Plugmold products include two (2) AL2010B Blank End Fittings and one (1) AL2001 Base Coupling unless otherwise indicated in the product desciption.



# Plugmold Multioutlet Systems

# AL2000/AL2400 Series Aluminum Raceway Fittings Ordering Information

#### **AL2000**




Base and Cover - 6063-T5 extruded aluminum, satin anodized finish, .060" (1.5mm) nominal thickness.

**Country of Origin: USA** 


Cross-Sectional Area: 1in² (645mm²)

#### AL2400



Capacity: 1.7 in.<sup>2</sup> (1097mm<sup>2</sup>)

ITEM	CAT. NO.	LENGTH				
Base	AL2000B-5	5' (1.5m)				
Cover	AL2000C-5	5' (1.5m)				
Base	AL2000B-10	10' (3.m)				
Base	AL2400B-5	5' (1.5m)				
Cover	AL2400C	5' (1.5m)				
Base	AL2400B-10	10' (3.m)				



 $\bigcirc$ 



**Supporting Clip** – Mount to surface with No. 8 flathead screws. Use with AL2000 Series.

**Country of Origin: USA** 



Wire Clip - Holds conductors in place in raceway (nonmetallic).

**Country of Origin: USA** 

#### W30/W30G




# **Pressure-Type Wire**

Connectors - W30 - For common connection of two, three, or four No. 12 or No.14 solid copper conductors (White).

**W30G** – For connection of equipment grounding of 2, 3, or 4 solid conductors No. 14 or No. 12 AWG (Green). 300V maximum; 20A 105° C maximum.

**Country of Origin: USA** 


NOTE: Not for use with aluminum conductors.



**Coupling** – For joining lengths of raceway. Use with AL2000 Series.


**Country of Origin: USA** 

CAT NO.	L	W			
AL2001	1 5/8" (41mm)	1 1/2" (38mm)			
AL2401	3" (76mm)	1 3/4" (44mm)			




**Cover Clip** – For covering joint where lengths of cover or base adjoin. Use with AL2000 Series.

Country of Origin: USA




**Ground Clamp** – Use with AL2000 Series.

Country of Origin: USA #8 Ground Stud W/Cup Washer



End Fitting – With 1/2" hub adapter. Use with AL2000 Series.


**Country of Origin: USA** 





**Box Adapter** – For feeding raceway from an existing wall outlet.

**Country of Origin: USA** 



**90° Flat Elbow** – For right angle turn on same surface. Comes with two couplings.

**Country of Origin: Mexico** 


CAT NO.		Α		В	С		
AL2011	3"	(76mm)	3"	(76mm)	1 9/16"	(40mm)	
AL2411	4"	(102mm)	4"	(102mm)	2"	(51mm)	



Plugmold<sup>®</sup> Multioutlet Systems

# AL2000/AL2400 Series Aluminum Raceway Fittings Ordering Information

AL2015 AL2415




**Tee** – For branch connection of two runs of AL2000 Raceway. Three couplings furnished.

**Country of Origin: Mexico** 

CAT NO.		A		В	С		
AL2015	1 7/16"	(37mm)	4"	(102mm)	1 9/16"	(40mm)	
AL2415	4"	(102mm)	6"	(152mm)	2"	(51mm)	


AL2017 AL2417



**Internal Elbow** – For bending around internal corners. Two couplings furnished.

**Country of Origin: Mexico** 

CAT NO.	Α			
AL2017	3" (76mm)			
AL2417	4" (102mm)			




**External Elbow** – For making 90° external corners. Two couplings furnished.

**Country of Origin: Mexico** 

CAT NO.		4	В		
AL2018	17/8"	(48mm)	3"	(76mm)	
AL2418	3"	(76mm)	5"	(127mm)	


AL2038



#### **Round Fixture Box**

(Solid Base) – Designed for use in hanging fixtures. Cover takes any (35mm) device with mounting screw centers of 2 3/4", 3 1/2", and 4 1/16" (70mm, 89mm, and (103mm). Base has concentric 1/2" and 3/4" KOs.

**Country of Origin: USA** 



In-line Single Pole Switch – Single pole 120V switch. Two

Country of Origin: Mexico

couplings furnished.


AL2043TR

6"
(152mm)

In-line Receptacle – Two 15A, 120V U-ground factory wired receptacles. Couplings furnished. Receptacles are tamperresistant.

**Country of Origin: USA** 

#### AL2409




**Ground Clamp** – Use with AL2400 Series.

Country of Origin: USA

#8 Ground Stud W/Cup Washer

AL2010B



Blank End – Use with AL2000 Series.

**Country of Origin: USA** 

# AL2410B2




**End Fitting** – With 1/2" plastic KO. Use with AL2400 Series.

**Country of Origin: USA** 

11/4"

#### AL2044 AL2044-2




Deep Device Box – For receptacles and deep devices such as those of signal and alarm systems. Base has open back plate for mounting to existing wall box and solid back plate insert with 1/2" (AL2000 Raceway) and 3/4" (AL2000 Raceway) KO to close opening.

**Country of Origin: USA** 

CAT. NO.	L	W	D	GANG #
AL2044	4 5/8" (117mm)	3 1/16" (73mm)	2 1/4" (57mm)	1
AL2044-2	4 5/8" (117mm)	4 27/32" (121mm)	2 1/2" (64mm)	2

#### AL2047



#### **Shallow Switch & Receptacle Box**

- Designed for standard shallow switches and receptacles. Base has open back plate for mounting to existing wall box and solid back plate insert with 1/2" and 3/4" KO to close opening.

**Country of Origin: USA** 

CAT. NO.	L	W	D	GANG #
AL2047	4 5/8" (117mm)	3 1/16" (73mm)	13/8" (35mm)	1
AL2047-2	4 5/8" (117mm)	4 27/32" (121mm)	13/8" (35mm)	2



# Nonmetallic Plugmold<sup>®</sup> Multioutlet Assemblies

Nonmetallic Plugmold Mulitoutlet Systems provides a versatile solution for many applications. Plugmold sections offer single or alternating circuits, standard or isolated ground receptacles, and Snapicoil\* harnesses of prewired receptacles or cord ended units.

Nonmetallic Plugmold has a textured ivory finish with duplex receptacles, and can be customized to accommodate virtually any application.




Nonmetallic Plugmold Multioutlet Systems are available in a variety of configurations.

# **Plugmold NM2000 Series Nonmetallic Multioutlet Systems**

Plugmold NM2000 Series Wire Fill Capacities for Power								
CABLE TYPE	WIRE SIZE THHN/THWN	Inches	O.D. (mm)	NUMBER OF CONDUCTORS (40% FILL) NM2000/NM2400				
POWER WIRING WITHOUT DEVICES	10 AWG 12 AWG 14 AWG	0.164 0.130 0.111	(4.2) (3.3) (2.8)	15 31 45				
POWER WIRING WITH DEVICES (Plugmold Series)	10 AWG 12 AWG 14 AWG	0.153 0.122 0.105	(3.9) (3.1) (2.7)	- 8 * 8 *				

<sup>\*</sup> Including one hot, neutral, and ground wire from the receptacle.



Plugmold Multioutlet Systems

# Plugmold NM2000 Series Nonmetallic Multioutlet Systems

#### Plugmold NM2000 Series Nonmetallic Part Numbering System NM2000 Series Nonmetallic Plugmold Series - Example: NM20GB306 NM<u>2</u> 0 <u>3</u> COLOR: AMPERAGE: WIRING CONFIGURATION: **CENTER DISTANCE:** LENGTH: Nonmetallic = NM = 15A 48" (1.2m) = (229mm) GBA = GBA 12" (305mm) = 1260" (1.5m) = 20A = 5 = IG\* 72" (1.8m) 18" (457mm) = 18(760 mm) = 30NOTE: Not all combinations of color, wiring configurations, length, and center distance are available as standard products.

For additional information on custom options, contact Wiremold Technical Support at 1-844-957-3783.

NOTE: NM2000 Series Nonmetallic Plugmold products are available in an ivory finish with ivory receptacles.

\* All NM2000 Series Plugmold products include two (2) NM2010B Blank End Fittings unless otherwise indicated in the product desciption.

Plugmold NM2000 Series Raceway Wiring Configurations								
		With Snapicoil						
GB Series: 3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated grounding conductor.	GBA Series: 4-wire, #12 THHN (2 hot, 1 neutral and 1 ground), 2 circuit; outlets wired alternately; has insulated grounding conductor.	IG Series: 3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated-isolated grounding conductor. Orange receptacles.	GB Series: 3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated grounding conductor.	GBA Series: 4-wire, #12 THHN (2 hot, 1 neutral and 1 ground), 2 circuit; outlets wired alternately; has insulated grounding conductor.				

NOTE: SNAPICOIL REELS on custom order. Snapicoil harness is available on reels if lengths greater than 50' are needed, or if multiple lengths are required for production-type jobs. The maximum length per reel is 240' for Snapicoil with outlets 12" and 18" on centers; 500' with outlets 30" on center. Packaging includes the necessary number of lengths of base, holecut cover, wire clips, and couplings for complete installation. Price and delivery information should be obtained prior to specifying or ordering. To specify or order, add "R" to the Snapicoil number. Ex: NM20GB12R. Other outlet spacings available on custom order.

Receptacles are made from high impact thermoplastic. Snapicoil packaging includes the necessary lengths of NM2000B Base, NM2000C Hole Cut Cover, NM2000WC Wire Clips, and NM2001 Couplings for complete installation.

Cord-Ended Nonmetallic Plugmold Multioutlet Systems										
CAT NO.	UNIT LENGTH		OUTLETS QUANTITY			TYPE	SWITCH	CIRCUIT BREAKER	HOUSING	
NM20-C3	3'	(.92m)	3 Duplex	6'	(1.8m)	14/3 SJT	Yes	Yes	PVC-Ivory	
NM20-C4	4'	(1.2m)	4 Duplex	6'	(1.8m)	14/3 SJT	Yes	Yes	PVC-Ivory	
NM20-C5	5'	(1.5m)	5 Duplex	6'	(1.8m)	14/3 SJT	Yes	Yes	PVC-Ivory	
NM20-C6	6'	(1.8m)	6 Duplex	6'	(1.8m)	14/3 SJT	Yes	Yes	PVC-Ivory	

	Plugmold NM2000 Series Raceway with Snapicoil Harness									
CATALOG NO.	LENGTH	WIRING CONFIG		OUTLETS (15A 120V NEMA 5-15SR) CENTER DISTANCE QUANTITY			HOLE CUT COVER QUANTITY LENGTH			
NM20GB12	48'	GB	12"	(152mm)	24 Duplex	8	6'	(1.8m)	PVC-Ivory	
NM20GBA12	48'	GBA	12"	(305mm)	24 Duplex	8	6'	(1.8m)	PVC-Ivory	



Plugmold Multioutlet Systems


# Plugmold NM2000 onmetallic Multioutlet Systems Ordering Information

#### **Product**

#### **Description/Specifications**

**Plugmold NM2000 Series** 

Available in 4' (1.2m), 5' (1.5m) and 6' (1.8m) lengths with 9" (229mm), 12" (305mm) and 18" (457mm) and 30" (762mm) receptacle spacing. 15A receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor). Packed 2 per carton. Each unit supplied with two (2) Blank End Fittings.




	1 3/4" (44mm)		
		$\Rightarrow$	
(3)		હ્યે હિ	1" 25mm)
		<u>_√</u> ( <u></u>	,

CATALOG NO.	FINISH	LEN Feet	GTH (mm)	WIRING CONFIG	CENTER Inches	R DISTANCE (mm)	OUTLETS QUANTITY & T	
NM20GB412	Nonmetallic	4'	(1.2m)	GB	12"	305mm)	4 Duplex	15A
NM20GBA412	Nonmetallic	4'	(1.2m)	GBA	12"	(305mm)	4 Duplex	15A
NM20IG412	Nonmetallic	4'	(1.2 m)	GB	12"	(305mm)	4 Duplex	15A
NM20GB512	Nonmetallic	5'	(1.5m)	GB	12"	(305mm)	5 Duplex	15A
NM20GB515	Nonmetallic	5'	(1.5m)	GB	15"	(381mm)	4 Duplex	15A
NM20GB530	Nonmetallic	5'	(1.5m)	GB	30"	(760mm)	2 Duplex	15A
NM20GBA512	Nonmetallic	5'	(1.5m)	GBA	12"	(305mm)	5 Duplex	15A
NM20IG512	Nonmetallic	5'	(1.5m)	IG	12"	(305mm)	5 Duplex	15A
NM20GB609	Nonmetallic	6'	(1.8m)	GB	9"	(229mm)	8 Duplex	15A
NM20GB612	Nonmetallic	6'	(1.8m)	GB	12"	(305mm)	6 Duplex	15A
NM20GB618	Nonmetallic	6'	(1.8m)	GB	18"	(457mm)	4 Duplex	15A
NM20GBA609	Nonmetallic	6'	(1.8m)	GBA	9"	(229mm)	8 Duplex	15A
NM20GBA612	Nonmetallic	6'	(1.8m)	GBA	12"	(305mm)	6 Duplex	15A
NM20IG612	Nonmetallic	6'	(1.8m)	IG	12"	(305mm)	6 Duplex	15A

#### **Plugmold NM2400 Series**

Available in 4' (1.2m), 5' (1.5m) and 6' (1.8m) lengths with 9" (229mm), 12" (305mm) and 18" (457mm) and 30" (762mm) receptacle spacing. 20A receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor). Packed 2 per carton. Each unit supplied with two (2) Blank End Fittings.



CATALOG NO.	FINISH	LEN Feet	GTH (mm)	WIRING	CENTER Inches	R DISTANCE (mm)	OUTLETS QUANTITY & T	
						, ,		
NM24GB412	Nonmetallic	4'	(1.2m)	GB	12"	305mm)	4 Duplex	20A
NM24GBA412	Nonmetallic	4'	(1.2m)	GBA	12"	(305mm)	4 Duplex	20A
NM24GB512	Nonmetallic	5'	(1.5m)	GB	12"	(305mm)	5 Duplex	20A
NM24GB530	Nonmetallic	5'	(1.5m)	GB	30"	(760mm)	2 Duplex	20A
NM24GBA512	Nonmetallic	5'	(1.5m)	GBA	12"	(305mm)	5 Duplex	20A
NM24GB612	Nonmetallic	6'	(1.8m)	GB	12"	(305mm)	6 Duplex	20A
NM24GB618	Nonmetallic	6'	(1.8m)	GB	18"	(457mm)	4 Duplex	20A
NM24GBA612	Nonmetallic	6'	(1.8m)	GB A	12"	(305mm)	6 Duplex	20A


NOTE: NM2000 Series Nonmetallic Plugmold products are available in an ivory finish with ivory receptacles.

All NM2000 Series Plugmold products include two (2) NM2010B Blank End Fittings and one (1) NM2001 Base Coupling unless otherwise indicated in the product desciption.




# Plugmold Multioutlet Systems

# Plugmold NM2000 Series Nonmetallic Multioutlet Systems Ordering Information



ITEM	CAT. NO.	LENGTH		MATERIAL
Base	NM2000B	8'	(2.4m)	PVC-Ivory
Cover	NM2000C	8'	(2.4m)	PVC-Ivory
Base & Cover	NM2000BC	5'	(1.52m)	PVC-Ivory


## NM2003



Supporting Clip - Mount to surface with No. 8 flathead screw. Use with NM2000 Series.

**Country of Origin: USA** 

#### W30/W30G




**Pressure-Type Wire Connectors -**W30 - For common connection of two, three, or four No. 12 or No.14 solid copper conductors (White). W30G - For connection of equipment grounding of 2, 3, or 4 solid conductors No. 14 or No. 12 AWG (Green). 300V maximum; 20A 105° C maximum.

#### **Country of Origin: USA**

NOTE: Not for use with aluminum conductors.


#### NM2006



Cover Clip - For covering joint where lengths of NM2000 Series cover or base adjoin. Use with NM2000 Series.


**Country of Origin: USA** 

#### NM2010A




Entrance End - Has 1/2" trade size KO on end and bottom. Use with NM2000 Series.

#### Country of Origin: USA



#### NM2010B




Blank End Fitting - Use with NM2000 Series.

**Country of Origin: USA** 

#### NM2011







#### NM2015

Tee - For branches at right angles.

#### **Country of Origin: USA** 4 1/2" (114mm) 15/16 (33mm) 17/8 (48mm)




#### NM2017




Internal Elbow - For right turns at inside corners.

#### **Country of Origin: USA**



#### NM2018

External Elbow - Used for making 90° turns at outside corners.



NM2000 Series fittings work with both NM20 (15A) and NM24 (20A) Plugmold Multioutlet Systems.

Plugmold Multioutlet Systems


# Plugmold NM2000 Series Nonmetallic Multioutlet Systems Ordering Information

# NM2051H 2 3/4" (70mm) (114mm)

Wall Box Adapter – For feeding raceway from an existing wall outlet; horizontal applications. Provides complete access to wall box for connections.

**Country of Origin: USA** 

#### NM2048 NM2048-2



#### Sure-Snap® Device Box -

Cover snaps onto base, no screws required. Cover has twistouts on all sides. Rectangular KO in base for extension to wall box.

**Country of Origin: USA** 


NM2051V		3/4" 0mm)	<b>&gt;</b>
4 1/2" (114mm)	•		

Wall Box Adapter – For feeding raceway from an existing wall outlet; vertical applications. Provides complete access to wall box for connections.

**Country of Origin: USA** 

CAT. NO.	L	W	D	GANG #
NM2048	4 3/4" (121mm)	3" (76mm)	13/4" (44mm)	1
NM2048-2	4 3/4" (121mm)	4 7/8" (124mm)	13/4" (44mm)	2


#### NM2027-15 NM2027-20



Replacement Receptacles – 15A and 20A replacement devices. 6" (152mm) wire leads each side. Used to replace faulty receptacles in Plugmold Strips, not for installation in blank raceway base.

**Country of Origin: USA** 

#### NM2044



#### Extra Deep Device Box -

For mounting power/ communication device when additional depth is required. Has combination twistouts for 2700, 2800, 2900, and NM2000.

**Country of Origin: USA** 

CAT. NO.	L	W	D	GANG #
NM2044	4 3/4" (121mm)	3" (76mm)	2 3/4" (44mm)	1
NM2044-2	4 3/4" (121mm)	4 7/8" (124mm)	2 3/4" (44mm)	2

NOTE: NM2000 Series fittings work with both NM20 (15A) and NM24 (20A) Plugmold Multioutlet Systems.



Plugmold<sup>®</sup> Multioutlet Systems

NOTE: All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America 60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us

**Canada** 905.738.9195 www.legrand.ca

