


Decorator Devices Heavy-Duty Receptacles Tamper-Resistant 15 & 20A, 125V


Pass & Seymour

TR26262, TR26362

Sturdy tamper-resistant receptacles in Decorator-style.

leek, ergonomic Decorator-style matches other Decorator devices while giving the same performance and ease of installation as our standard tamper-resistant devices. The thermoplastic dual mechanical shutter system helps prevent children from sticking objects into the receptacle. They feature screw-pressure-plate back wiring and a back wire clamp on the ground terminal.





SF907R1 — Updated September 2006 — For latest specs visit www.legrand.us/passandseymour




Pass & Seymour

Decorator Devices Heavy-Duty Receptacles Tamper-Resistant 15 & 20A, 125V

Ordering Information

Catalog Number	Rating A. V.	Color	NEMA Config. No.		
Duplex Receptacles Back & Side Wire					
TR26262-I	15 125	lvory	5-15R		
TR26262-W	15 125	White	5-15R		
TR26262	15 125	Brown	5-15R		
TR26262-GRY	15 125	Gray	5-15R		
TR26262-BK	15 125	Black	5-15R		
TR26262-RED	15 125	Red	5-15R		
TR26262-LA	15 125	Light Almond	5-15R		
TR26362-I	20 125	lvory	5-20R		
TR26362-W	20 125	White	5-20R		
TR26362	20 125	Brown	5-20R		
TR26362-GRY	20 125	Gray	5-20R		
TR26362-BK	20 125	Black	5-20R		
TR26362-RED	20 125	Red	5-20R		
TR26362-LA	20 125	Light Almond	5-20R		



For more information on these and other P&S products refer to our Catalog or visit our web site.

Decorator Devices Heavy-Duty Receptacles Tamper-Resistant 15 & 20A, 125V




Technical Specifications

3rd Party Compliance

UL Listed, File Number E140596, Standard UL498. Federal Specification WC596. CSA Certified, File Number LR16063, Standard CSA-C22.2 No. 42. Conforms to NEMA WD-1 and WD-6.

Performance				
Electrical				
Dielectric Voltage	Withstands 2000V minimum			
Maximum Working Voltage	250V			
Current Interrupting	Certified for current interrupting at full-rated current			
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current			
Mechanical				
Terminal Identification	Terminal Identification in accordance with UL498 (Brass, White, Green)			
Terminal Accommodation	#14 AWG – #10 AWG copper conductor only			
Product Identification	Ratings are a permanent part of the device			
Environmental				
Flammability	UL94 V2			
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact			



Dimensions for 15 & 20 Amp

Materials					
Face Back Body Line Contacts Mounting Strap Ground Contacts Pressure Plate Tamper Shutter	Nylon Nylon .036 688 Brass Plated Steel Strap with Integral Ground .031 260 Brass Thermoplastic	Terminal Screws Ground Screw Assembly Drive Screw Auto-Ground Clip Mounting Screws	#10 Tri-Drive Brass (Neutral = Nickel-Plated Steel) #10 Hex Tri-Drive Brass Zinc-Plated Steel Steel Tri-Drive Steel		

Warranty


1 Year

Complimentary Devices & Accessories





- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade

GFCIs

- Specification Grade
- Dead Front



SWITCHES

- Extra Heavy-Duty
- Extra Heavy-Duty Lighted
- Extra Heavy-Duty Security
- Extra Heavy-Duty Locking
- Hard Use
- Commercial Grade

WALL PLATES

- TradeMaster[®]
- Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

Also available...

- Light Almond Devices
- Hospital Grade Devices
- PlugTail[™] Devices
- **TVSS & Isolated** Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok[®] Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor[®] Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour P.O. Box 4822 Syracuse, NY 13221-4822 800-223-4185

North America Headquarters 60 Woodlawn Street West Hartford, CT 06110 Phone: 1.877.BY.LEGRAND (295.3472) Fax: 1.860.232.2062 www.legrand.us

Legrand Canada 570 Applewood Crescent Vaughan, ON, L4K 4B4 Phone: 905.738.9195 Fax: 905.738.9721 www.legrand.ca

SF907R1 — Updated September 2006 — For latest specs visit www.legrand.us/passandseymour

