## **BA3 Series**

100 A 600 V; shallow

## **Product specifications**

- Conductor range: 6-2 AWG
- Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination overhead/underground
- Supplied with screw type ring

- Weatherproof Type 3R enclosure
- Primarily used in: All provinces

Note: Supply from an underground network often requires use of stud type connector. Consult your local utility.



Approved for copper

BA3-1 1/4V



Cat. no.		Dimensions (in.)			Weight each	
	Description	Н	W	D	lb	kg
4 Jaw	·					
BA3-V	Overhead, hub opening	91/4	77/16	311/16	5	2.2
BA3-INV	Overhead opening comes with insulated neutral	91/4	77/16	311/16	5	2.2
BA3-1V	Overhead, hub opening, comes with 1 in. hub	91/4	77/16	3 <sup>11</sup> / <sub>16</sub>	5	2.2
BA3-1 1/4V	Overhead, hub opening, comes with 1¼ in. hub	91/4	77/16	3 <sup>11</sup> /16	5	2.2
BA3-1 1/4INV	Overhead , hub opening comes with 1¼ in. hub and insulated neutral	91/4	71/16	311/16	5	2.2
BA3-TV	Underground	91/4	77/16	311/16	5	2.2
BA3-INTV	Underground come with insulated neutral	91/4	77/16	311/16	5	2.2
BA3-TCV	Combination overhead-underground	91/4	77/16	3 <sup>11</sup> /16	5	2.2
BA3-INTCV	combination overhead-underground come with insulated neutral	91/4	77/16	311/16	5	2.2
BA33-V	Overhead, twin hub opening	91/4	77/16	311/16	5	2.2
BA33-INV	Overhead, twin hub opening come with insulated neutral	91/4	77/16	311/16	5	2.2
BA33-1V	Overhead, twin hub opening comes with 1 in. hubs	91/4	77/16	3 <sup>11</sup> /16	5	2.2
BA33-1 1/4V	Overhead, twin hub opening, comes with 11/4 in. hubs	91/4	77/16	311/16	5	2.2
BA4-V*	Indoor type, KO on top	91/4	77/16	311/16	5	2.2
BA4-INV*	Indoor type, KO on top, comes with insulated neutral	91/4	77/16	311/16	5	2.2
BA4-VGN*	Indoor type, KO on top, comes with ground lug on neutral	91/4	77/16	311/16	5	2.2

Factory-installed accessories

Include: -5

 $5^{th}$  jaw, standard capacity, 9 o'clock position

\*for indoor use only unit is not NEMA 3R

## Diagrams



