

Project:		Type:
Drawn by:	Catalogue #:	Date:

Individual Spec Sheet

DOUBLE RING

LED CEILING LUMINAIRE

5 CCT Selectable

ORDERING INFORMATION

Order code: 68977

 Model number:
 CLDR12-R15W-A-5CBN

 UPC:
 069549023024

Case quantity: 4

PHYSICAL DATA

Size in. (mm): 12" (300)
Shape: Round
Housing material: Steel
Housing finish: Brushed Nickel
Lens material: Polystyrene
Lens finish: Frosted
Mounting: Surface

PERFORMANCE DATA

Watts (W): 15 **Volts (VAC):** 120

Color temperature (K)¹: 2 700/3 000/3 500/4 000/5 000

Lumen output (Im)2: 1 250 Efficacy (Im/W): 80 CRI: 80 Life L70 (h)3: 50 000 Beam angle (°): 120 **Dimming:** Yes Power factor: 0.90 Frequency (Hz): 60

Operating temp. range: $-20 \, ^{\circ}\text{C}$ to 45 $^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to 113 $^{\circ}\text{F}$)

¹ Typical color temperature range: +/- 5 %.

LUMEN SPECIFICATION TABLE

Order	Model number	2 700 K		3 000 K		3 500 K		4 000 K		5 000 K	
code		Lumen output (Im)	Efficiency (Im/w)								
68977	CLDR12-R15W-A-5CBN	1 206	80	1 274	85	1 377	92	1 402	93	1 330	89

DEFAULT PROGRAMMING

3 000 K

COMPATIBLE ACCESSORIES

Order code	Model number	Туре	Finish	Diameter (in.)	Compatible with	Case qty (master)
68983	LEN-CLDR12	Lens	Frosted	10 3/4	68977, 68980	10

























This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications. Data is based upon tests performed in a ontrolled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



² Lumen values are derived from Energy Star reported data. Initial lumens range: +/- 10 %.

³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.




COMPATIBLE DIMMERS¹

Brand	Model
LEGRAND	RH703PTUTC
COOPER	AAL06, SAL06P3
LEVITON	066EV, IPL06, 6674, DSL06-1ZL, DSM10-1LZ, IPE04-1LZ, DDMX1
LUTRON	PD-6WCL, RRD-6NA-WH, DVCL-153P, CTCL-153P, DVCL-253P, AYCL-253P, DVRP-253-WH, SELV-300P, MACL-153P

Dimming range: 5%-10%

DIMENSIONS AND WEIGHT




	12"
Net weight (lbs)	1.76

PHOTOMETRIC DATA¹

68977 • CLDR12-R15W-A-5CBN • 15 W • 3 000 K • 1 273.6 Im

Polar candela distribution



Zonal lumen summary


Zone	Lumens	% Fixture	
0-30	274.8	21.6	
0-40	455.1	35.7	
0-60	827.9	65	
60-90	327.8	25.7	
70-100	221.4	17.4	
90-120	89.4	7	
0-90	1 155.7	90.7	
90-180	117.9	9.3	
0-180	1 273.6	100	

Illuminance at a distance



Qty	Description	Price
Name:	ations of the luminaire configuration mentioned above.	
Company: Signature:		
Signature:		Date:

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.



¹ This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.

¹ Complete IES files available on our website.