


DRAWING NO.																	
10034254																	
CATALOG NUMBER	ITEM NUMBER	C-C	L	TONGUE STAMPING		REV.	DATE	DESCRIPTION		ECO	BY	C'K'D.					
				BURNDY	ALSTROM			ADDED FLAG AND TEXT NOTE #3									

BG12D93G102W	10028498	11.81 [300]	12.93 [328]	BG12D93G102W	BB0364760-2000
BG14D90G102W	10031716	13.78 [350]	14.90 [378]	BG14D90G102W	BB0364760-1000
BG16D87G102W	10028497	15.75 [400]	16.87 [428]	BG16D87G102W	BB0364760-3000
BG22D38G102W	10028499	21.26 [540]	22.38 [568]	BG22D38G102W	BB0364760-4000



NOTES:

- APPROXIMATE AMP RATING 415 INDOOR, 495 OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS, ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

3 "UL" SYMBOL PER INTERNAL SPEC. L4219, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.

TO ORDER BURNDY®PRODUCTS CALL 1-800-346-4175 MANCHESTER, NH 03109, USA FOR PRODUCT INFO = http://www.fciconnect.com			
BRAID			
ITEM NO: (TABLE)			
CAT NO: BG--D--G102W (TABLE)			
SCALE: 1/1			
DRAWN BY: P LAPONIUS 9/10/03			
CHECKER: J MICHAUD 9/10/03			
DSN APPVL: J MICHAUD 9/10/03			
MFG APPVL: -- --			
QC APPVL: C ACKERMAN 9/10/03		DRAWING NO	
MKT APPVL: D HAMILTON 9/9/03			
PROD FAM: --		10034254	
PROJECT #: --			
DOCUMENT TYPE: Sales		SHEET 1 of 1	
REL LEVEL: AutoCAD			
SIZE		B	
D			