




REV	DATE	DESCRIPTION	ECO	BY	C'K.
B	05/05/2017 00:00:00 AM	LOGO UPDATE	46674	BK	MB



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
- APPROXIMATE AMP RATING: 1500 A.
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

BRAID

ITEM NO: 10102041

CAT. NO: B41G14G2

DRAWN BY: C. RAJEEV 07/18/09

CHECKER: --

DSN APPVL: --

MFG APPVL: --

QA APPVL: J. BRODEUR

MKT APPVL: --

PROD FAM: Product/Mechanical Grounding

PROJECT #: --

DOCUMENT TYPE: Sales

REL LEVEL: Released

BURNDY

SCALE: NTS

DRAWING NO

REV

10104322

SHEET 1 OF 1

B