


REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
C	05/02/2017 09:05:00 AM	LOGO UPDATE	46639	BK	MB



NOTES:

1. APPROXIMATE AMP RATING: 1000 INDOOR, 1200 OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

3 'UL' SYMBOL PER INTERNAL SPECIFICATION L4219, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

BRAID - FLEXIBLE

ITEM NO: 10052765

CAT. NO: B4FI6G8TN

DRAWN BY: RL BOISVERT 02/17/05

CHECKER: P.LAPONIUS 02/17/05

DSN APPVL: J.MICHAUD 02/04/05

MFG APPVL: N/A --

QA APPVL: J.BRODEUR 02/04/05

MKT APPVL: R.BROOKS 02/03/05

PROD FAM: --

PROJECT #: --

DOCUMENT TYPE: Sales

REL LEVEL: Released



SCALE: 5:8

DRAWING NO

10053418

SHEET 1 OF 1

REV

C