


M12549 4



NOTES:
 1. ALL DIMENSIONS ARE IN INCHES [mm].
 2. TO BE USED WITH HUBBELL BOX
 CAT.#: RR1500 OR HBL985 & HBL989.

CATALOT NO:	DESCRIPTION	RATING	COLOR
RR1512LA	2G RECESS TR DUPLEX RECEPTACLE W/FEED THRU, 15A 125V	15A, 125V	LIGHT ALMOND
RR1512I			IVORY
RR1512W			WHITE
RR1512			BROWN
RR1512GY			GRAY

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
COVER	THERMOPLASTIC	COLOR PER CAT#
BASE	THERMOPLASTIC	YELLOW
BRUSH COVER	THERMOPLASTIC	
BRUSH	THERMOPLASTIC	WHITE
STRAP	GALV.STEEL	
LINE SCREW	STEEL	BRASS PLATE
GR. SCREW	STEEL	Zn PLATE + GREEN
NEUTRAL SCREW	STEEL	Zn PLATE
DRIVE SCREW	STEEL	Zn PLATE
MOUNTING SCREW	STEEL	Zn PLATE
TERMINAL	BRASS	

SYM	REVISIONS	APP	DATE
4	UPDATED DRAWING PER DCN 23671 SBW		6/11/18
3	UPDATE THE PRINT PER DCN #21107.		03/17/15
2	BASE COLOR YELLOW WAS BLACK PER DCN #20927.		12/10/14
1	NEW RELEASE PER DCN #20652		08/18/14

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
 2G RECESS TR DUP RCPT W/FEED THRU, 15A 125V

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
.XX = ± .01	DR. BY N.H	APP. BY SM
.XXX = ± .005	TR. BY N.H	SCALE 1/2
ANGLES = ± 2°	CHK. BY C.Z	DATE 06/04/2014

DIMENSION SHEET FOR CAT. NO. **M12549 4**
 SEE TABLE
 REPAIRABLE NON-REPAIRABLE
B