



# KAD-LED Luminaire & Retrofit Door

Familiar Form. New Technology.



Outdoor

# Familiar Form. New Technology.

Cast in a traditional dayform, the KAD-LED area luminaire from Lithonia Lighting® provides classic styling with the latest LED and controls technology.

Whether your application calls for complete luminaires or the retrofit of an existing KAD, the new KAD-LED is the most cost-effective solution, with paybacks as low as **three years!**

## Replace 400W metal halide and save 69% in energy costs!

	400W Metal Halide	KAD-LED (40 LEDs)	Savings
Input Watts	460W	141W	<b>319W (69%)</b>
Expected Life (hours)	15,000	100,000+	<b>6+lamp changes</b>
Annual kWh (4,380 annual nighttime hrs.)	2,014	618	<b>1,396 kWh (69%)</b>
Annual Energy/Luminaire (@ \$0.10 per kWh)	\$201.48	\$61.76	<b>\$139.72</b>

The KAD-LED is DesignLights Consortium® (DLC) qualified. For utility rebates in your area, visit [www.dsireusa.org](http://www.dsireusa.org).



## Get more light on-target with superior uniformity.

- Greater coverage – distribution patterns are 14% wider and 20% farther
- The elimination of hot spots creates greater uniformity
- Less wasted backlight – light is directed where its needed

## Save more energy using the fully integrated bi-level motion sensor.

Order the KAD-LED with the factory installed bi-level motion sensor for even more savings! The fully programmable motion sensor enables the luminaire stay in dimmed mode during periods of non-occupancy and quickly ramps to full light output when motion is detected.



## Easy to Install

Whether your application calls for a complete luminaire or the retrofitting of an existing Lithonia Lighting HID KAD luminaire.



### KAD-LED Complete Luminaire

**We've made the upgrade to LED easy...**

Every KAD-LED area luminaire comes complete with the Lithonia Lighting Universal Mounting Bracket, which allows the complete KAD-LED luminaire to mount to virtually any existing drill hole pattern on both square and round poles. This eliminates the need to drill, which significantly reduces the time spent during installation.

### KARDR-LED Retrofit Door

**... and the retrofit door is even easier!**

If you already have a KAD luminaire, you can leave the upper housing in place and upgrade to LED by replacing the glass door with the KARDR-LED retrofit door. Everything is on the retrofit door, and by making three electrical connections, the door can be installed in less than three minutes!

See our retrofit installation video at [www.acuitybrands.com/kardr-led](http://www.acuitybrands.com/kardr-led).



**Multiple lumen packages provide energy-saving solutions for 175W to 400W metal halide.**

Metal Halide	KAD-LED			
Nominal Watts (Input Watts)	# LEDs	Input Watts	Delivered Lumens	Energy Savings
400W (460W)	40 LEDs	141W (R3)	14,890 (4000K)	<b>69%</b>
	30 LEDs	108W	11,502	<b>77%</b>
250W (295W)	30 LEDs	108W	11,502	<b>63%</b>
	20 LEDs	73W	7,854	<b>75%</b>
175W (210W)	20 LEDs	73W	7,854	<b>65%</b>

# KAD-LED (Complete Luminaire)

## Ordering Information

EXAMPLE: KAD LED 40C 1000 40K R5 MVOLT SPUMBAK04 DDBXD

KAD LED										
Series	LEDs		Drive current		CCT		Distribution		Voltage	Mounting
KAD LED	20C	20 LEDs	530	530 mA	30K	3000 K	R2	Type II	MVOLT	<b>Shipped included</b>
	30C	30 LEDs	700	700 mA	40K	4000 K	R3	Type III	120	SPUMBAK__ Square pole universal mounting adapter
	40C	40 LEDs	1000	1000 mA	50K	5000 K	R4	Type IV	208	RPUMBAK__ Round pole universal mounting adapter
	60C	60 LEDs					R5	Type V	240	SPD__ Square pole
								277	RPD__ Round pole	04 4" arm
								347	WBD__ Wall bracket	06 6" arm
								480	WWD__ Wood pole or wall	09 9" arm
										12 12" arm
										<b>Shipped separately</b>
										DAD12P Degree arm (pole)
										DAD12WB Degree arm (wall)

Options						Finish (required)	
<b>Shipped installed</b>						<b>Shipped separately</b>	
PER	NEMA twist-lock receptacle only (no controls)		PIR1FC3V	Motion/ambient sensor, 8-15' mounting height, ambient sensor enabled at 1fc <sup>6</sup>		WG	Wire guard
PERS	NEMA twist-lock five-wire receptacle only (no controls)		PIR1FC3V	Motion/ambient sensor, 15-30' mounting height, ambient sensor enabled at 1fc <sup>6</sup>		KMA	Mast arm external fitter
PER7	Seven-wire receptacle only (no controls)		PNMTDD3	Part night, dim till dawn			
SF	Single fuse (120, 277, 347V)		PNMT5D3	Part night, dim 5 hrs			
DF	Double fuse (208, 240, 480V)		PNMT6D3	Part night, dim 6 hrs			
PIR	Motion sensor, 8-15' mounting height		PNMT7D3	Part night, dim 7 hrs			
PIRH	Motion sensor, 15-30' mounting height		HS	Houseside shield			
BL30	Bi-level switched dimming, 30%						
BL50	Bi-level switched dimming, 50%						
						DDBXD	Dark bronze
						DBLXD	Black
						DNAXD	Natural aluminum
						DWHXD	White
						DDBTXD	Textured dark bronze
						DBLBXD	Textured black
						DNATXD	Textured natural aluminum
						DWHGXD	Textured white

# KARDR-LED (Retrofit Door)

## Ordering Information

EXAMPLE: KARDR LED 40C 1000 40K R5 MVOLT DDBXD

KARDR LED										
Series	LEDs		Drive current		CCT		Distribution		Voltage	
KARDR LED	20C	20 LEDs	530	530 mA	30K	3000 K	R2	Type II	MVOLT	277
	30C	30 LEDs	700	700 mA	40K	4000 K	R3	Type III	120	347
	40C	40 LEDs	1000	1000 mA	50K	5000 K	R4	Type IV	208	480
	60C	60 LEDs					R5	Type V	240	

Options						Finish (required)	
<b>Shipped installed</b>						<b>Shipped separately</b>	
PIR	Motion sensor, 8-15' mounting height		WG	Wire guard		DDBXD	Dark bronze
PIRH	Motion sensor, 15-30' mounting height					DDBTXD	Textured dark bronze
HS	Houseside shield					DBLBXD	Textured black
						DNAXD	Natural aluminum
						DNATXD	Textured natural aluminum
						DWHXD	White
						DWHGXD	Textured white

Please use the spec sheet at [www.acuitybrands.com](http://www.acuitybrands.com) when ordering to ensure component compatibility for your desired configuration.

Please visit [www.acuitybrands.com](http://www.acuitybrands.com) for more information.