



# BD24TN

by Burndy  
Catalog ID: BD24TN

Tin Plated Copper Braid 24 in Long

## Product Details

### General

|                                       |               |
|---------------------------------------|---------------|
| Connector Type                        | Braid         |
| Material                              | Copper        |
| Material - Ferrules                   | Y             |
| Physical Attribute - Number of Braids | 1             |
| Plated                                | Y             |
| Plating Type                          | Tin           |
| UPC                                   | 781810120835  |
| UPC 12 Digit                          | 7818101208355 |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 610 mm   |
| Dimension - Length Overall inch | 24.00 in |

### Electrical Ratings

|                           |       |
|---------------------------|-------|
| Rating - Indoor Amperage  | 190 A |
| Rating - Outdoor Amperage | 225 A |

### Certifications and Compliance

|                                    |       |
|------------------------------------|-------|
| Certification - CSA Approved       | Yes   |
| Certification - ETL                | No    |
| Certification - UL Recognized      | No    |
| Certification - cULus              | No    |
| Industry Standard(s)               | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX    |

|           |     |
|-----------|-----|
| UL Listed | Yes |
|-----------|-----|

Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)