



DRAWING NO. 10039046		
TABLE		
CATALOG NUMBER	ITEM NUMBER	L
BD9G123	10038933	9.00 [229]
BD10G123	10038176	10.00 [254]
BD12G123	25021015	12.00 [305]
BD22G123	10038934	22.00 [559]
BD24G123	10038935	24.00 [610]

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
B	12/11/07	ADDED FLAGS AND TEX NOTES 4 & 5	15258	PL	DB



NOTES:

- APPROXIMATE AMP RATING: 190 INDOOR, 225 OUTDOOR
THIS RATING MAY VARY WITH AMBIENT CONDITIONS,
ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS, ROUNDED OFF TO THE
NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- CAN BE ORDERED WITH PLATED FERRULES BY ADDING SUFFIX "TN" FOR TIN PLATING.
- "UL" SYMBOL PER INTERNAL SPEC. L4219, LOCATION AND SIZE TO BE DETERMINED
BY MANUFACTURING.
- "CSA" SYMBOL PER INTERNAL SPEC. L4591, LOCATION AND SIZE TO BE DETERMINED
BY MANUFACTURING.

TO ORDER BURNDY®PRODUCTS CALL 1-800-346-4175 MANCHESTER, NH 03109, USA FOR PRODUCT INFO = http://www.fciconnect.com			
BRAID			
ITEM NO: (TABLE)			
CAT NO: BD--G123 (TABLE)			
SCALE: 1/1			
DRAWN BY: P LAPONIUS 3/10/04			
CHECKER: D BOISVERT 3/11/04			
DSN APPVL: J MICHAUD 3/9/04			
MFG APPVL: ---			
QC APPVL: J BRODEUR 3/9/04		DRAWING NO	
MKT APPVL: R BROOKS 3/9/04			
PROD FAM: ---		10039046	
PROJECT #: ---		B	
DOCUMENT TYPE: Sales		SHEET 1 OF 1	
REL LEVEL: AutoCAD			