

## FEATURES & SPECIFICATIONS

### INTENDED USE

For use with frame-in LP6F, LP6 and housings LC6, LI6, L7X, L7XR, LI6F, L7XF and L7XFR.

### CONSTRUCTION

Aluminum white reflector.

Polyester powder coat paint.

White eyelid faceplate.

White integral flange as standard.

### INSTALLATION

Socket to trim interface.

Retaining clips riveted to top of reflector hold trim inside housing.

Rough-ins with clips retain trims.

### LISTINGS

U.L. Listed to U.S. and Canadian safety standards.

Damp location listed.

### WARRANTY

1-year limited warranty. Complete warranty terms located at

[www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

Actual performance may differ as a result of end-user environment and application.

Note: Specifications subject to change without notice.


Catalog Number
Notes
Type

6" Full Reflector Trim

# 6W1

PREMIUM WALLWASH

Narrow Flange




### Specifications

Height: 7-1/4" (18.4)

Lamp opening: 6-3/8" (16.2)

Diameter: 7-5/8" (19.4)

Trim height when used with Non-IC incandescent rough-ins.



All dimensions are inches (centimeters) unless otherwise indicated.

### ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

Example: 6W1


6W1	
Series	Finish
6W1	(blank) White eyelid

<b>Accessories:</b> Order as separate catalog number.	
CRT6	6" goof ring, white


### Housing Compatibility: Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
IC	Incandescent	40 A19	LI6
	Fluorescent	13DTT 26TRT	L7XF, L7XFR, LI6F
Non-IC	Incandescent	100 A19	LC6, L7X, L7XR, LP6
	Fluorescent	18DTT	LP6F, L7XF, L7XFR
		18TRT 26TRT	L7XF, L7XFR LP6F

# 6W1 6" Premium Wallwash Full Reflector Trim



Footcandle values are initial and tables are based on a minimum of 6 units. For fixture-to-wall distance other than those shown, use maximum of 1 to 1 spacing (distance between fixtures not more than distance to wall) for best results.



**6W1**, 100W A19 lamp, 1750 rated lumens, test no. 2188120209

1'	10	7	10	9	6	9	5	3	5	4	3	4	3	2	3	2	2	2
2'	17	12	17	14	10	14	8	6	8	7	5	7	5	3	5	4	3	4
3'	19	15	19	16	13	16	10	8	10	9	7	9	6	4	6	5	4	5
4'	17	14	17	14	13	14	11	8	11	9	8	9	7	5	7	6	5	6
5'	14	12	14	11	11	11	10	8	10	9	8	9	7	6	7	6	5	6
6'	11	9	11	9	8	9	9	7	9	7	7	7	7	6	7	6	5	6
7'	8	7	8	7	6	7	7	6	7	6	6	6	6	5	6	5	5	5
8'	6	5	6	5	5	5	6	5	6	5	5	5	5	4	5	5	4	5
9'	5	4	5	4	4	4	5	4	5	4	4	4	5	4	5	4	4	4
10'	4	3	4	3	3	3	4	3	4	4	3	4	4	3	4	3	3	3

**6W1**, 13W F13DTT/27K lamp, 660 rated lumens, test no. 2188041303

1'	8	6	8	7	4	7	3	3	3	3	3	3	2	2	2	2	2	2
2'	14	12	14	11	9	11	7	8	7	5	7	5	4	4	4	4	3	4
3'	13	12	13	10	10	10	7	8	7	6	6	6	5	4	5	4	4	4
4'	10	10	10	8	9	8	8	7	8	6	6	6	5	5	5	4	4	4
5'	7	7	7	6	6	6	6	6	6	5	6	5	5	4	5	4	4	4
6'	5	5	5	4	4	4	5	5	5	4	4	4	5	4	5	4	4	4
7'	4	3	4	3	3	3	4	4	4	3	3	3	4	3	4	3	3	3
8'	3	2	3	2	2	2	3	3	3	2	2	2	3	3	3	2	2	2
9'	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
10'	1	1	1	1	1	1	2	2	2	2	1	2	2	2	2	2	2	2

To calculate light levels for other lamps, multiply the footcandle levels by the ratio of desired-lamp lumens to displayed-lamp lumens.

Example: fc level at nadir for 100W A19 is 19. With a 75W A19, fc level is  $19 \times (1,210/1,750)$  or 13 fc.

Incandescent		Compact Fluorescent	
Lamp	Lumens	Lamp	Lumens
150W A21	2,850	26W DTT	1,800
100W A19	1,750	18W DTT	1,250
75W A19	1,210	13W DTT	860
60W A19	870		
40W A19	460		
Consult chart on page <b>LAMP</b> for appropriate <b>R</b> or <b>PAR</b> lamp data.			