

## Trac 12<sup>™</sup> Directional Spotlights

Ultra-efficient, contemporary directional lighting





## Juno® Trac 12™ Directional Spotlights

The Juno Trac 12 system offers a spectacular array of contemporary directional spotlights. With miniaturized sizing and multiple light sources to choose from – including ultra-efficient LEDs – these dynamic little fixtures can enhance any residential, retail, or commercial décor.

## Trac 12 is easily integrated into displays, low soffits, and ceilings or it can be pendant-suspended for dramatic accent lighting.

The diminutive dimensions of Trac 12 allow it to squeeze into tight spaces inaccessible to standard-size, line voltage track systems. Trac 12 is powered by remote low voltage transformers, eliminating the need for transformers at each fixture. This can be helpful in meeting today's stringent energy codes, since power calculations are typically based on the capacity of the transformers, rather than the linear feet of installed track.

## Juno® Trac 12™ Directional Spotlights



TI 2521



TL261L



TL381L

### Cylindra<sup>™</sup> LED – TL252L

The contemporary styling of the Cylindra LED subtly enhances practically any décor without diverting attention from the surrounding environment. Soft curved surfaces combine with clean, crisp edges to provide a uniquely attractive aesthetic. The Trac 12 Cylindra 13W LED spotlight approximates the light output and distribution of 75W MR16 halogen lamps, utilizing less than 1/5 of the energy and having a rated life of 50,000 hours. Cylindra's integral, bayonet-mounted accessory holder accommodates one accessory if desired. The white-light Cylindra LED is compatible with standard Trac 12 systems utilizing 12V AC LEDcompatible transformers.

#### Conix® II LED - TL261L

The sleek sculptured Conix II LED fixture has integral TIR optics which enable uniform spot, flood or narrow flood distributions to be achieved. The Conix II LED spotlight approximates the light output and distribution of 75W MR16 halogen lamps, utilizing less than 1/5 of the energy and having a rated life of 50,000 hours. Its integral, bayonet-mounted accessory holder accommodates one accessory if desired. The white-light Conix II LED is compatible with standard Trac 12 systems utilizing 12V AC LEDcompatible transformers.

## Contemporary Cylinder – TL381L

The classic appearance of the Contemporary Cylinder LED fixture offers a fresh take on the traditional aesthetic. This 13W LED spotlight approximates the light output and distribution of 75W MR16 halogen lamps, utilizing less than 1/5 of the energy and having a rated life of 50,000 hours. Its integral, bayonet-mounted accessory holder accommodates one accessory if desired. The whitelight Contemporary Cylinder LED is compatible with standard Trac 12 systems utilizing 12V AC LEDcompatible transformers.


## Dimensions Finishes




Black (BL) White (WH)

**Color Temperatures –** 2700K, 3000K, 3500K or 4000K

**CRI** – 80 CRI minimum or high 90 CRI minimum (2700K & 3000K only)



<sup>\*</sup>See page 5 or specification sheet for optional accessories.



<sup>\*</sup>See page 5 or specification sheet for optional accessories.

<sup>\*</sup>See page 5 or specification sheet for optional accessories.

## Juno® Trac 12™ Directional Spotlights



TI 114

### **LED Mini-Cylinder Spotlight – TL114**

The Trac 12 LED Mini-Cylinder Spotlight delivers big-time performance from a fixture so small that it fits easily in the palm of your hand. It offers the light output and distribution of 20W MR11 halogen but requires just one-third the energy and lasts more than 10-times longer. LED Mini-Cylinders provide up to 332 lumens of brilliant white light and are compatible with standard Trac 12 systems utilizing 12V AC LED-compatible transformers.

# Dimensions Finishes Black (BL) White (WH) Color Temperatures — 2700K, 3000K, 3500K or 4000K Optics — Spot, Narrow Flood or Flood With optional Snoot



<sup>\*</sup>See page 5 or specification sheet for optional accessories.





### Cylindra<sup>™</sup> - TL141

The Juno Trac 12 version of the popular Cylindra Series fixture transforms this unique design into a miniature, low-profile MR16 unit. Because it is fully enclosed, Cylindra is ideal where shielding from lamp backlighting is desired. Cylindra incorporates a clear glass lens and features an integral bayonetmount media cartridge that can simultaneously accept up to two light control accessories.

Lamp	Dimensions	Finishes	
12V or 24V 50W max. MR16	2-7/8"	Black (BL) White (WH)	

\*See page 5 or specification sheet for optional accessories.



### **Professional-Grade Media Cartridge**

All Cylindra™ lampholders feature a quick-release bayonet-mount media cartridge that simultaneously accepts up to two light control accessories. Media can be easily installed or removed without the use of tools. The bayonet-mount attachment simplifies relamping and fixture maintenance, making Cylindra a popular choice with owners, designers and installers.

## Juno® Trac 12™ Directional Spotlights



TL1040





TL296

### Lily16 - TL1040

Constructed with a semi-open design, this series provides for improved airflow around the lamp, optimized LED lamp life. They may

### leading to better cooling and also be used with MR16 halogen lamps with integral cover glass.

12V or 24V 50W max. MR16

Lamp



**Dimensions** 

# Black (BL)

**Finishes** 

White (WH)

### **Gimbal Rings –** TL196 & TL296

Choose the basic single yoke of the TL196 or the more elegant, sculpted dual-yoke design of the TL296.

Lamp	Dimensions	Finishes
12V or 24V 50W max. MR16	2-1/2" 2-1/4" 2-1/4" -2"-  TL196	Black (BL) White (WH
	2-3/4" + 2-1/4" 2-1/4"	

TL296



### Trac 12<sup>™</sup> | Accessories

### **Light Control Accessories**

The Juno complete range of light control accessories permit the designer to custom tailor effects. See individual fixture pages and specification sheets for additional details.

Beam Contro	l Lenses		1-3/4" DIAMETER	COMPATIBLE WITH	2" DIAMETER	COMPATIE WITH
offitte.	These alter the light	Prismatic Spread Lens	PRISM 175	TL196, TL296	PRISM 200	TL141*,
	distribution, enlarging or	Linear Spread Lens	LSPREAD 175		LSPREAD 200	TL252L, TL261L,
	elongating it, softening the	Uniformity Lens (Solite™)	SOLITE 175		SOLITE 200	TL381L
	beam edge or removing striations.	Diffusion Lens	DIFF 175		DIFF 200	
IV Filters	,					
	These museum quality lenses filter out ultraviolet radiation below 400 nanometers to protect fade sensitive art and objects from light degradation.		UVF 175		UVF 200	
ichroic Col	or Correction Filters					
	Color Correction Filters correct the light, either to warm it up to approximate incandescent, or cool it down to approximate daylight.	Halogen-to-Incandescent, 2700K	DCCF 175 HAL2700		DCCF 200 HAL2700	<u>'</u>
		Halogen-to-Daylight, 4250K	DCCF 175 HAL4250		DCCF 200 HAL4250	
olor Filters	'	Dichroic Glass Filters				
	Color Filters change white	Red	DGF 175 DRED		DGF 200 DRED	
	light into colored light and	Medium Green	DGF 175 MGRN		DGF 200 MGRN	
	are available in colored glass and more efficient/saturated	Medium Blue	DGF 175 MBLU		DGF 200 MBLU	
	dichroic filters.	Yellow	DGF 175 DYEL		DGF 200 DYEL	
		Magenta	DGF 175 MAGEN		DGF 200 MAGEN	
	Blue-Green (Cyan)	DGF 175 CYAN		DGF 200 CYAN		
		Colored Glass Filters				
		Medium Pink	CGF 175 MPINK		CGF 200 MPINK	
		Warm Red	CGF 175 WRED		CGF 200 WRED	
		Daylight Blue	CGF 175 DLTBLUE		CGF 200 DLTBLUE	
		Medium Blue	CGF 175 MBLU		CGF 200 MBLU	
		Medium Amber	CGF 175 MAMB		CGF 200 MAMB	
		Medium Green	CGF 175 MGRN		CGF 200 MGRN	
ouvers	Louvers provide greater visual source cut-off and reduce	Hexcell Louvers	HCLBL 175	_	HCLBL 200	
vebrows an	perceived fixture brightness.					
CDIOWS all	Eyebrows and Snoots extend	Eyebrows			EYEBROWBL 200	
	lamp shielding and can	Snoots			SNOOTBL 200	
arn Doors	reduce spill light at the edge of a beam pattern.					
ZIII DOOFS	Barn Doors create a theatrical	Barn Doors	T74BL 175			
	look and allow control of the spill light at the edge of a beam pattern.					

<sup>\*</sup>Simultaneously accepts any combination of up to two filters, lenses or louvers.

Solite™ is a trademark of AGC Solar.

Trac 12 also offers a variety of linear lighting module options, ideal for cove, undercabinet, undershelf, task, and casework display lighting in residential, retail, or commercial interior applications (search "TL214LED" or "TL201" on our website for additional information).




Photo Credits: Westin River North, Chicago, IL (Picture Boy Photography) Cover, Page 3: Sony Easton Store (Mark Steele Photography)

