

KEENE

by  Signify

Garage & Canopy

LED Luminaire

GC40-GC57-GC88
40W, 57W, and 88W



When you are searching for durable, cost-effective lighting for parking garages, covered walkways and outdoor canopies – the Keene **Garage and Canopy LED luminaire** is exactly what you need. Compact and efficient, it has durable, weather tight construction and a rugged, UV-stabilized, frosted lens.

Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Ordering guide

example: GC57-NW-G1-SM-5-8-BZ

Luminaire	LED Color	Generation	Mounting	Distribution	Voltage	Finish
	NW	G1	SM	5		BZ
GC40 Garage & Canopy LED 40W	NW Neutral White 4000K, 70CRI	G1 Génération 1	SM Surface Mount	5 Type 5 Symmetrical	8 120-277VAC 6 347VAC	BZ Bronze
GC57 Garage & Canopy LED 57W						
GC88 Garage & Canopy LED 88W						

LED Wattage and Lumen Values

Neutral White Ordering Codes	Total LEDs	LED Current (mA)	Color Temp.(K)	Average System Wattage ¹	Lumen Output ^{1,2}	Efficacy (LPW)
GC40-NW-G1-SM-5-8-BZ	1	950	4000	37	4735	128
GC57-NW-G1-SM-5-8-BZ	1	1400	4000	57	6322	111
GC88-NW-G1-SM-5-8-BZ	1	1535	4000	87	10,519	121

1. Wattage and lumen output may vary by +/-8% due to LED manufacturer forward volt specification and ambient temperature.

2. Lumen values based on photometric tests performed in compliance with IESNA LM-79.

NOTE: Contact your Keene representative for additional photometric tests or information.

Predicted Lumen Depreciation Data

Ambient Temp °C	System Current	L ₇₀ per TM21 ^{1,2}	Lumen Maintenance @ 60,000 hrs
25°C	up to 1400 mA	>60,000	80%

1. L₇₀ is the predicted time when LED performance depreciates to 70% of initial lumen output.

2. Calculated per IESNA TM 21-II. Published L₇₀ hours limited to 6 times actual LED test hours.




GC40-GC57-GC88

LED Luminaire 40W, 57W, and 88W


Garage & Canopy

Dimensions

40W & 57W



88W



Approximate Luminaire Weight

40W & 57W: 5.1 lbs (2.31 Kg)

88W: 8.2 lbs (3.72 Kg)

Specifications

Housing and Heat Sink

Single piece die cast Aluminum alloy. Housing also acts as a heat sink, designed to ensure high efficacy and superior cooling by natural convection. Air flow pattern always close to LEDs and driver optimizing their efficiency and life. Product does not use any cooling device with moving parts (only passive cooling).

Mounting

Die formed 16 ga. galvanized steel plate is supplied for mounting to a recessed or surface-mounted 4" (10.16 cm) junction box (by others) – flush ceiling mount to a recessed junction box, or direct mount to a surface-mounted junction box. Integral hanger on the plate supports the luminaire during wiring. Single screw secures luminaire for quick and easy installation. For pendant mounting, casting has 3/4" NPS tapped hole for direct mounting onto rigid 3/4" pendant (by others).

Lens

UV stabilized polycarbonate lens with extruded silicone gasket surrounding the entire perimeter of the LED light engine and electronics compartment providing an IP65 seal. Lens secured with tamper-resistant screws. Lens frosted to help reduce glare.

Light Engine

Composed of 3 main components: LED Module/Optical System / Driver. Electrical components are RoHS compliant. LEDs tested by ISO 17025-2005 accredited lab in accordance with IESNA LM-80 guidelines extrapolations in accordance with IESNA TM-21.

LED Module

Composed of COB white LED. Color temperature as per ANSI/NEMA bin Neutral White, 4000 Kelvin nominal (3985 +/- 275K or 3710K to 4260K), CRI 70 min.

Optical System

Type V symmetric distribution, optimized for target lumens and a superior lighting uniformity. Photometric performance shall be tested per, LM-79 and published in accordance with LM-63.

Driver

High power factor of 90% min. Electronic driver, operating range 50/60 Hz, Class 2.

Other Integrated Features

Surge Protection: Each luminaire is provided as standard with 4kV surge protection.

Wiring

Insulated wiring, seals where wiring exists the luminaire. Due to the inrush current that occurs with electronic drivers, recommend using a time delay or slow blow fuse to avoid unnecessary and unwanted fuse blowing that can occur with fast acting fuses.

Hardware

All exposed screws shall be stainless and/or corrosion resistant and captive. All seals and sealing devices are made and/or lined with EPDM and/or silicone and/or rubber.

Finish

Fade and abrasion resistant, electrostatically applied, thermally cured, triglycidal isocyanurate (TGIC) polyester powdercoat textured bronze finish.

LED Products Manufacturing Standard

The electronic components sensitive to electrostatic discharge (ESD) such as light emitting diodes (LEDs) are assembled in compliance with EC61340-5-1 and ANSI/ESD S20.20 standards so as to eliminate ESD events that could decrease the useful life of the product.

Vibration Resistance

40W & 57W: Surface Mount meets the ANSI C136.31 Luminaire Vibration specifications for Normal applications (1.5G).

All wattages: Pendant Mount meets the ANSI C136.31 Luminaire Vibration specifications for Bridge/Overpass applications (3G).

Certifications and Compliance

cULus Listed for Canada and USA. DesignLights Consortium qualified. Entire luminaire is rated for operation in ambient temperature of -40°C (-40°F) up to +40°C (+104°F).

IP66 Rating

Entire luminaire including light engine and driver/electrical compartment IP66 rated.

Limited Warranty

5-year limited warranty. See signify.com/warranties for details and restrictions. Visit our eCatalog or contact your local sales representative for more information.

