

Selector switch, metal Spring return from right Long lever position, A Cam 2 position Operator only white insert Non-Illuminated UL file E22655 in Vol. 6 (7) Sec. 13 (2)

<b>design of the product</b>	Actuator round
<b>Enclosure</b>	
<b>number of command points</b>	1
<b>delivery state as a kit</b>	No
<b>Actuator</b>	
<b>design of the actuating element</b>	selector switch
<b>material of the actuating element</b>	plastic
<b>shape of the actuating element</b>	Extended handle
<b>type of unlocking device</b>	without
<b>number of switching positions</b>	2
<b>Front ring</b>	
<b>product component front ring</b>	Yes
<b>design of the front ring</b>	standard
<b>material of the front ring</b>	metal
<b>color of the front ring</b>	chrome
<b>Holder</b>	
<b>material of the holder</b>	Metal
<b>General technical data</b>	
<b>product component</b>	No
• light source	
<b>degree of pollution</b>	1
<b>protection class IP</b>	IP66
<b>operating frequency maximum</b>	600 1/h
<b>Ambient conditions</b>	
<b>ambient temperature</b>	
• during operation	-35 ... +70 °C
• during storage	-40 ... +85 °C
<b>Installation/ mounting/ dimensions</b>	
<b>shape of the installation opening</b>	round
<b>Certificates/ approvals</b>	
<b>Further information</b>	

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52SB2ACB>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52SB2ACB>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/US2:52SB2ACB>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=US2:52SB2ACB&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:52SB2ACB&lang=en)

last modified:

5/31/2021 