



# Halogen

Halogen lamps are designed to provide a crisp white light, a long life and constant lumen maintenance.

The use of halogen gas enables the filament to burn slower and to operate at a higher temperature, allowing for a whiter and brighter light output. Halogen also offers for a longer life and greater lumens per watt, making halogen lamps more efficient than regular incandescent lamps.

The crisp white light produced by halogen lamps reflects nicely on crystal by making it sparkle and enhances the beauty of crystal chandeliers.

Halogen lamps are dimmable and can be used in the most compact and stylish fixtures.

Many STANDARD halogen lamps are offered with a coating that filters UV rays and they can be identified by the UV STOP icon.

# A19 Energy Saver



## A19

Order code	Description	Watts (W)	Base	Volts (V)	Lumens output (lm)	Average life (hrs)	Finish	Operating position	Incan. equivalent (W)	Case qty (master)
<b>A19</b>										
62795 <sup>1,2</sup>	H43/A19/CL/120V/STD	43	E26	120	750	1 000	Clear	Universal	60	100
62799 <sup>1,2</sup>	H43/A19/FR/120V/STD	43	E26	120	750	1 000	Frost	Universal	60	100
62801 <sup>1,2</sup>	H72/A19/FR/120V/STD	72	E26	120	1 490	1 000	Frost	Universal	100	100

# JC & JD



## JC (G4)



## T3 (BA15d)



## T3 (E11)

Order code	Description	Watts (W)	Base	Volts (V)	Lumen output (lm)	Average life (hrs)	Finish	Case qty (inner/master)
<b>JC (G4)</b>								
51129	H10JC/CL/2M/G4/12V/STD	10	G4	12	130	2 000	Clear	100/1 000
51130	H20JC/CL/2M/G4/12V/STD	20	G4	12	300	2 000	Clear	100/1 000
67786	H20JC/CL/2M/G4/24V	20	G4	24	350	2 000	Clear	25/100
<b>T3 (BA15d)</b>								
69281	H75T3/CL/2M/BA15D/120V	75	BA15d	130	1 050	2 000	Clear	12/120
69245	H100T3/CL/2M/BA15D/130V/STD S2	100	BA15d	130	1 600	2 000	Clear	50/500
50885	H250T3/CL/2M/BA15D/130V/STD	250	BA15d	130	4 800	2 000	Clear	12/120
<b>T3 (E11)</b>								
69239	H50T3/CL/2M/E11/130V/STD S2	50	E11	130	1 120	2 000	Clear	50/500
69240	H75T3/CL/2M/E11/130V/STD S2	75	E11	130	1 350	2 000	Clear	50/500
69241	H100T3/CL/2M/E11/130V/STD S2	100	E11	130	1 800	2 000	Clear	50/500
69243	H250T3/CL/2M/E11/130V/STD S2	250	E11	130	4 800	2 000	Clear	50/500
69242	H150T3/CL/2M/E11/130V/STD S2	150	E11	130	2 000	2 000	Clear	50/500

<sup>1</sup>This product is affected by provincial Energy Efficiency Regulations in Ontario, Quebec & British Columbia. Note that it will remain available until stock is depleted.



# JD & JCD



JCD (GY6.35)



JCD (G8)



JD (G9 Glass Base)

Order code	Description	Watts (W)	Base	Volts (V)	Lumen output (lm)	Average life (hrs)	Finish	Case qty (inner/master)
<b>JD (G9) - Glass Base</b>								
58260	H25JD/42mm/CL/2M/G9/130V/STD	25	G9	130	255	2 000	Clear	12/120
57259	H40JD/42MM/CL/2M/G9/130V/STD	40	G9	130	480	2 000	Clear	12/120
57256	H40JD/42MM/F/2M/G9/130V/STD	40	G9	130	480	2 000	Frost	12/120
69557	H50JD/42MM/CL/2M/G9/130V/STD S2	50	G9	130	600	2 000	Clear	100/500
57258	H60JD/42MM/CL/2M/G9/130V/STD	60	G9	130	800	2 000	Clear	12/120
58258	H75JD/42mm/CL/2M/G9/130V/STD	75	G9	130	1 050	2 000	Clear	12/120
<b>JCD (GY6.35)</b>								
69577	H20JCD/CL/2M/GY6.35/120V/STD S2	20	GY6.35	120	180	2 000	Clear	100/500
50879	H35JCD/CL/2M/GY6.35/120V/STD	35	GY6.35	120	380	2 000	Clear	12/120
50878	H50JCD/CL/2M/GY6.35/120V/STD	50	GY6.35	120	600	2 000	Clear	12/120
10317	H75JCD/CL/2M/GY6.35/120V/STD	75	GY6.35	120	1 050	2 000	Clear	12/120
<b>JCD (G8)</b>								
55055	H20JCD/CL/2M/G8/120V/STD	20	G8	120	200	2 000	Clear	12/120
15710	JCD100W/130V/G8	100	G8	130	1 600	2 000	Clear	12/120

# Xenon JD



T3 (BA15d)



T3 (E11)



T3 (E12)



T3 (E12)

Order code	Description	Watts (W)	Base	Volts (V)	Lumen output (lm)	Average life (hrs)	Finish	Case qty (inner/master)
<b>T3 (BA15d)</b>								
60956	X60T3/2M/BA15D/120V/STD	60	BA15d	120	960	2 000	Clear	12/120
<b>T3 (E11)</b>								
60954	X60T3/2M/E11/120V/STD	60	E11	120	960	2 000	Clear	12/120
<b>T3 (E12)</b>								
60948	X20T3/2M/E12/120V/STD	20	E12	120	200	2 000	Clear	12/120
<b>T3 (E12)</b>								
60949	X20T3/F/2M/E12/120V/STD	20	E12	120	200	2 000	Frost	12/120
60953	X40T3/F/2M/E12/120V/STD	40	E12	120	560	2 000	Frost	12/120

