

SAFETY DATA SHEET

1. Identification Product identifier	Aluma Shield			
Other means of identification				
SDS number	SDS-00012			
Product code	See Section 16			
Recommended use	Lubricant, Grease and Release Product, Sealant			
Recommended restrictions	None known.			
Manufacturer/Importer/Supplier	/Distributor information			
Company name	ABB Installation Products Inc.			
Address	860 Ridge Lake Blvd.			
	Memphis, TN 38120 US			
Telephone	901-252-5000 ext.8324			
E-mail	Not available.			
Emergency phone number	CHEMTREC - 24 HOURS: +1 800-424-9300			
2. Hazard(s) identification				
Physical hazards	Not classified.			
Health hazards	Not classified.			
OSHA defined hazards	Not classified.			
Label elements				
Hazard symbol	None.			
Signal word	None.			
Hazard statement	The mixture does not meet the criteria for classification.			
Precautionary statement				
Prevention	Observe good industrial hygiene practices.			
Response	Wash hands after handling.			
Storage	Store away from incompatible materials.			
Disposal	Dispose of waste and residues in accordance with local authority requirements.			
Hazard(s) not otherwise classified (HNOC)	None known.			
Supplemental information	Very toxic to aquatic life with long lasting effects.			

3. Composition/information on ingredients

Mixtures

Chemical name		CAS number	%
Zinc (powder)		7440-66-6	45-55
Composition comments	All concentrations are in percent by weight percent by volume. Components not listed are either non-haza The specific chemical identity and/or exact trade secret.	ardous or are below reportable li	mits.
4. First-aid measures			
Inhalation	Move to fresh air. Call a physician if sympt	oms develop or persist.	
Skin contact	Wash off with soap and water. Get medica	I attention if irritation develops a	and persists.
Eye contact	Rinse with water. Get medical attention if i	rritation develops and persists.	
Aluma Shield			SDS U

Ingestion	Rinse mouth. Get medical attention if symptoms occur.
Most important symptoms/effects, acute and delayed	Direct contact with eyes may cause temporary irritation.
Indication of immediate medical attention and special treatment needed	Treat symptomatically.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.
5. Fire-fighting measures	
Suitable extinguishing media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire. Dousing metallic fires with water may generate hydrogen gas, an extremely dangerous explosion hazard, particularly if fire is in a confined environment.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	Move containers from fire area if you can do so without risk.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	No unusual fire or explosion hazards noted.
6. Accidental release meas Personal precautions, protective equipment and emergency procedures	SURES Keep unnecessary personnel away. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Cover with plastic sheet to prevent spreading. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.
	Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.
Environmental precautions	Never return spills in original containers for re-use. For waste disposal, see section 13 of the SDS. Avoid discharge into drains, water courses or onto the ground.
7. Handling and storage	
Precautions for safe handling	Avoid contact with skin, eyes and clothing. Remove and wash contaminated clothing promptly. Do not breathe vapor. Do not eat, drink or smoke when using the product. Wear appropriate personal protective equipment. Observe good industrial hygiene practices. Wash thoroughly after handling.
Conditions for safe storage, including any incompatibilities	Store in tightly closed container. Store away from incompatible materials (see Section 10 of the SDS). Keep out of the reach of children.
8. Exposure controls/perse	onal protection
Occupational exposure limits	No exposure limits noted for ingredient(s).
Biological limit values	No biological exposure limits noted for the ingredient(s).
Exposure guidelines	Occupational Exposure Limits are not relevant to the current physical form of the product.
Appropriate engineering controls	Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.
Individual protection measures, Eye/face protection	such as personal protective equipment Wear safety glasses with side shields (or goggles).
Skin protection Hand protection	Wear appropriate chemical resistant gloves. Nitrile gloves are recommended.
Skin protection Other	Wear suitable protective clothing.

Respiratory protection	In case of insufficient ventilation, wear suitable respiratory equipment.
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
General hygiene considerations	Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties Appearance

Appearance	
Physical state	Solid.
Form	Semifluid. Gel.
Color	Gray.
Odor	Petroleum-like.
Odor threshold	Not available.
рН	Not available.
Melting point/freezing point	> 572 °F (> 300 °C)
Initial boiling point and boiling range	> 572 °F (> 300 °C)
Flash point	> 572.0 °F (> 300.0 °C)
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or exp	losive limits
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	Not available.
Vapor density	Not available.
Relative density	1.63
Solubility(ies)	
Solubility (water)	Negligible.
Solubility (solvents)	Largely.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Explosive properties	Not explosive.
Oxidizing properties	Not oxidizing.

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	Reacts slowly with water.
Conditions to avoid	Contact with incompatible materials.
Incompatible materials	Acids. Oxidizing acids.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Information on likely routes of	-		
Inhalation	No advers	e effects due to inhalation are expected.	
Skin contact	No adverse effects due to skin contact are expected.		
Eye contact	Direct contact with eyes may cause temporary irritation.		
Ingestion	Expected to be a low ingestion hazard.		
Symptoms related to the physical, chemical and toxicological characteristics	Direct con	tact with eyes may cause temporary irritation.	
Information on toxicological ef	fects		
Acute toxicity	Not expec	ted to be acutely toxic.	
Product	Species	з Т	est Results
Aluma Shield (CAS Mixture)			
<u>Acute</u>			
Oral			
LD50		5	575 mg/kg Acute Toxicity estimate
Skin corrosion/irritation	No advers	e effects due to skin contact are expected.	
Serious eye damage/eye	Direct con	tact with eyes may cause temporary irritation.	
irritation			
Respiratory or skin sensitizatio			
Respiratory sensitization	-	piratory sensitizer.	
Skin sensitization		uct is not expected to cause skin sensitization.	
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.		
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.		
IARC Monographs. Overall	Evaluation	of Carcinogenicity	
Not listed. NTP Report on Carcinogen	IS		
Not listed.			
	ed Substanc	es (29 CFR 1910.1001-1053)	
Not regulated.	This was du		
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects. Not classified.		
Specific target organ toxicity - single exposure			
Specific target organ toxicity - repeated exposure	Not classi	fied.	
Aspiration hazard	Not an as	piration hazard.	
Further information	This product has no known adverse effect on human health.		
12. Ecological informatio Ecotoxicity			
Components	Very toxic to aquatic life with long lasting effects.		
Zinc (powder) (CAS 7440-66	<u></u>	Species	Test Results
Algae	EC50	Pseudokirchneriella subcapitata	0.09 - 0.125 mg/l, 72 hours
Crustacea	EC50	Water flea (Daphnia magna)	0.139 - 0.908 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas)	-
			-
Persistence and degradability Bioaccumulative potential	No data a		
Mobility in soil	No data av		

Other adverse effectsNo other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation
potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions	Collect and reclaim or dispose in sealed containers at licensed waste disposal site.
Local disposal regulations	Dispose in accordance with all applicable regulations.
Hazardous waste code	The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information

DOT

Not regulated as dangerous goods.

ΙΑΤΑ

ΙΑΤΑ	
UN number	UN3082
UN proper shipping name	Environmentally hazardous substance, liquid, n.o.s. (ZINC (POWDER))
Transport hazard class(es)	
Class	9
Subsidiary risk	-
Packing group	
Environmental hazards	YES
ERG Code	9L
Special precautions for use	r Read safety instructions, SDS and emergency procedures before handling.
IMDG	
UN number	UN3082
UN proper shipping name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (ZINC (POWDER))
Transport hazard class(es)	
Class	9
Subsidiary risk	-
Packing group	
Environmental hazards	
Marine pollutant	YES
EmS	F-A, S-F
Special precautions for use	r Read safety instructions, SDS and emergency procedures before handling.
Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not established.
General information	IMDG Regulated Marine Pollutant.
15. Regulatory information	n
US federal regulations	This product is not known to be a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
TSCA Section 12(b) Ex	port Notification (40 CFR 707, Subpt. D)
Not regulated.	
	bstance List (40 CFR 302.4)
Zinc (powder) (CAS	
SARA 304 Emergency r	
Not regulated.	
9	ulated Substances (29 CFR 1910.1001-1053)
Not regulated.	
Toxic Substances Control	All components of the mixture on the TSCA $g(h)$ inventory are designated "active"
Act (TSCA)	All components of the mixture on the TSCA 8(b) inventory are designated "active".
Superfund Amendments and Re	eauthorization Act of 1986 (SARA)
SARA 302 Extremely hazard	dous substance
Not listed.	

chemical				
SARA 313 (TRI reporting) Chemical name		0.4.0	0/ h	
Zinc (powder)		CAS number 7440-66-6	<u>% by wt.</u> 45-55	
. ,		7440-00-0	40-00	
ther federal regulations				
Clean Air Act (CAA) Sectior	112 Hazardous Air	Pollutants (HAPS) List		
Not regulated. Clean Air Act (CAA) Sectior	n 112(r) Accidental R	elease Prevention (40 C	FR 68.130)	
Not regulated.				
Safe Drinking Water Act (SDWA)	Not regulated.			
S state regulations				
US. Massachusetts RTK - S	ubstance List			
Zinc (powder) (CAS 7440	·			
US. New Jersey Worker and	Community Right-t	o-Know Act		
Zinc (powder) (CAS 7440 US. Pennsylvania Worker a		t-to-Know Law		
Zinc (powder) (CAS 7440 US. Rhode Island RTK)-66-6)			
Zinc (powder) (CAS 7440)-66-6)			
California Proposition 65				
	any chemicals current	rcement Act of 1986 (Prop ly listed as carcinogens of gov.		
US. California. Candida subd. (a))	te Chemicals List. S	afer Consumer Products	s Regulations (Cal. Code F	Regs, tit. 22, 69502.3,
Zinc (powder) (CAS	7440-66-6)			
ternational Inventories				
Country(s) or region	Inventory name			On inventory (yes/no)
Canada	Domestic Substance	es List (DSL)		Ye
Canada		stances List (NDSL)		N
United States & Puerto Rico	Toxic Substances (Control Act (TSCA) Invento	ory	Ye
*A "Yes" indicates this product co A "No" indicates that one or more country(s).				ninistered by the governing
6. Other information, inc	luding date of pr	eparation or last rev	vision	
sue date	17-December-2015	•		
evision date		•		

Revision date	26-February-2019
Version	E
HMIS® ratings	Health: 0 Flammability: 1 Physical hazard: 0 Personal protection: X
NFPA ratings	
Disclaimer	ABB Installation Products Inc. cannot anticipate product, or the products of other manufacturers the user's responsibility to ensure safe conditio product, and to assume liability for loss injune.

ABB Installation Products Inc. cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available.

Product	Codes			
21059	3LN07	60141	60273NT	ATL10-38
AP8	3LN08	60142	60274	ATL10-38-B1-6
M-53	3LN09	60144	60275	ATL1-38-B1-6
1XPZ5	3LN10	60147	60275NT	ATL20-12
1XPZ6	3LN11	60148	60276	ATL20-12-B1
1XPZ7	3LN12	60150	60278	ATL20-38
1XPZ8	3LN13	60151	60278N	ATL20-38-B1-6
1XPZ9	60096	60154	60278NT	ATL2-14
1XRA1	60097	60156	60284	ATL2-38
1XRA2	60099	60157	60500-TB	ATL2-38-B1
1XRA3	60101-TB	60160	60501-TB	ATL2-38-B1-6
1XRA4	60102-TB	60162	60507-TB	ATL2-38-B2
1XRA5	60103-TB	60165	60512	ATL250-12
1XRA6	60104-TB	60166	60516	ATL2502
1XRA7	60106-TB	60168	60522-TB	ATL2-516
1XRA8	60107-TB	60171	60530-TB	ATL30-12
3LM77	60108-TB	60171NT	60536	ATL30-38
3LM78	60109-TB	60171UF	60542	ATL30-38-B1-6
3LM79	60112-TB	60172	60548	ATL350-12
3LM80	60113-TB	60174	60554	ATL3502
3LM81	60114-TB	60174NT08	60560	ATL4-14
3LM82	60116-TB	60176	60565	ATL4-38
3LM83	60117-TB	60178	60568	ATL4-516-B1-6
3LM84	60118-TB	60230	60571	ATL5002
3LM85	60120	60236	60574	ATL6002
3LM86	60120BT	60238	60576	ATL6-10-B1-6
3LM87	60122	60242	60578	ATL6-14
3LM88	60123	60244	60584	ATL7502
3LM89	60124	60248	6MFT9	ATL8-10-B1-6
3LM90	60126	60250	ASP1	60277
3LM91	60128	60254	ASP10	
3LM92	60129	60256	ASP2	
3LM93	60130	60262	ASP20	
3LM94	60132	60265	ASP250	
3LM95	60134	60267	ASP30	
3LM96	60135	60269	ASP300	
3LM97	60136	60271	ASP4	
3LN04	60136G	60273	ASP40	
3LN05	60138	60273BT	ASP6	
3LN06	60140	60273N	ASP8	