

Plug Fuses: G/GP/TD

Plug Fuses

UL/CSA LISTED POWER FUSES



Mersen Plug Fuses are for industrial and residential applications. Standard non-time delay fuses are for receptacle and lighting circuits. For Canadian requirements, a type “P” fuse is used for non-motor loads and type “D” fuses are used for electric heating and cycling loads circuits. Both fuses have low melting-point temperature elements. Low-Temp time delay plug fuses have thermal sensitivity are also for cycling loads and motor circuits.

CATALOG NUMBERS (AMPS)

Catalog Number Edison Base		
Non-Time Delay CSA	“P” Type Non-time Delay CSA	“D” Type Time-delay CSA
G3	-	-
G6	-	-
G10	-	-
-	GP15	TD15
-	GP20	TD20
-	GP25	TD25
-	GP30	TD30

FR15 Rejector Rings available

FRW Rejection removal tool available to remove FR15

RATINGS:

- **Volts:** 125VAC
- **Amps:** 3 to 30A
- **IR:** 10kA I.R. AC
- Choice of Edison Base, Types “P” or “D”

APPROVALS:

- CSA Certified Class 142301, File 15525



TYPE S PLUG FUSE ADAPTORS

Type S adaptors screw into the Edison base and allow Type S fuses to be installed. Type S adaptors prevent the wrong ampere size fuse from being used.



Cat. No./Rating	Fuse Range - Amps
SAG3-2/10	1-8/10 - 3-2/10
SAG6-1/4	3-1/2 - 6-1/4
SAG15	7 - 15
SAG20	20
SAG30	25 - 30