2														1					
		THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE US										NY WAY	DETRIME	NTAL TO	THE IN	TERESTS	OF PANDUIT CO	RP.	
						NDUIT RT NO.*	RECOMMENDED FASTENER	'A'	'B'	'C'	'D'	'E'	'F'	'G' 'REF'	'H' 'REF'	'I' 'REF'	USE WITH THESE CABLE TIE CROSS SECTIONS	WEIGHT (g) lbs/100	
					TI	M3S8	#8 (M4) SCREW	0.863	0.610	0.373			0.208	0.105 [2.7]	0.325 [8.3]	0.180 [4.6]		0.369 (167.5	
					TN	13S10	#10 (M5) SCREW	[21.9]	[15.5]	[9.4]	0.320 [8.1]	0.088 [2.2]	[5.3]	0.115 [2.9]	0.415 [10.5]	0.210 [5.3]	MINIATURE INTERMEDIATE	0.363 (165.0	
В					TN	13S25	1/4" (M6) SCREW	0.879 [22.3]	0.629 [16.0]	0.379	± .020 [0.5]	± .020 [0.5]	0.210 [5.3]	0.155 [3.9]	0.506 [12.9]	0.262 [6.7]	STANDARD LT. HEAVY	0.296 (134.5	
					TM	3S2510	#10 (M5) SCREW	0.873 [22.2]	0.620 [15.7]	[9.6]			0.212 [5.4]	0.120 [3.0]	0.480	0.200 [5.1]		0.321 (145.5	
	*A *											17A 17A							
\		SEE NOTE 2.										NOTES: *1. SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR. SEE www.panduit.com FOR TEFZEL, METAL DETECTABLE AND PEEK MOUNT DRAWINGS. 2. HOLE DIMENSIONS SHOULD ACCOMMODATE SPECIFIED RECOMMENDED FASTENER.							
		' G '	▼				H' 'C'	* D	V	•	. * E *		CO PR	MPENSA [*] OCESS. UNT AS	TE FOR Pandui Stated	VARIAN T ASSU) ON TH	PIECES TO ICE IN THE PAC IRES MINIMUM F IE BAG. S ARE METRIC [mm	PIECE	
				-	v I	, —	L 'F'					ТІТІ							
A				1	1	A - A					1			M35	5 -	TI	E MOUN		A
	17 A	A 3/10/2023 RVU ANRO MSAD UPDATED MILLIMETERS [] 'H' AND 'I					D 'I'.		GAECN0	ITEN	ITEM REVISION NAME								
	16	 		RVU JADE KJM ADDED NOTE 3.					GAECN0	DATA	DATASET FILE NAME								
	<u> </u>							GAECN0		LINI ESS OTHERWISE SPECIFIED						-			
	13	9/14/17			W LHACL'H'DIAMETER NEED TO CHANGE EROM 385 TO 415 TGAECNO436/T DIMENSIONAL TOLERANCES ARE: IN [mm]]				I SEE N	NOTE 1	1								
A/16	12	12 6/27/13 BWG JADE				RTFI REVISED CHART AND NOTE 1. SEE ECN FOR FULL DETAILS.					GB02391	N/12	THIF			ANGLE ECTION	DRAWING NUMBER: GB0239EN		
D10100DA/16	REV	DATE	BY	CHK	APR		DESCF	IPTION			ECN		NN BY DATE		JADE SCA		SHT 1 OF		SIZE
J				2								9							

1

2