



PL-L Long 4-Pin Base

PL-L 40W/841/4P/RS/IS 1CT/25

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.


Product data

General Information	
Cap-Base	2G11 [2G11]
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	841 [CCT of 4100K]
Luminous Flux	3,500 lumen
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	87 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	36.3 W
Lamp Current (Nom)	0.320 A
Voltage (Nom)	126 V

Voltage (Nom)	126 V
Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	PL-L 40W/841/4P/RS/IS 1CT/25
Order code	927908008429
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927908008429
Full product name	PL-L 40W/841/4P/RS/IS 1CT/25
EAN/UPC - Case	50046677111804
EAN/UPC - Product/Case	046677111809


PL-L Long 4-Pin Base

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-L 40W/841/4P/RS/IS 1CT/25	39 mm	18 mm	540 mm	565 mm	571.6 mm

Photometric data



Spectral Power Distribution Colour - PL-L 40W/841/4P/RS/IS 1CT/25

