










ProLine G2




<p>1</p>  <p>(3x)</p>	<p>2</p>  <p>(1x)</p>	<p>3</p>  <p>(8x)</p>
<p>4</p>  <p>(4x)</p>	<p>5</p> <p>M8x1.25</p>  <p>(4x)</p>	<p>6</p> <p>M8x1.25</p>  <p>(8x)</p>
<p>7</p>  <p>(0x)</p>		




1





2




4X C



3





4X D



4X E

4.5 ± 0.5 N*M
[40 ± 4.0 LBF*IN]



$6.8 \pm 0.7 \text{ N}^*\text{M}$
 $[60 \pm 6.0 \text{ LBF}^*\text{IN}]$

4X F

