



### Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------



### General

Provided equipment	Documentation CD Installation guide Rack Mounting brackets USB cable
Product web sub-family	Cloud-enabled monitoring
Number of tare power	45 W
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

### Physical

Cable length	8 ft (2.44 m)
Number of rack unit	2U
Color	Black
Depth	15.98 in (40.6 cm)
Height	3.39 in (8.6 cm)
Mounting location	Front
Mounting preference	Lower
Net weight	45.24 lb(US) (20.52 kg)
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Width	17.01 in (43.2 cm)

### Input

Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	NEMA 5-15P
Efficiency at full load	85...136 V adjustable 93...130 V
Other Input Voltages	110 V 125 V
Number of cables	1
Nominal Input Voltage	120 V

## Output

Rated power in W	600 W
Max Configurable Power (Watts)	600 W
Harmonic distortion	Less than 5%
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
Other Output Voltages	110 V 125 V
Topology	Line Interactive
Waveform Type	Sine wave
Nb of power socket outlets	6 NEMA 5-15R
Output voltage	120 V
Maximum configurable power in VA	1000 VA
Rated power in VA	1000 VA
Transfer Time	6ms typical : 10ms maximum

## Conformance

Product certifications	CULus ENERGY STAR V2.0 (USA)
Standards	CSA C22.2 No. 107.1 FCC Part 15 class A ICES-003 UL 1778
Equipment protection policy	Lifetime : \$150000

## Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)
Acoustic level	41 dBA
Online Thermal Dissipation	175 Btu/h

## Batteries & Runtime

Battery type	Lead-Acid battery
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Liquid Electrolyte Value	0
Battery Charge Power (Watts)	72 W rated
Battery power in VAh	216 VAh runtime
Battery life	4...6 year(s)
Extendable Run Time	0

## Communications & Management

Free slots	0
Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

## Surge Protection and Filtering

Surge energy rating	680 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

## Ordering and shipping details

GTIN	00731304322733
Package weight(Lbs)	45.66 lb(US) (20.71 kg)

## Packing Units

Package 1 Height	9.25 in (23.5 cm)
Package 1 width	21.06 in (53.5 cm)
Package 1 Length	22.44 in (57 cm)
Number of Units in Package 3	16

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
ENERGY STAR	<a href="#">ENERGY STAR UPS V2.0 (USA)</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------