



SAFETY DATA SHEET

1. Identification

Product identifier Silicone Lubricant

Other means of identification

SDS number SDS-00031

Product code 2015, 5KVBOOT-2L, 5KVBOOT-3L, SL-5, SL5-ELA, 82-08

CAS number 63148-62-9

Recommended use Lubricant

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Company name ABB Installation Products Inc.

Address 860 Ridge Lake Blvd.
Memphis, TN 38120
US

Telephone 901-252-5000 ext.8324

E-mail Not available.

Emergency phone number CHEMTREC - 24 HOURS: +1 800-424-9300

2. Hazard(s) identification

Physical hazards Not classified.

Health hazards Not classified.

OSHA defined hazards Not classified.

Label elements

Hazard symbol None.

Signal word None.

Hazard statement The substance does not meet the criteria for classification.

Precautionary statement

Prevention Observe good industrial hygiene practices.

Response Wash hands after handling.

Storage Store away from incompatible materials.

Disposal Dispose of waste and residues in accordance with local authority requirements.

Hazard(s) not otherwise classified (HNOC) None known.

Supplemental information None.

3. Composition/information on ingredients

Substances

| Chemical name | Common name and synonyms | CAS number | % |
|--------------------------------|--------------------------|------------|------|
| Siloxanes and silicones, Di-Me | | 63148-62-9 | > 99 |

4. First-aid measures

Inhalation Move to fresh air. Call a physician if symptoms develop or persist.

Skin contact Wash off with soap and water. Get medical attention if irritation develops and persists.

Eye contact Rinse with water. Get medical attention if irritation develops and persists.

Ingestion Rinse mouth. Get medical attention if symptoms occur.

| | |
|---|--|
| Most important symptoms/effects, acute and delayed | Direct contact with eyes may cause temporary irritation. |
| Indication of immediate medical attention and special treatment needed | Treat symptomatically. |
| General information | Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. |

5. Fire-fighting measures

| | |
|--|--|
| Suitable extinguishing media | Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2). Do not use water jet as an extinguisher, as this will spread the fire. |
| Unsuitable extinguishing media | |
| Specific hazards arising from the chemical | During fire, gases hazardous to health may be formed. |
| Special protective equipment and precautions for firefighters | Self-contained breathing apparatus and full protective clothing must be worn in case of fire. |
| Fire fighting equipment/instructions | Move containers from fire area if you can do so without risk. |
| Specific methods | Use standard firefighting procedures and consider the hazards of other involved materials. |
| General fire hazards | No unusual fire or explosion hazards noted. Will burn if involved in a fire. |

6. Accidental release measures

| | |
|--|--|
| Personal precautions, protective equipment and emergency procedures | Keep unnecessary personnel away. For personal protection, see section 8 of the SDS. |
| Methods and materials for containment and cleaning up | The product is immiscible with water. In case of spills, beware of slippery floors and surfaces. Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. Following product recovery, flush area with water. Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS. Avoid discharge into drains, water courses or onto the ground. |
| Environmental precautions | |

7. Handling and storage

| | |
|---|--|
| Precautions for safe handling | Avoid contact with skin and eyes. Be aware of potential for surfaces to become slippery. |
| Conditions for safe storage, including any incompatibilities | Store in tightly closed container. Store away from incompatible materials (see Section 10 of the SDS). |

8. Exposure controls/personal protection

| | |
|--|---|
| Occupational exposure limits | No exposure limits noted for ingredient(s). |
| Biological limit values | No biological exposure limits noted for the ingredient(s). |
| Appropriate engineering controls | Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. |
| Individual protection measures, such as personal protective equipment | |
| Eye/face protection | Wear safety glasses with side shields (or goggles). |
| Skin protection | |
| Hand protection | Wear appropriate chemical resistant gloves. |
| Skin protection | |
| Other | Wear suitable protective clothing. |
| Respiratory protection | No personal respiratory protective equipment normally required. |
| Thermal hazards | Wear appropriate thermal protective clothing, when necessary. |

General hygiene considerations

Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state Liquid.
Form Liquid. Hazy liquid.
Color Not available.

Odor Vinegar
Odor threshold Not available.

pH Not available.

Melting point/freezing point Not available.

Initial boiling point and boiling range Not available.

Flash point > 500.0 °F (> 260.0 °C) Cleveland Open Cup

Evaporation rate Not available.

Flammability (solid, gas) Not applicable.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) Not available.

Flammability limit - upper (%) Not available.

Explosive limit - lower (%) Not available.

Explosive limit - upper (%) Not available.

Vapor pressure Not available.

Vapor density Not available.

Relative density 1.0 at 25 °C (water = 1)

Solubility(ies)

Solubility (water) Insoluble (< 0.1%)

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature Not available.

Decomposition temperature Not available.

Viscosity Not available.

Other information

Density 0.94 g/cm³ at 25 °C

Explosive properties Not explosive.

Heat of combustion (NFPA 30B) 0 kJ/g

Kinematic viscosity 1000 mm²/s (77 °F (25 °C))

Oxidizing properties Not oxidizing.

Percent volatile < 0.5 %

Surface tension 20 mN/m (77 °F (25 °C))

VOC < 25 gm/l

10. Stability and reactivity

Reactivity

The product is stable and non-reactive under normal conditions of use, storage and transport.

Chemical stability

Material is stable under normal conditions.

Possibility of hazardous reactions

No dangerous reaction known under conditions of normal use.

Conditions to avoid

Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. Contact with incompatible materials.

| | |
|---|--|
| Incompatible materials | Strong oxidizing agents. |
| Hazardous decomposition products | Carbon oxides. Silicon oxides. Formaldehyde. |

11. Toxicological information

Information on likely routes of exposure

| | |
|---------------------|--|
| Inhalation | No adverse effects due to inhalation are expected. |
| Skin contact | May cause mild skin irritation. |
| Eye contact | Direct contact with eyes may cause temporary irritation. |
| Ingestion | Expected to be a low ingestion hazard. |

Symptoms related to the physical, chemical and toxicological characteristics Direct contact with eyes may cause temporary irritation.

Information on toxicological effects

| | |
|--|--|
| Acute toxicity | Not expected to be acutely toxic. |
| Skin corrosion/irritation | May cause mild skin irritation. |
| Serious eye damage/eye irritation | Direct contact with eyes may cause temporary irritation. |

Respiratory or skin sensitization

| | |
|----------------------------------|---|
| Respiratory sensitization | Not a respiratory sensitizer. |
| Skin sensitization | This product is not expected to cause skin sensitization. |

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity Not classifiable as to carcinogenicity to humans.

IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

NTP Report on Carcinogens

Not listed.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not regulated.

Reproductive toxicity This product is not expected to cause reproductive or developmental effects. Not classified.

Specific target organ toxicity - single exposure

Specific target organ toxicity - repeated exposure Not classified.

Aspiration hazard Not an aspiration hazard.

Chronic effects Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential No data available.

Mobility in soil Expected to have low mobility in soil. The product is insoluble in water.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions Collect and reclaim or dispose in sealed containers at licensed waste disposal site.

Local disposal regulations Dispose in accordance with all applicable regulations.

Hazardous waste code The waste code should be assigned in discussion between the user, the producer and the waste disposal company.

Waste from residues / unused products Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).

Contaminated packaging

Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information**DOT**

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not established.

15. Regulatory information**US federal regulations**

All components are on the U.S. EPA TSCA Inventory List.
This product is not known to be a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)**SARA 302 Extremely hazardous substance**

Not listed.

SARA 311/312 Hazardous chemical No

SARA 313 (TRI reporting)

Not regulated.

Other federal regulations**Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List**

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Contains component(s) regulated under the Safe Drinking Water Act.

US state regulations**US. Massachusetts RTK - Substance List**

Not regulated.

US. New Jersey Worker and Community Right-to-Know Act

Not listed.

US. Pennsylvania Worker and Community Right-to-Know Law

Not listed.

US. Rhode Island RTK

Not regulated.

California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 2016 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins. For more information go to www.P65Warnings.ca.gov.

International Inventories

| Country(s) or region | Inventory name | On inventory (yes/no)* |
|-----------------------------|--|------------------------|
| Australia | Australian Inventory of Chemical Substances (AICS) | Yes |
| Canada | Domestic Substances List (DSL) | Yes |
| Canada | Non-Domestic Substances List (NDSL) | No |
| China | Inventory of Existing Chemical Substances in China (IECSC) | Yes |
| Europe | European Inventory of Existing Commercial Chemical Substances (EINECS) | No |
| Europe | European List of Notified Chemical Substances (ELINCS) | No |
| Japan | Inventory of Existing and New Chemical Substances (ENCS) | Yes |
| Korea | Existing Chemicals List (ECL) | Yes |
| New Zealand | New Zealand Inventory | Yes |
| Philippines | Philippine Inventory of Chemicals and Chemical Substances (PICCS) | Yes |
| Taiwan | Taiwan Chemical Substance Inventory (TCSI) | Yes |
| United States & Puerto Rico | Toxic Substances Control Act (TSCA) Inventory | Yes |

*A "Yes" indicates this product complies with the inventory requirements administered by the governing country(s).

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 18-December-2015

Revision date 21-December-2018

Version D

HMIS® ratings
Health: 1
Flammability: 1
Physical hazard: 0

NFPA ratings



Disclaimer

ABB Installation Products Inc. cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available.