

Fire Alarm Cable

Unshielded Multiconductor

SPECIFICATIONS  **HL**


CSA C22.2 NO. 208, UL listed type FPL

CONSTRUCTION

Conductor: Solid copper conductor

Insulation: PVC

Outer Jacket: -30°C to 105°C, flame and sunlight resistant Polyvinyl Chloride (PVC)



Voltage: 300V

Options: Various colours for outer jackets

Product No.	No. of Conductors	AWG Size	Insulation Thickness		Outer Jacket Thickness		Nominal Diameter		Cable Weight		Maximum Pulling Tension	
			inches	mm	inches	mm	Outer Jacket		Lbs/mft	kg/km	lbs	kgs
							inches	mm				
30-306	6	22	0.012	0.3	0.03	0.76	0.219	5.56	30.11	44.9	12	27
30-315	15	22	0.012	0.3	0.03	0.76	0.305	7.75	60.62	90.4	30	66
30-320	20	22	0.012	0.3	0.032	0.81	0.336	8.53	77.57	115.68	40	88
30-331*	2	18	0.015	0.38	0.03	0.76	0.146 x 0.22 0	3.71 x 5.59	25.96	38.71	4	9
30-332	2	18	0.015	0.38	0.03	0.76	0.213	5.41	25.96	38.71	4	9
30-333	3	18	0.015	0.38	0.03	0.76	0.225	5.72	33.33	49.7	6	13
30-334	4	18	0.015	0.38	0.03	0.76	0.244	6.2	41.22	61.47	8	18
30-335	5	18	0.015	0.38	0.03	0.76	0.265	6.73	49.25	73.45	10	22
30-336	6	18	0.015	0.38	0.032	0.81	0.292	7.42	60.36	90.01	12	27
30-337	7	18	0.015	0.38	0.032	0.81	0.292	7.42	66.96	99.86	14	31
30-338	8	18	0.015	0.38	0.032	0.81	0.315	8	75.3	112.29	16	35
30-339	9	18	0.015	0.38	0.032	0.81	0.337	8.56	83.67	124.77	18	40
30-340	10	18	0.015	0.38	0.032	0.81	0.353	8.97	91.04	135.77	20	44
30-341	11	18	0.015	0.38	0.032	0.81	0.366	9.3	99.32	148.11	22	49
30-345	15	18	0.015	0.38	0.04	1.02	0.415	10.54	128.9	192.23	30	66
30-350	20	18	0.015	0.38	0.04	1.02	0.46	11.68	174.7	260.53	40	88
30-351	21	18	0.015	0.38	0.04	1.02	0.478	12.14	181.77	271.07	42	93
30-360	30	18	0.015	0.38	0.04	1.02	0.557	14.15	245.3	365.81	60	133
30-370	50	18	0.015	0.38	0.048	1.22	0.701	17.81	410	611.42	100	221

*Parallel Construction

FOR MORE INFORMATION

150 North Murray St.
Trenton, Ontario
(800) 263 . 3322
www.decacables.com

 **ECA CABLES**